

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930109

Luminaire Tested: DFN2DS-HX2F0-050DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930109
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-050DS950-FLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4677.7 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 49.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930109

CATALOG NUMBER: DFN2DS-HX2F0-050DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930109

CATALOG NUMBER: DFN2DS-HX2F0-050DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4332	4332	4332
5°	4348	4286	4311
10°	4323	4243	4264
15°	4269	4187	4183
20°	4193	4105	4101
25°	4118	4003	4003
30°	4021	3910	3877
35°	3931	3798	3743
40°	3818	3686	3616
45°	3706	3575	3487
50°	3583	3461	3337
55°	3457	3326	3203
60°	3316	3166	3049
65°	3164	3006	2868
70°	2972	2813	2680
75°	2703	2590	2527
80°	2400	2326	2206
85°	1957	1865	1673

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3706 cd/sqm

TEST NUMBER: P930109

CATALOG NUMBER: DFN2DS-HX2F0-050DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.0	3.7
10°-20°	486.9	10.4
20°-30°	715.5	15.3
30°-40°	831.0	17.8
40°-50°	830.0	17.7
50°-60°	723.7	15.5
60°-70°	535.0	11.4
70°-80°	302.7	6.5
80°-90°	79.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1375.4	29.4
0°-40°	2206.5	47.2
0°-60°	3760.2	80.4
0°-90°	4677.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4677.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1838	1838	1838	1838	1838	
5°	1838	1832	1812	1826	1823	175
15°	1750	1740	1717	1724	1715	493
25°	1584	1570	1540	1543	1540	729
35°	1367	1349	1321	1310	1301	853
45°	1112	1100	1073	1054	1047	858
55°	842	831	810	788	780	752
65°	568	557	539	523	514	561
75°	297	294	284	274	278	317
85°	72	71	69	64	62	85
90°	0	0	0	0	0	

TEST NUMBER: P930109

CATALOG NUMBER: DFN2DS-HX2F0-050DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1838.5	1838.5	1838.5	1838.5	1838.5
2.5°	1849.2	1840.4	1820.9	1838.5	1835.2
5°	1838.5	1831.6	1812.0	1826.1	1822.8
7.5°	1826.1	1815.6	1796.2	1810.4	1806.8
10°	1806.8	1794.5	1773.3	1787.3	1782.1
12.5°	1780.2	1769.7	1748.5	1757.3	1753.7
15°	1750.1	1739.7	1716.6	1723.8	1714.9
17.5°	1713.0	1702.5	1679.5	1688.2	1679.5
20°	1672.4	1661.9	1637.1	1642.3	1635.4
22.5°	1631.8	1615.9	1592.8	1592.8	1589.2
25°	1584.0	1569.9	1539.9	1543.3	1539.9
27.5°	1530.9	1518.5	1495.7	1490.4	1481.6
30°	1478.0	1463.8	1437.3	1432.1	1425.0
32.5°	1421.4	1410.9	1382.5	1371.9	1364.8
35°	1366.6	1349.0	1320.6	1310.0	1301.2
37.5°	1304.7	1288.8	1260.4	1248.1	1239.3
40°	1241.2	1226.9	1198.5	1182.8	1175.7
42.5°	1179.3	1165.0	1136.8	1119.0	1108.5
45°	1112.1	1099.7	1073.0	1053.8	1046.6
47.5°	1046.6	1034.2	1006.0	986.4	975.9
50°	977.6	968.8	944.1	919.3	910.4
52.5°	910.4	898.0	875.2	855.7	843.3
55°	841.6	830.9	809.7	788.5	779.7
57.5°	772.5	763.7	740.7	719.5	712.3
60°	703.6	696.7	671.9	652.3	647.1
62.5°	636.5	624.1	606.4	588.7	581.6
65°	567.6	556.9	539.2	523.3	514.5
67.5°	496.9	487.9	472.1	459.7	452.6
70°	431.4	424.3	408.3	396.0	389.1
72.5°	364.3	357.1	348.3	335.9	330.7
75°	296.9	293.5	284.5	274.0	277.6
77.5°	236.9	229.7	226.2	220.9	215.7
80°	176.9	175.0	171.4	166.2	162.6
82.5°	120.2	120.2	118.5	111.4	111.4
85°	72.4	70.7	69.0	63.6	61.9
87.5°	31.8	28.4	24.8	19.5	17.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930109

CATALOG NUMBER: DFN2DS-HX2F0-050DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.38	17.99	16.74	18.30	18.61	15.93	17.54	16.30	17.86	18.17
	3H	18.13	19.58	18.50	19.91	20.27	17.63	19.09	18.01	19.42	19.78
	4H	18.77	20.14	19.17	20.49	20.87	18.28	19.65	18.68	19.99	20.37
	6H	19.24	20.51	19.65	20.87	21.27	18.74	20.01	19.15	20.37	20.76
	8H	19.38	20.60	19.81	20.98	21.38	18.88	20.09	19.31	20.48	20.88
	12H	19.47	20.63	19.90	21.02	21.45	18.96	20.12	19.39	20.50	20.93
4H	2H	16.94	18.30	17.33	18.65	19.03	16.58	17.95	16.98	18.30	18.68
	3H	18.91	20.06	19.32	20.46	20.86	18.50	19.65	18.91	20.05	20.45
	4H	19.69	20.72	20.12	21.14	21.57	19.26	20.30	19.70	20.71	21.15
	6H	20.28	21.19	20.74	21.63	22.09	19.85	20.76	20.31	21.20	21.65
	8H	20.47	21.32	20.93	21.76	22.23	20.04	20.88	20.50	21.32	21.79
	12H	20.61	21.37	21.09	21.84	22.31	20.15	20.91	20.63	21.39	21.86
8H	4H	19.96	20.81	20.42	21.25	21.72	19.59	20.43	20.05	20.88	21.34
	6H	20.68	21.38	21.17	21.87	22.34	20.29	21.00	20.79	21.49	21.96
	8H	20.93	21.57	21.44	22.07	22.56	20.54	21.17	21.05	21.68	22.17
	12H	21.13	21.69	21.64	22.18	22.74	20.72	21.28	21.23	21.77	22.33
12H	4H	19.99	20.75	20.47	21.22	21.69	19.62	20.38	20.10	20.86	21.33
	6H	20.72	21.35	21.23	21.86	22.35	20.35	20.98	20.86	21.49	21.98
	8H	21.03	21.59	21.54	22.08	22.64	20.66	21.21	21.16	21.71	22.27