

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930110

Luminaire Tested: DFN2DS-HX2F0-050DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930110
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-050DS950-RLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4016.3 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 49.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930110

CATALOG NUMBER: DFN2DS-HX2F0-050DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930110

CATALOG NUMBER: DFN2DS-HX2F0-050DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4601	4601	4601
5°	4619	4543	4569
10°	4583	4469	4431
15°	4531	4337	4212
20°	4458	4147	3939
25°	4383	3933	3675
30°	4280	3712	3337
35°	4178	3472	3040
40°	4077	3223	2696
45°	3958	2945	2384
50°	3835	2663	2080
55°	3709	2359	1786
60°	3564	2040	1482
65°	3399	1714	1350
70°	3202	1412	1241
75°	2960	1287	1159
80°	2613	1151	1056
85°	2055	906	906

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3958 cd/sqm

TEST NUMBER: P930110

CATALOG NUMBER: DFN2DS-HX2F0-050DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	4.6
10°-20°	502.4	12.5
20°-30°	705.4	17.6
30°-40°	768.9	19.1
40°-50°	706.7	17.6
50°-60°	555.0	13.8
60°-70°	361.3	9.0
70°-80°	186.0	4.6
80°-90°	47.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1390.9	34.6
0°-40°	2159.8	53.8
0°-60°	3421.5	85.2
0°-90°	4016.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4016.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1953	1953	1953	1953	1953	
5°	1953	1944	1921	1937	1932	185
15°	1857	1838	1778	1744	1727	523
25°	1686	1629	1513	1440	1414	775
35°	1453	1363	1207	1096	1057	909
45°	1188	1069	884	758	716	917
55°	903	765	574	468	435	807
65°	610	466	308	248	242	604
75°	325	201	141	129	127	344
85°	76	39	34	34	34	91
90°	0	0	0	0	0	

TEST NUMBER: P930110

CATALOG NUMBER: DFN2DS-HX2F0-050DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1952.8	1952.8	1952.8	1952.8	1952.8
2.5°	1961.6	1952.8	1933.4	1951.1	1947.6
5°	1952.8	1944.1	1921.0	1936.9	1931.7
7.5°	1936.9	1926.4	1901.6	1908.6	1899.7
10°	1915.7	1903.3	1868.1	1862.7	1852.1
12.5°	1889.2	1873.4	1825.6	1815.1	1795.5
15°	1857.4	1837.9	1777.9	1744.4	1726.7
17.5°	1820.3	1792.0	1717.7	1678.9	1650.5
20°	1777.9	1742.5	1654.1	1610.1	1571.1
22.5°	1732.0	1691.3	1588.7	1528.7	1502.3
25°	1686.0	1629.4	1512.8	1440.4	1413.7
27.5°	1631.3	1571.1	1442.1	1359.0	1318.4
30°	1573.0	1505.7	1364.3	1274.2	1226.4
32.5°	1516.3	1435.0	1290.2	1184.1	1139.9
35°	1452.7	1362.6	1207.1	1095.7	1056.8
37.5°	1390.9	1293.6	1129.4	1007.3	963.2
40°	1325.5	1219.5	1047.9	922.5	876.6
42.5°	1258.4	1145.2	966.7	835.9	791.8
45°	1187.7	1069.2	883.7	758.1	715.6
47.5°	1120.5	995.1	804.2	678.6	639.8
50°	1046.3	920.8	726.4	604.3	567.4
52.5°	973.7	841.1	652.1	535.5	502.0
55°	903.0	765.2	574.3	468.3	434.8
57.5°	830.7	689.3	505.5	406.5	378.2
60°	756.4	615.0	432.9	342.9	314.6
62.5°	684.0	542.6	371.1	286.3	272.3
65°	609.7	466.5	307.5	247.5	242.1
67.5°	539.0	395.9	247.5	217.4	212.1
70°	464.8	327.0	205.0	187.3	180.2
72.5°	394.2	263.3	171.4	157.3	153.8
75°	325.2	201.4	141.4	129.0	127.3
77.5°	256.3	143.1	111.4	104.2	100.6
80°	192.6	102.5	84.8	77.8	77.8
82.5°	134.3	69.0	58.3	54.7	54.7
85°	76.0	38.8	33.5	33.5	33.5
87.5°	28.4	14.1	14.1	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930110

CATALOG NUMBER: DFN2DS-HX2F0-050DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.54	18.06	16.90	18.37	18.69	12.50	14.02	12.86	14.33	14.65
	3H	18.30	19.67	18.68	20.00	20.36	13.76	15.13	14.14	15.46	15.82
	4H	18.97	20.25	19.37	20.60	20.98	14.27	15.55	14.67	15.89	16.27
	6H	19.46	20.64	19.87	21.01	21.40	14.65	15.83	15.06	16.20	16.59
	8H	19.62	20.75	20.05	21.14	21.54	14.77	15.90	15.20	16.29	16.69
	12H	19.73	20.81	20.16	21.19	21.62	14.85	15.93	15.28	16.31	16.74
4H	2H	16.64	17.92	17.04	18.27	18.65	13.19	14.47	13.59	14.82	15.20
	3H	18.58	19.64	18.99	20.04	20.44	14.64	15.70	15.05	16.10	16.50
	4H	19.32	20.28	19.76	20.70	21.14	15.24	16.19	15.67	16.61	17.05
	6H	19.92	20.75	20.37	21.19	21.65	15.72	16.56	16.18	17.00	17.46
	8H	20.13	20.91	20.59	21.35	21.82	15.89	16.66	16.35	17.11	17.57
	12H	20.28	20.98	20.77	21.46	21.93	16.00	16.70	16.48	17.18	17.65
8H	4H	19.35	20.13	19.81	20.57	21.04	15.59	16.37	16.05	16.81	17.28
	6H	19.99	20.63	20.48	21.12	21.60	16.18	16.82	16.67	17.31	17.79
	8H	20.24	20.81	20.75	21.32	21.81	16.40	16.97	16.91	17.48	17.97
	12H	20.44	20.95	20.95	21.44	22.01	16.58	17.09	17.09	17.58	18.14
12H	4H	19.33	20.03	19.82	20.51	20.98	15.63	16.33	16.12	16.81	17.28
	6H	19.97	20.54	20.48	21.05	21.54	16.24	16.82	16.75	17.33	17.82
	8H	20.25	20.76	20.76	21.25	21.82	16.51	17.02	17.02	17.51	18.08