

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930127

Luminaire Tested: DFN2DS-HX2F0-060DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930127
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-060DS950-FLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5613.3 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 61.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930127

CATALOG NUMBER: DFN2DS-HX2F0-060DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930127

CATALOG NUMBER: DFN2DS-HX2F0-060DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5198	5198	5198
5°	5218	5143	5173
10°	5187	5091	5116
15°	5123	5025	5020
20°	5032	4926	4921
25°	4942	4804	4804
30°	4826	4693	4652
35°	4717	4558	4491
40°	4581	4424	4339
45°	4447	4291	4185
50°	4300	4153	4005
55°	4148	3991	3843
60°	3979	3800	3659
65°	3797	3608	3442
70°	3566	3376	3216
75°	3244	3108	3032
80°	2879	2791	2647
85°	2347	2238	2009

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4447 cd/sqm

TEST NUMBER: P930127

CATALOG NUMBER: DFN2DS-HX2F0-060DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.7	3.7
10°-20°	584.3	10.4
20°-30°	858.6	15.3
30°-40°	997.2	17.8
40°-50°	996.0	17.7
50°-60°	868.5	15.5
60°-70°	642.0	11.4
70°-80°	363.2	6.5
80°-90°	95.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1650.5	29.4
0°-40°	2647.7	47.2
0°-60°	4512.2	80.4
0°-90°	5613.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5613.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2206	2206	2206	2206	2206	
5°	2206	2198	2174	2191	2187	209
15°	2100	2088	2060	2068	2058	592
25°	1901	1884	1848	1852	1848	875
35°	1640	1619	1585	1572	1561	1024
45°	1334	1320	1288	1264	1256	1030
55°	1010	997	972	946	936	903
65°	681	668	647	628	617	673
75°	356	352	341	329	333	380
85°	87	85	83	76	74	102
90°	0	0	0	0	0	

TEST NUMBER: P930127

CATALOG NUMBER: DFN2DS-HX2F0-060DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2206.2	2206.2	2206.2	2206.2	2206.2
2.5°	2219.0	2208.5	2185.0	2206.2	2202.1
5°	2206.2	2197.9	2174.4	2191.4	2187.3
7.5°	2191.4	2178.8	2155.4	2172.5	2168.2
10°	2168.2	2153.4	2127.9	2144.8	2138.4
12.5°	2136.3	2123.6	2098.2	2108.8	2104.5
15°	2100.2	2087.6	2059.9	2068.5	2057.9
17.5°	2055.7	2043.1	2015.4	2025.9	2015.4
20°	2006.8	1994.2	1964.5	1970.8	1962.5
22.5°	1958.2	1939.0	1911.4	1911.4	1907.1
25°	1900.8	1884.0	1847.9	1851.9	1847.9
27.5°	1837.1	1822.2	1794.7	1788.5	1777.9
30°	1773.7	1756.5	1724.8	1718.5	1709.9
32.5°	1705.6	1693.1	1659.0	1646.2	1637.7
35°	1640.0	1618.8	1584.8	1571.9	1561.3
37.5°	1565.7	1546.5	1512.6	1497.6	1487.1
40°	1489.3	1472.2	1438.3	1419.4	1410.8
42.5°	1415.0	1397.9	1364.2	1342.8	1330.2
45°	1334.5	1319.6	1287.7	1264.5	1255.9
47.5°	1255.9	1241.1	1207.1	1183.7	1171.0
50°	1173.1	1162.5	1132.9	1103.1	1092.5
52.5°	1092.5	1077.7	1050.2	1026.8	1012.0
55°	1009.9	997.1	971.6	946.2	935.6
57.5°	927.1	916.6	888.9	863.4	854.8
60°	844.3	835.9	806.3	782.8	776.5
62.5°	763.7	748.8	727.6	706.5	698.0
65°	681.1	668.3	647.1	628.0	617.4
67.5°	596.2	585.4	566.5	551.7	543.1
70°	517.7	509.2	490.0	475.1	466.8
72.5°	437.1	428.6	418.0	403.1	396.8
75°	356.3	352.3	341.4	328.9	333.1
77.5°	284.3	275.8	271.4	265.2	258.8
80°	212.2	210.0	205.7	199.4	195.1
82.5°	144.3	144.3	142.2	133.7	133.7
85°	86.8	84.9	82.8	76.3	74.3
87.5°	38.3	34.0	29.7	23.4	21.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930127

CATALOG NUMBER: DFN2DS-HX2F0-060DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.01	18.62	17.37	18.93	19.25	16.56	18.18	16.93	18.49	18.80
	3H	18.76	20.21	19.14	20.54	20.90	18.27	19.72	18.65	20.05	20.41
	4H	19.41	20.78	19.80	21.12	21.50	18.91	20.28	19.31	20.63	21.00
	6H	19.88	21.14	20.29	21.51	21.90	19.37	20.64	19.78	21.01	21.40
	8H	20.02	21.23	20.44	21.62	22.02	19.51	20.73	19.94	21.11	21.51
	12H	20.11	21.27	20.54	21.65	22.08	19.60	20.76	20.03	21.14	21.57
4H	2H	17.57	18.94	17.97	19.29	19.66	17.22	18.59	17.62	18.93	19.31
	3H	19.55	20.69	19.95	21.09	21.49	19.14	20.28	19.55	20.68	21.08
	4H	20.32	21.36	20.75	21.77	22.21	19.90	20.93	20.33	21.35	21.78
	6H	20.92	21.82	21.37	22.26	22.72	20.49	21.39	20.94	21.83	22.29
	8H	21.11	21.95	21.57	22.40	22.86	20.67	21.52	21.13	21.96	22.42
	12H	21.24	22.00	21.72	22.48	22.94	20.79	21.55	21.27	22.02	22.49
8H	4H	20.60	21.44	21.06	21.88	22.35	20.22	21.07	20.68	21.51	21.97
	6H	21.31	22.01	21.80	22.50	22.98	20.93	21.63	21.42	22.12	22.59
	8H	21.57	22.20	22.08	22.71	23.19	21.18	21.81	21.69	22.31	22.80
	12H	21.77	22.33	22.28	22.82	23.38	21.35	21.91	21.86	22.40	22.96
12H	4H	20.62	21.38	21.10	21.86	22.33	20.26	21.02	20.74	21.49	21.96
	6H	21.35	21.99	21.86	22.49	22.98	20.99	21.62	21.50	22.12	22.61
	8H	21.67	22.23	22.18	22.72	23.28	21.29	21.85	21.80	22.34	22.90