

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930170

Luminaire Tested: DFN2DS-HX3F0-050DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930170
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-050DS840-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4254.3 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930170

CATALOG NUMBER: DFN2DS-HX3F0-050DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930170

CATALOG NUMBER: DFN2DS-HX3F0-050DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2396	2396	2396
5°	2405	2366	2379
10°	2387	2328	2308
15°	2359	2258	2193
20°	2322	2160	2051
25°	2283	2048	1914
30°	2229	1933	1738
35°	2176	1808	1583
40°	2123	1678	1404
45°	2061	1533	1242
50°	1997	1387	1083
55°	1932	1228	930
60°	1856	1062	772
65°	1770	893	703
70°	1668	735	647
75°	1541	670	603
80°	1361	599	550
85°	1070	472	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2061 cd/sqm

TEST NUMBER: P930170

CATALOG NUMBER: DFN2DS-HX3F0-050DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.9	4.6
10°-20°	532.2	12.5
20°-30°	747.2	17.6
30°-40°	814.5	19.1
40°-50°	748.6	17.6
50°-60°	587.9	13.8
60°-70°	382.7	9.0
70°-80°	197.0	4.6
80°-90°	50.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1473.3	34.6
0°-40°	2287.8	53.8
0°-60°	3624.3	85.2
0°-90°	4254.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4254.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2069	2069	2069	2069	2069	
5°	2069	2059	2035	2052	2046	196
15°	1968	1947	1883	1848	1829	554
25°	1786	1726	1602	1526	1498	821
35°	1539	1443	1279	1161	1119	963
45°	1258	1132	936	803	758	972
55°	957	810	608	496	461	855
65°	646	494	326	262	256	640
75°	344	213	150	137	135	364
85°	80	41	36	36	36	96
90°	0	0	0	0	0	

TEST NUMBER: P930170

CATALOG NUMBER: DFN2DS-HX3F0-050DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2068.6	2068.6	2068.6	2068.6	2068.6
2.5°	2077.9	2068.6	2047.9	2066.8	2063.0
5°	2068.6	2059.3	2034.8	2051.6	2046.1
7.5°	2051.6	2040.5	2014.3	2021.7	2012.3
10°	2029.2	2016.1	1978.8	1973.1	1961.9
12.5°	2001.2	1984.4	1933.7	1922.6	1901.9
15°	1967.5	1946.8	1883.3	1847.7	1829.0
17.5°	1928.1	1898.2	1819.5	1778.4	1748.3
20°	1883.3	1845.7	1752.2	1705.5	1664.2
22.5°	1834.6	1791.5	1682.9	1619.3	1591.3
25°	1785.9	1725.9	1602.4	1525.7	1497.5
27.5°	1727.9	1664.2	1527.5	1439.5	1396.5
30°	1666.2	1594.9	1445.1	1349.7	1299.1
32.5°	1606.2	1520.0	1366.7	1254.3	1207.4
35°	1538.8	1443.3	1278.7	1160.7	1119.4
37.5°	1473.3	1370.3	1196.3	1067.0	1020.3
40°	1404.0	1291.8	1110.0	977.2	928.5
42.5°	1332.9	1213.1	1024.0	885.4	838.7
45°	1258.1	1132.5	936.0	803.0	758.1
47.5°	1186.9	1054.1	851.9	718.8	677.7
50°	1108.3	975.4	769.5	640.1	601.0
52.5°	1031.4	891.0	690.8	567.3	531.7
55°	956.6	810.5	608.3	496.1	460.6
57.5°	879.9	730.1	535.4	430.6	400.6
60°	801.2	651.5	458.6	363.3	333.2
62.5°	724.5	574.8	393.1	303.3	288.4
65°	645.8	494.2	325.7	262.2	256.5
67.5°	571.0	419.3	262.2	230.2	224.6
70°	492.4	346.3	217.1	198.4	190.9
72.5°	417.5	278.9	181.6	166.7	162.9
75°	344.4	213.3	149.7	136.6	134.8
77.5°	271.5	151.6	118.0	110.4	106.6
80°	204.0	108.6	89.8	82.4	82.4
82.5°	142.2	73.1	61.8	58.0	58.0
85°	80.5	41.1	35.5	35.5	35.5
87.5°	30.0	14.9	14.9	13.1	13.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930170

CATALOG NUMBER: DFN2DS-HX3F0-050DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.27	15.79	14.64	16.11	16.42	10.23	11.75	10.60	12.07	12.38
	3H	16.04	17.40	16.41	17.73	18.09	11.50	12.86	11.87	13.19	13.55
	4H	16.70	17.98	17.10	18.33	18.71	12.00	13.28	12.40	13.63	14.01
	6H	17.19	18.37	17.60	18.74	19.13	12.38	13.56	12.79	13.93	14.32
	8H	17.36	18.48	17.78	18.87	19.27	12.50	13.63	12.93	14.02	14.42
	12H	17.46	18.54	17.89	18.92	19.35	12.58	13.66	13.01	14.04	14.47
4H	2H	14.37	15.66	14.77	16.00	16.38	10.93	12.21	11.33	12.56	12.93
	3H	16.31	17.37	16.72	17.77	18.17	12.37	13.43	12.78	13.83	14.23
	4H	17.06	18.01	17.49	18.43	18.87	12.97	13.93	13.40	14.34	14.78
	6H	17.65	18.48	18.11	18.92	19.38	13.46	14.29	13.91	14.73	15.19
	8H	17.86	18.64	18.33	19.09	19.55	13.62	14.40	14.08	14.84	15.31
	12H	18.02	18.71	18.50	19.19	19.66	13.74	14.43	14.22	14.91	15.38
8H	4H	17.08	17.86	17.54	18.30	18.77	13.32	14.10	13.79	14.54	15.01
	6H	17.72	18.36	18.22	18.85	19.33	13.91	14.55	14.41	15.04	15.52
	8H	17.97	18.55	18.48	19.06	19.54	14.13	14.71	14.64	15.22	15.70
	12H	18.17	18.68	18.68	19.18	19.74	14.31	14.82	14.82	15.31	15.88
12H	4H	17.07	17.76	17.55	18.24	18.71	13.37	14.06	13.85	14.54	15.01
	6H	17.70	18.28	18.21	18.79	19.28	13.97	14.55	14.49	15.06	15.55
	8H	17.98	18.49	18.49	18.99	19.55	14.25	14.76	14.76	15.25	15.81