

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1037684

Luminaire Tested: S124DS-B575DB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1037684
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DS-B575DB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct Surface with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2493.0 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 24
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1037684

CATALOG NUMBER: S124DS-B575DB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1037684

CATALOG NUMBER: S124DS-B575DB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	73
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62
4	83	71	63	56	81	70	62	56	67	60	55	65	59	54	63	58	53
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41
7	66	52	44	38	64	52	43	37	50	43	37	49	42	37	47	41	37
8	61	48	39	34	60	47	39	34	46	39	33	45	38	33	43	37	33
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30
10	54	41	33	28	52	40	33	28	39	32	27	38	32	27	37	31	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7920	7920	7920
5°	7944	7848	7906
10°	7894	7785	7823
15°	7799	7674	7694
20°	7672	7538	7544
25°	7527	7381	7360
30°	7350	7197	7131
35°	7166	7004	6911
40°	6976	6785	6661
45°	6776	6570	6444
50°	6556	6379	6181
55°	6318	6130	5931
60°	6080	5852	5674
65°	5812	5586	5360
70°	5510	5233	5028
75°	5050	4805	4685
80°	4494	4311	4203
85°	3930	3789	3714

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6776 cd/sqm

TEST NUMBER: P1037684

CATALOG NUMBER: S124DS-B575DB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	3.7
10°-20°	257.9	10.3
20°-30°	379.6	15.2
30°-40°	441.2	17.7
40°-50°	441.2	17.7
50°-60°	385.9	15.5
60°-70°	286.5	11.5
70°-80°	162.5	6.5
80°-90°	46.6	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	729.1	29.2
0°-40°	1170.3	46.9
0°-60°	1997.4	80.1
0°-90°	2493.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2493.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	921	909	914	911	260
25°	837	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	149	149	170
85°	42	42	40	40	40	48
90°	0	0	0	0	0	

TEST NUMBER: P1037684

CATALOG NUMBER: S124DS-B575DB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	971.3	971.3	971.3	971.3	971.3
2.5°	974.4	972.1	963.5	971.3	970.5
5°	970.5	967.4	958.8	967.4	965.8
7.5°	963.5	960.4	951.1	958.1	957.3
10°	953.4	950.3	940.2	946.4	944.8
12.5°	940.2	937.0	926.1	933.2	930.8
15°	923.8	920.7	909.0	913.7	911.4
17.5°	905.1	901.2	890.3	893.5	891.9
20°	884.1	880.2	868.6	870.9	869.3
22.5°	861.6	856.1	844.4	849.1	846.0
25°	836.6	831.2	820.3	821.1	818.0
27.5°	808.6	803.2	793.1	791.5	787.6
30°	780.6	774.4	764.3	761.2	757.3
32.5°	751.0	745.6	734.7	730.8	726.9
35°	719.9	714.5	703.6	698.1	694.2
37.5°	687.2	682.5	670.9	665.4	660.0
40°	655.3	649.1	637.4	629.6	625.7
42.5°	621.1	618.0	604.7	595.4	593.0
45°	587.6	582.2	569.7	561.1	558.8
47.5°	552.6	548.7	537.0	527.7	521.4
50°	516.8	513.7	502.8	491.9	487.2
52.5°	481.8	477.9	466.2	456.8	450.6
55°	444.4	442.1	431.2	421.8	417.2
57.5°	409.4	407.0	396.1	386.8	382.1
60°	372.8	368.9	358.8	351.8	347.9
62.5°	337.0	333.9	323.0	316.8	312.9
65°	301.2	297.3	289.5	281.7	277.8
67.5°	264.6	261.5	253.7	245.9	245.2
70°	231.1	225.7	219.5	213.2	210.9
72.5°	195.3	189.9	185.2	180.6	178.2
75°	160.3	156.4	152.5	149.4	148.7
77.5°	126.1	124.5	120.6	119.9	117.5
80°	95.7	93.4	91.8	90.3	89.5
82.5°	66.2	65.4	65.4	64.6	63.8
85°	42.0	42.0	40.5	40.5	39.7
87.5°	20.2	19.5	18.7	18.7	18.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)