

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930153

Luminaire Tested: DFN2DS-HX3F0-040DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930153
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-040DS850-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4391.7 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 38.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930153

CATALOG NUMBER: DFN2DS-HX3F0-040DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930153

CATALOG NUMBER: DFN2DS-HX3F0-040DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1999	1999	1999
5°	2007	1978	1990
10°	1995	1958	1968
15°	1970	1933	1931
20°	1935	1895	1893
25°	1901	1848	1848
30°	1856	1805	1789
35°	1814	1753	1727
40°	1762	1701	1669
45°	1710	1650	1610
50°	1654	1597	1540
55°	1596	1535	1478
60°	1530	1461	1407
65°	1461	1388	1324
70°	1372	1298	1237
75°	1248	1196	1166
80°	1107	1073	1019
85°	904	861	772

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1710 cd/sqm

TEST NUMBER: P930153

CATALOG NUMBER: DFN2DS-HX3F0-040DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	3.7
10°-20°	457.1	10.4
20°-30°	671.7	15.3
30°-40°	780.2	17.8
40°-50°	779.2	17.7
50°-60°	679.5	15.5
60°-70°	502.3	11.4
70°-80°	284.2	6.5
80°-90°	75.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1291.3	29.4
0°-40°	2071.5	47.2
0°-60°	3530.2	80.4
0°-90°	4391.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4391.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1726	1720	1701	1714	1711	164
15°	1643	1633	1612	1618	1610	463
25°	1487	1474	1446	1449	1446	684
35°	1283	1266	1240	1230	1222	801
45°	1044	1032	1007	989	983	806
55°	790	780	760	740	732	706
65°	533	523	506	491	483	527
75°	279	276	267	257	261	298
85°	68	66	65	60	58	80
90°	0	0	0	0	0	

TEST NUMBER: P930153

CATALOG NUMBER: DFN2DS-HX3F0-040DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1736.1	1727.8	1709.5	1726.0	1722.9
5°	1726.0	1719.5	1701.2	1714.4	1711.3
7.5°	1714.4	1704.5	1686.2	1699.7	1696.3
10°	1696.3	1684.7	1664.8	1678.0	1673.0
12.5°	1671.3	1661.4	1641.5	1649.9	1646.4
15°	1643.1	1633.2	1611.6	1618.3	1610.0
17.5°	1608.3	1598.4	1576.8	1585.0	1576.8
20°	1570.0	1560.1	1537.0	1541.8	1535.4
22.5°	1532.0	1517.0	1495.4	1495.4	1492.0
25°	1487.1	1473.9	1445.7	1448.9	1445.7
27.5°	1437.3	1425.6	1404.2	1399.2	1391.0
30°	1387.6	1374.3	1349.4	1344.4	1337.8
32.5°	1334.5	1324.6	1298.0	1288.0	1281.2
35°	1283.0	1266.5	1239.9	1229.9	1221.6
37.5°	1224.9	1209.9	1183.3	1171.8	1163.5
40°	1165.2	1151.8	1125.2	1110.4	1103.8
42.5°	1107.1	1093.7	1067.3	1050.6	1040.7
45°	1044.0	1032.5	1007.4	989.3	982.6
47.5°	982.6	970.9	944.4	926.1	916.3
50°	917.8	909.5	886.3	863.0	854.7
52.5°	854.7	843.2	821.7	803.4	791.7
55°	790.2	780.1	760.2	740.3	732.1
57.5°	725.3	717.1	695.3	675.5	668.8
60°	660.5	654.0	630.8	612.5	607.5
62.5°	597.5	585.9	569.4	552.7	546.1
65°	532.9	522.8	506.3	491.3	483.1
67.5°	466.4	458.0	443.3	431.6	425.0
70°	405.0	398.4	383.4	371.7	365.2
72.5°	342.0	335.3	327.0	315.4	310.4
75°	278.8	275.6	267.2	257.3	260.6
77.5°	222.4	215.7	212.4	207.4	202.5
80°	166.0	164.2	160.9	156.0	152.7
82.5°	112.9	112.9	111.3	104.6	104.6
85°	68.0	66.4	64.8	59.7	58.1
87.5°	29.9	26.6	23.3	18.3	16.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930153

CATALOG NUMBER: DFN2DS-HX3F0-040DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.69	15.30	14.05	15.61	15.93	13.25	14.86	13.61	15.17	15.48
	3H	15.44	16.89	15.82	17.22	17.58	14.95	16.40	15.33	16.73	17.09
	4H	16.09	17.46	16.48	17.80	18.18	15.59	16.96	15.99	17.31	17.68
	6H	16.56	17.82	16.97	18.19	18.58	16.05	17.32	16.46	17.69	18.08
	8H	16.70	17.91	17.12	18.30	18.70	16.20	17.41	16.62	17.80	18.19
	12H	16.79	17.95	17.22	18.33	18.76	16.28	17.44	16.71	17.82	18.25
4H	2H	14.25	15.62	14.65	15.97	16.34	13.90	15.27	14.30	15.61	15.99
	3H	16.23	17.37	16.64	17.77	18.17	15.82	16.96	16.23	17.36	17.76
	4H	17.00	18.04	17.43	18.45	18.89	16.58	17.61	17.01	18.03	18.46
	6H	17.60	18.50	18.05	18.94	19.40	17.17	18.07	17.62	18.51	18.97
	8H	17.79	18.63	18.25	19.08	19.54	17.35	18.20	17.81	18.64	19.10
	12H	17.92	18.68	18.40	19.16	19.62	17.47	18.23	17.95	18.70	19.17
8H	4H	17.28	18.12	17.74	18.56	19.03	16.90	17.75	17.36	18.19	18.66
	6H	17.99	18.69	18.48	19.18	19.66	17.61	18.31	18.10	18.80	19.27
	8H	18.25	18.88	18.76	19.39	19.87	17.86	18.49	18.37	18.99	19.48
	12H	18.45	19.01	18.96	19.50	20.06	18.04	18.59	18.54	19.08	19.64
12H	4H	17.30	18.06	17.78	18.54	19.01	16.94	17.70	17.42	18.17	18.64
	6H	18.03	18.67	18.54	19.17	19.66	17.67	18.30	18.18	18.80	19.29
	8H	18.35	18.91	18.86	19.40	19.96	17.97	18.53	18.48	19.02	19.58