

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930208

Luminaire Tested: DFN2DS-HX3F0-070DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930208
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-070DS850-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6598.5 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 73.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930208

CATALOG NUMBER: DFN2DS-HX3F0-070DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930208

CATALOG NUMBER: DFN2DS-HX3F0-070DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3716	3716	3716
5°	3731	3670	3690
10°	3702	3610	3579
15°	3660	3503	3402
20°	3601	3350	3182
25°	3540	3177	2969
30°	3457	2998	2695
35°	3375	2805	2455
40°	3293	2603	2178
45°	3197	2378	1926
50°	3098	2151	1680
55°	2996	1905	1443
60°	2879	1648	1198
65°	2746	1385	1090
70°	2586	1140	1002
75°	2391	1039	936
80°	2111	929	853
85°	1659	732	732

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3197 cd/sqm

TEST NUMBER: P930208

CATALOG NUMBER: DFN2DS-HX3F0-070DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.7	4.6
10°-20°	825.5	12.5
20°-30°	1158.9	17.6
30°-40°	1263.3	19.1
40°-50°	1161.1	17.6
50°-60°	911.9	13.8
60°-70°	593.5	9.0
70°-80°	305.5	4.6
80°-90°	78.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2285.1	34.6
0°-40°	3548.4	53.8
0°-60°	5621.4	85.2
0°-90°	6598.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6598.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3208	3208	3208	3208	3208	
5°	3208	3194	3156	3182	3174	304
15°	3052	3020	2921	2866	2837	860
25°	2770	2677	2485	2366	2323	1274
35°	2387	2239	1983	1800	1736	1494
45°	1951	1756	1452	1246	1176	1507
55°	1484	1257	944	770	714	1326
65°	1002	766	505	407	398	993
75°	534	331	232	212	209	565
85°	125	64	55	55	55	150
90°	0	0	0	0	0	

TEST NUMBER: P930208

CATALOG NUMBER: DFN2DS-HX3F0-070DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3208.4	3208.4	3208.4	3208.4	3208.4
2.5°	3222.9	3208.4	3176.4	3205.7	3199.8
5°	3208.4	3193.9	3156.1	3182.3	3173.6
7.5°	3182.3	3165.0	3124.4	3135.7	3121.3
10°	3147.5	3127.2	3069.2	3060.3	3043.0
12.5°	3104.0	3077.8	2999.3	2982.0	2949.9
15°	3051.6	3019.6	2921.0	2865.9	2836.9
17.5°	2990.6	2944.2	2822.2	2758.3	2711.8
20°	2921.0	2862.8	2717.7	2645.3	2581.2
22.5°	2845.6	2778.7	2610.1	2511.6	2468.2
25°	2770.1	2677.0	2485.4	2366.5	2322.8
27.5°	2680.1	2581.2	2369.3	2232.9	2166.0
30°	2584.3	2473.7	2241.4	2093.6	2015.1
32.5°	2491.3	2357.6	2119.7	1945.4	1872.7
35°	2386.8	2238.6	1983.3	1800.4	1736.3
37.5°	2285.2	2125.3	1855.5	1654.8	1582.5
40°	2177.6	2003.6	1721.7	1515.7	1440.1
42.5°	2067.4	1881.6	1588.3	1373.3	1301.0
45°	1951.3	1756.5	1451.9	1245.5	1175.9
47.5°	1840.9	1634.9	1321.3	1114.9	1051.1
50°	1719.0	1512.9	1193.4	992.9	932.2
52.5°	1599.7	1381.9	1071.4	879.8	824.7
55°	1483.6	1257.2	943.5	769.5	714.4
57.5°	1364.7	1132.4	830.5	667.8	621.4
60°	1242.7	1010.4	711.3	563.5	516.9
62.5°	1123.7	891.5	609.6	470.4	447.3
65°	1001.8	766.4	505.3	406.7	397.7
67.5°	885.6	650.3	406.7	357.0	348.4
70°	763.7	537.2	336.7	307.7	296.0
72.5°	647.5	432.5	281.6	258.5	252.6
75°	534.2	330.8	232.2	211.9	209.2
77.5°	421.1	235.0	183.0	171.2	165.5
80°	316.4	168.5	139.3	127.9	127.9
82.5°	220.6	113.3	95.8	89.9	89.9
85°	124.8	63.8	55.1	55.1	55.1
87.5°	46.5	23.1	23.1	20.3	20.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930208

CATALOG NUMBER: DFN2DS-HX3F0-070DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.80	17.32	16.16	17.63	17.95	11.76	13.28	12.12	13.59	13.91
	3H	17.56	18.93	17.94	19.25	19.62	13.02	14.39	13.40	14.71	15.08
	4H	18.23	19.51	18.63	19.86	20.23	13.52	14.80	13.92	15.15	15.53
	6H	18.72	19.90	19.13	20.27	20.66	13.90	15.09	14.32	15.45	15.85
	8H	18.88	20.01	19.31	20.40	20.80	14.03	15.16	14.46	15.54	15.95
	12H	18.98	20.06	19.42	20.45	20.87	14.11	15.19	14.54	15.57	16.00
4H	2H	15.90	17.18	16.30	17.53	17.91	12.45	13.73	12.85	14.08	14.46
	3H	17.83	18.90	18.24	19.30	19.70	13.89	14.96	14.31	15.36	15.76
	4H	18.58	19.54	19.01	19.95	20.39	14.49	15.45	14.93	15.87	16.30
	6H	19.17	20.01	19.63	20.45	20.91	14.98	15.81	15.44	16.26	16.72
	8H	19.39	20.17	19.85	20.61	21.08	15.14	15.92	15.61	16.37	16.83
	12H	19.54	20.24	20.02	20.71	21.19	15.26	15.96	15.74	16.43	16.91
8H	4H	18.61	19.38	19.07	19.83	20.30	14.85	15.63	15.31	16.07	16.54
	6H	19.24	19.89	19.74	20.38	20.86	15.43	16.08	15.93	16.57	17.05
	8H	19.49	20.07	20.01	20.58	21.07	15.66	16.23	16.17	16.74	17.23
	12H	19.70	20.21	20.21	20.70	21.27	15.83	16.34	16.34	16.84	17.40
12H	4H	18.59	19.29	19.07	19.76	20.23	14.89	15.59	15.37	16.06	16.54
	6H	19.22	19.80	19.74	20.31	20.80	15.50	16.08	16.01	16.59	17.07
	8H	19.51	20.02	20.02	20.51	21.08	15.77	16.28	16.28	16.77	17.34