

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930209

Luminaire Tested: DFN2DS-HX3F0-070DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930209
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-070DS927-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5488.6 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 73.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930209

CATALOG NUMBER: DFN2DS-HX3F0-070DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930209

CATALOG NUMBER: DFN2DS-HX3F0-070DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2499	2499	2499
5°	2508	2472	2487
10°	2494	2447	2459
15°	2463	2415	2413
20°	2419	2368	2365
25°	2375	2309	2309
30°	2320	2256	2236
35°	2267	2191	2159
40°	2202	2126	2086
45°	2137	2062	2012
50°	2067	1996	1925
55°	1994	1919	1847
60°	1912	1826	1759
65°	1825	1734	1655
70°	1714	1623	1546
75°	1559	1494	1458
80°	1384	1342	1273
85°	1130	1077	965

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2137 cd/sqm

TEST NUMBER: P930209

CATALOG NUMBER: DFN2DS-HX3F0-070DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.0	3.7
10°-20°	571.3	10.4
20°-30°	839.5	15.3
30°-40°	975.1	17.8
40°-50°	973.8	17.7
50°-60°	849.2	15.5
60°-70°	627.7	11.4
70°-80°	355.2	6.5
80°-90°	93.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1613.8	29.4
0°-40°	2588.9	47.2
0°-60°	4411.9	80.4
0°-90°	5488.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5488.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2157	2157	2157	2157	2157	
5°	2157	2149	2126	2143	2139	205
15°	2054	2041	2014	2022	2012	578
25°	1859	1842	1807	1811	1807	855
35°	1604	1583	1550	1537	1527	1001
45°	1305	1290	1259	1236	1228	1007
55°	988	975	950	925	915	883
65°	666	653	633	614	604	658
75°	348	344	334	322	326	372
85°	85	83	81	75	73	100
90°	0	0	0	0	0	

TEST NUMBER: P930209

CATALOG NUMBER: DFN2DS-HX3F0-070DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2157.2	2157.2	2157.2	2157.2	2157.2
2.5°	2169.8	2159.4	2136.5	2157.2	2153.2
5°	2157.2	2149.1	2126.2	2142.7	2138.7
7.5°	2142.7	2130.3	2107.4	2124.2	2120.0
10°	2120.0	2105.5	2080.6	2097.1	2091.0
12.5°	2088.7	2076.5	2051.6	2061.9	2057.7
15°	2053.6	2041.2	2014.1	2022.5	2012.2
17.5°	2009.9	1997.7	1970.6	1981.0	1970.6
20°	1962.2	1949.9	1920.8	1927.0	1918.9
22.5°	1914.7	1896.0	1868.9	1868.9	1864.7
25°	1858.6	1842.0	1806.9	1810.8	1806.9
27.5°	1796.3	1781.8	1754.9	1748.7	1738.4
30°	1734.2	1717.5	1686.5	1680.3	1671.9
32.5°	1667.7	1655.4	1622.2	1609.7	1601.3
35°	1603.5	1582.8	1549.5	1537.0	1526.7
37.5°	1530.9	1512.2	1478.9	1464.4	1454.0
40°	1456.3	1439.5	1406.3	1387.8	1379.4
42.5°	1383.6	1366.9	1333.9	1313.0	1300.6
45°	1304.8	1290.3	1259.0	1236.4	1228.0
47.5°	1228.0	1213.5	1180.2	1157.3	1145.1
50°	1147.1	1136.7	1107.6	1078.6	1068.2
52.5°	1068.2	1053.8	1026.9	1004.0	989.4
55°	987.5	975.0	950.1	925.2	914.8
57.5°	906.5	896.1	869.1	844.2	835.9
60°	825.5	817.3	788.4	765.5	759.3
62.5°	746.7	732.2	711.5	690.9	682.5
65°	666.0	653.4	632.7	614.0	603.7
67.5°	583.0	572.5	553.9	539.4	531.0
70°	506.2	497.9	479.1	464.6	456.4
72.5°	427.4	419.0	408.7	394.2	388.0
75°	348.4	344.4	333.8	321.6	325.7
77.5°	278.0	269.6	265.4	259.2	253.1
80°	207.5	205.4	201.2	195.0	190.8
82.5°	141.1	141.1	139.1	130.8	130.8
85°	85.0	83.0	81.0	74.6	72.6
87.5°	37.4	33.3	29.1	22.9	20.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930209

CATALOG NUMBER: DFN2DS-HX3F0-070DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.46	16.07	14.83	16.39	16.70	14.02	15.63	14.38	15.94	16.26
	3H	16.21	17.67	16.59	18.00	18.36	15.72	17.18	16.10	17.50	17.86
	4H	16.86	18.23	17.26	18.58	18.95	16.37	17.73	16.76	18.08	18.46
	6H	17.33	18.60	17.74	18.96	19.35	16.83	18.10	17.24	18.46	18.85
	8H	17.47	18.68	17.90	19.07	19.47	16.97	18.18	17.39	18.57	18.97
	12H	17.56	18.72	17.99	19.11	19.53	17.05	18.21	17.48	18.59	19.02
4H	2H	15.02	16.39	15.42	16.74	17.12	14.67	16.04	15.07	16.39	16.76
	3H	17.00	18.15	17.41	18.54	18.94	16.59	17.74	17.00	18.14	18.54
	4H	17.78	18.81	18.21	19.23	19.66	17.35	18.39	17.78	18.80	19.24
	6H	18.37	19.28	18.83	19.72	20.17	17.94	18.85	18.39	19.29	19.74
	8H	18.56	19.41	19.02	19.85	20.32	18.12	18.97	18.59	19.41	19.88
	12H	18.69	19.45	19.17	19.93	20.40	18.24	19.00	18.72	19.48	19.95
8H	4H	18.05	18.90	18.51	19.34	19.80	17.68	18.52	18.14	18.96	19.43
	6H	18.76	19.47	19.26	19.96	20.43	18.38	19.09	18.88	19.57	20.05
	8H	19.02	19.65	19.53	20.16	20.65	18.63	19.26	19.14	19.77	20.26
	12H	19.22	19.78	19.73	20.27	20.83	18.81	19.37	19.32	19.86	20.42
12H	4H	18.08	18.84	18.56	19.31	19.78	17.71	18.47	18.19	18.95	19.42
	6H	18.81	19.44	19.32	19.95	20.43	18.44	19.07	18.95	19.58	20.07
	8H	19.12	19.68	19.63	20.17	20.73	18.75	19.30	19.25	19.79	20.36