

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930229

Luminaire Tested: DFN2DS-HX3F0-080DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930229
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-080DS930-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6454.8 lumens
Efficiency: N/A
Efficacy: 76.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 84.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930229

CATALOG NUMBER: DFN2DS-HX3F0-080DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930229

CATALOG NUMBER: DFN2DS-HX3F0-080DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2939	2939	2939
5°	2950	2908	2925
10°	2933	2878	2892
15°	2896	2841	2838
20°	2845	2785	2782
25°	2794	2716	2716
30°	2728	2653	2630
35°	2667	2577	2539
40°	2590	2501	2453
45°	2514	2426	2366
50°	2431	2347	2264
55°	2345	2257	2173
60°	2249	2148	2069
65°	2147	2039	1946
70°	2016	1908	1818
75°	1834	1758	1714
80°	1628	1578	1497
85°	1328	1267	1135

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2514 cd/sqm

TEST NUMBER: P930229

CATALOG NUMBER: DFN2DS-HX3F0-080DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.8	3.7
10°-20°	671.8	10.4
20°-30°	987.3	15.3
30°-40°	1146.7	17.8
40°-50°	1145.3	17.7
50°-60°	998.7	15.5
60°-70°	738.2	11.4
70°-80°	417.7	6.5
80°-90°	110.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1898.0	29.4
0°-40°	3044.7	47.2
0°-60°	5188.6	80.4
0°-90°	6454.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6454.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2537	2537	2537	2537	2537	
5°	2537	2527	2500	2520	2515	241
15°	2415	2401	2369	2379	2366	680
25°	2186	2166	2125	2130	2125	1006
35°	1886	1862	1822	1808	1795	1178
45°	1535	1517	1481	1454	1444	1184
55°	1161	1146	1117	1088	1076	1038
65°	783	768	744	722	710	774
75°	410	405	393	378	383	437
85°	100	98	95	88	85	117
90°	0	0	0	0	0	

TEST NUMBER: P930229

CATALOG NUMBER: DFN2DS-HX3F0-080DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2536.9	2536.9	2536.9	2536.9	2536.9
2.5°	2551.7	2539.5	2512.6	2536.9	2532.3
5°	2536.9	2527.4	2500.5	2519.9	2515.3
7.5°	2519.9	2505.4	2478.5	2498.1	2493.2
10°	2493.2	2476.1	2446.9	2466.3	2459.1
12.5°	2456.5	2442.0	2412.7	2424.9	2420.0
15°	2415.1	2400.6	2368.7	2378.6	2366.4
17.5°	2363.8	2349.3	2317.5	2329.7	2317.5
20°	2307.7	2293.2	2259.0	2266.3	2256.7
22.5°	2251.8	2229.8	2197.9	2197.9	2193.0
25°	2185.7	2166.4	2124.9	2129.6	2124.9
27.5°	2112.5	2095.4	2063.8	2056.6	2044.4
30°	2039.5	2019.8	1983.4	1976.1	1966.3
32.5°	1961.4	1946.9	1907.8	1893.0	1883.2
35°	1885.7	1861.5	1822.3	1807.6	1795.4
37.5°	1800.3	1778.3	1739.3	1722.2	1710.0
40°	1712.6	1692.9	1653.9	1632.1	1622.3
42.5°	1627.2	1607.5	1568.7	1544.1	1529.7
45°	1534.6	1517.4	1480.7	1454.0	1444.3
47.5°	1444.3	1427.1	1388.0	1361.1	1346.6
50°	1349.0	1336.8	1302.6	1268.5	1256.3
52.5°	1256.3	1239.2	1207.7	1180.8	1163.7
55°	1161.3	1146.5	1117.4	1088.1	1075.9
57.5°	1066.1	1054.0	1022.1	992.8	983.0
60°	970.8	961.3	927.1	900.2	892.9
62.5°	878.2	861.1	836.8	812.5	802.6
65°	783.2	768.5	744.1	722.1	709.9
67.5°	685.6	673.2	651.4	634.4	624.5
70°	595.3	585.4	563.5	546.4	536.8
72.5°	502.6	492.8	480.6	463.6	456.3
75°	409.7	405.1	392.7	378.2	383.0
77.5°	326.9	317.0	312.1	304.9	297.6
80°	244.1	241.5	236.6	229.3	224.4
82.5°	165.9	165.9	163.6	153.7	153.7
85°	99.9	97.6	95.3	87.8	85.4
87.5°	44.0	39.1	34.1	26.9	24.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930229

CATALOG NUMBER: DFN2DS-HX3F0-080DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.03	16.64	15.39	16.95	17.27	14.58	16.19	14.95	16.51	16.82
	3H	16.78	18.23	17.16	18.56	18.92	16.29	17.74	16.66	18.07	18.43
	4H	17.42	18.79	17.82	19.14	19.52	16.93	18.30	17.33	18.65	19.02
	6H	17.89	19.16	18.30	19.53	19.92	17.39	18.66	17.80	19.02	19.42
	8H	18.04	19.25	18.46	19.64	20.04	17.53	18.74	17.96	19.13	19.53
	12H	18.13	19.29	18.56	19.67	20.10	17.61	18.77	18.04	19.16	19.58
4H	2H	15.59	16.96	15.99	17.31	17.68	15.24	16.60	15.63	16.95	17.33
	3H	17.56	18.71	17.97	19.11	19.51	17.16	18.30	17.57	18.70	19.10
	4H	18.34	19.38	18.77	19.79	20.23	17.92	18.95	18.35	19.37	19.80
	6H	18.94	19.84	19.39	20.28	20.74	18.50	19.41	18.96	19.85	20.31
	8H	19.13	19.97	19.59	20.41	20.88	18.69	19.53	19.15	19.98	20.44
	12H	19.26	20.02	19.74	20.49	20.96	18.81	19.57	19.29	20.04	20.51
8H	4H	18.61	19.46	19.07	19.90	20.37	18.24	19.09	18.70	19.53	19.99
	6H	19.33	20.03	19.82	20.52	20.99	18.95	19.65	19.44	20.14	20.61
	8H	19.59	20.22	20.10	20.72	21.21	19.19	19.83	19.70	20.33	20.82
	12H	19.79	20.34	20.29	20.84	21.40	19.37	19.93	19.88	20.42	20.98
12H	4H	18.64	19.40	19.12	19.88	20.34	18.27	19.03	18.75	19.51	19.98
	6H	19.37	20.00	19.88	20.51	21.00	19.00	19.64	19.51	20.14	20.63
	8H	19.69	20.24	20.19	20.74	21.30	19.31	19.87	19.82	20.36	20.92