

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930159

Luminaire Tested: DFN2DS-HX3F0-040DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930159
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-040DS935-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3405.6 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 38.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930159

CATALOG NUMBER: DFN2DS-HX3F0-040DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930159

CATALOG NUMBER: DFN2DS-HX3F0-040DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1550	1550	1550
5°	1556	1534	1543
10°	1547	1519	1526
15°	1528	1499	1497
20°	1501	1469	1468
25°	1474	1433	1433
30°	1439	1400	1388
35°	1407	1360	1340
40°	1366	1319	1294
45°	1326	1280	1248
50°	1283	1239	1194
55°	1238	1191	1146
60°	1187	1133	1091
65°	1133	1076	1027
70°	1064	1007	959
75°	968	927	905
80°	859	833	790
85°	700	667	599

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1326 cd/sqm

TEST NUMBER: P930159

CATALOG NUMBER: DFN2DS-HX3F0-040DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.0	3.7
10°-20°	354.5	10.4
20°-30°	520.9	15.3
30°-40°	605.0	17.8
40°-50°	604.3	17.7
50°-60°	526.9	15.5
60°-70°	389.5	11.4
70°-80°	220.4	6.5
80°-90°	58.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1001.4	29.4
0°-40°	1606.4	47.2
0°-60°	2737.6	80.4
0°-90°	3405.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3405.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1338	1338	1338	1338	1338	
5°	1338	1333	1319	1330	1327	127
15°	1274	1266	1250	1255	1248	359
25°	1153	1143	1121	1124	1121	531
35°	995	982	962	954	947	621
45°	810	801	781	767	762	625
55°	613	605	590	574	568	548
65°	413	405	393	381	375	409
75°	216	214	207	200	202	231
85°	53	52	50	46	45	62
90°	0	0	0	0	0	



TEST NUMBER: P930159

CATALOG NUMBER: DFN2DS-HX3F0-040DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1338.5	1338.5	1338.5	1338.5	1338.5
2.5°	1346.3	1339.9	1325.7	1338.5	1336.1
5°	1338.5	1333.4	1319.2	1329.5	1327.1
7.5°	1329.5	1321.8	1307.6	1318.0	1315.5
10°	1315.5	1306.4	1291.0	1301.3	1297.4
12.5°	1296.0	1288.4	1273.0	1279.4	1276.8
15°	1274.2	1266.5	1249.8	1254.9	1248.5
17.5°	1247.2	1239.5	1222.7	1229.1	1222.7
20°	1217.5	1209.8	1191.9	1195.7	1190.7
22.5°	1188.0	1176.4	1159.6	1159.6	1157.0
25°	1153.2	1142.9	1121.1	1123.6	1121.1
27.5°	1114.6	1105.5	1088.9	1085.1	1078.7
30°	1076.0	1065.7	1046.4	1042.6	1037.4
32.5°	1034.8	1027.2	1006.5	998.8	993.6
35°	994.9	982.1	961.5	953.7	947.3
37.5°	949.9	938.3	917.6	908.7	902.2
40°	903.6	893.2	872.6	861.1	856.0
42.5°	858.5	848.1	827.7	814.7	807.0
45°	809.6	800.7	781.2	767.2	762.0
47.5°	762.0	752.9	732.4	718.2	710.5
50°	711.7	705.3	687.3	669.3	662.8
52.5°	662.8	653.9	637.2	623.0	614.0
55°	612.8	604.9	589.5	574.0	567.7
57.5°	562.4	556.1	539.2	523.8	518.7
60°	512.2	507.1	489.2	475.0	471.1
62.5°	463.4	454.3	441.5	428.6	423.5
65°	413.2	405.4	392.6	381.0	374.6
67.5°	361.7	355.2	343.7	334.7	329.6
70°	314.1	308.9	297.3	288.3	283.2
72.5°	265.2	260.0	253.6	244.6	240.7
75°	216.2	213.7	207.2	199.5	202.1
77.5°	172.4	167.3	164.7	160.8	157.0
80°	128.7	127.4	124.8	121.0	118.4
82.5°	87.5	87.5	86.3	81.1	81.1
85°	52.7	51.5	50.2	46.3	45.1
87.5°	23.2	20.6	18.1	14.2	12.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930159

CATALOG NUMBER: DFN2DS-HX3F0-040DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.81	14.42	13.17	14.73	15.05	12.36	13.97	12.73	14.29	14.60
	3H	14.56	16.01	14.93	16.34	16.70	14.07	15.52	14.44	15.85	16.21
	4H	15.20	16.57	15.60	16.92	17.30	14.71	16.08	15.11	16.42	16.80
	6H	15.67	16.94	16.08	17.30	17.70	15.17	16.44	15.58	16.80	17.19
	8H	15.81	17.03	16.24	17.41	17.81	15.31	16.52	15.74	16.91	17.31
	12H	15.90	17.06	16.33	17.45	17.88	15.39	16.55	15.82	16.93	17.36
4H	2H	13.37	14.74	13.77	15.08	15.46	13.01	14.38	13.41	14.73	15.11
	3H	15.34	16.49	15.75	16.89	17.29	14.94	16.08	15.34	16.48	16.88
	4H	16.12	17.15	16.55	17.57	18.00	15.69	16.73	16.13	17.14	17.58
	6H	16.71	17.62	17.17	18.06	18.52	16.28	17.19	16.74	17.63	18.08
	8H	16.90	17.75	17.36	18.19	18.66	16.47	17.31	16.93	17.76	18.22
	12H	17.04	17.80	17.52	18.27	18.74	16.58	17.34	17.06	17.82	18.29
8H	4H	16.39	17.24	16.85	17.68	18.15	16.02	16.86	16.48	17.31	17.77
	6H	17.11	17.81	17.60	18.30	18.77	16.72	17.43	17.22	17.92	18.39
	8H	17.36	18.00	17.87	18.50	18.99	16.97	17.60	17.48	18.11	18.60
	12H	17.56	18.12	18.07	18.61	19.17	17.15	17.71	17.66	18.20	18.76
12H	4H	16.42	17.18	16.90	17.65	18.12	16.05	16.81	16.53	17.29	17.76
	6H	17.15	17.78	17.66	18.29	18.78	16.78	17.41	17.29	17.92	18.41
	8H	17.46	18.02	17.97	18.51	19.07	17.09	17.64	17.59	18.14	18.70