

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036900

Luminaire Tested: S122DS-B1005DB30-4F0-XX-W2A-F

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036900
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DS-B1005DB30-4F0-XX-W2A-F
Description: Define 2 Direct Surface with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4064.0 lumens
Efficiency: N/A
Efficacy: 66.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036900

CATALOG NUMBER: S122DS-B1005DB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1036900

CATALOG NUMBER: S122DS-B1005DB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25286	25286	25286
5°	25382	25015	25163
10°	25231	24763	24885
15°	24919	24441	24416
20°	24476	23959	23934
25°	24036	23366	23366
30°	23471	22824	22628
35°	22943	22172	21846
40°	22280	21519	21106
45°	21627	20870	20356
50°	20917	20198	19479
55°	20177	19415	18695
60°	19353	18479	17798
65°	18465	17548	16743
70°	17346	16421	15639
75°	15779	15125	14746
80°	14002	13582	12881
85°	11442	10879	9771

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21627 cd/sqm

TEST NUMBER: P1036900

CATALOG NUMBER: S122DS-B1005DB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.3	3.7
10°-20°	423.0	10.4
20°-30°	621.6	15.3
30°-40°	722.0	17.8
40°-50°	721.1	17.7
50°-60°	628.8	15.5
60°-70°	464.8	11.4
70°-80°	263.0	6.5
80°-90°	69.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1195.0	29.4
0°-40°	1917.0	47.2
0°-60°	3266.8	80.4
0°-90°	4064.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4064.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1597	1597	1597	1597	1597	
5°	1597	1591	1574	1587	1584	152
15°	1521	1511	1491	1498	1490	428
25°	1376	1364	1338	1341	1338	633
35°	1187	1172	1147	1138	1130	741
45°	966	955	932	915	909	746
55°	731	722	704	685	677	654
65°	493	484	468	455	447	487
75°	258	255	247	238	241	275
85°	63	61	60	55	54	74
90°	0	0	0	0	0	

TEST NUMBER: P1036900

CATALOG NUMBER: S122DS-B1005DB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1597.4	1597.4	1597.4	1597.4	1597.4
2.5°	1606.6	1598.9	1582.0	1597.4	1594.3
5°	1597.4	1591.2	1574.3	1586.6	1583.6
7.5°	1586.6	1577.4	1560.5	1572.8	1569.7
10°	1569.7	1559.0	1540.6	1552.8	1548.2
12.5°	1546.7	1537.5	1519.1	1526.7	1523.7
15°	1520.6	1511.4	1491.4	1497.5	1489.9
17.5°	1488.3	1479.1	1459.1	1466.8	1459.1
20°	1453.0	1443.8	1422.3	1426.9	1420.8
22.5°	1417.7	1403.9	1383.9	1383.9	1380.8
25°	1376.2	1363.9	1337.8	1340.9	1337.8
27.5°	1330.1	1319.4	1299.4	1294.8	1287.1
30°	1284.1	1271.8	1248.7	1244.1	1238.0
32.5°	1234.9	1225.7	1201.1	1191.9	1185.8
35°	1187.3	1171.9	1147.4	1138.1	1130.5
37.5°	1133.5	1119.7	1095.1	1084.4	1076.7
40°	1078.2	1065.9	1041.4	1027.5	1021.4
42.5°	1024.5	1012.2	987.6	972.3	963.0
45°	966.1	955.4	932.3	915.4	909.3
47.5°	909.3	898.5	874.0	857.1	847.8
50°	849.4	841.7	820.2	798.7	791.0
52.5°	791.0	780.3	760.3	743.4	732.6
55°	731.1	721.9	703.5	685.0	677.4
57.5°	671.2	663.5	643.6	625.1	619.0
60°	611.3	605.2	583.7	566.8	562.2
62.5°	552.9	542.2	526.8	511.5	505.3
65°	493.0	483.8	468.5	454.6	447.0
67.5°	431.6	423.9	410.1	399.3	393.2
70°	374.8	368.6	354.8	344.1	337.9
72.5°	316.4	310.3	302.6	291.8	287.2
75°	258.0	255.0	247.3	238.1	241.1
77.5°	205.8	199.7	196.6	192.0	187.4
80°	153.6	152.1	149.0	144.4	141.3
82.5°	104.4	104.4	102.9	96.8	96.8
85°	63.0	61.4	59.9	55.3	53.8
87.5°	27.6	24.6	21.5	16.9	15.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)