

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930213

Luminaire Tested: DFN2DS-HX3F0-070DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930213
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-070DS935-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5959.8 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 73.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930213

CATALOG NUMBER: DFN2DS-HX3F0-070DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930213

CATALOG NUMBER: DFN2DS-HX3F0-070DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2713	2713	2713
5°	2724	2685	2700
10°	2708	2657	2671
15°	2674	2623	2620
20°	2626	2571	2568
25°	2579	2508	2508
30°	2519	2449	2428
35°	2462	2379	2344
40°	2391	2309	2265
45°	2321	2240	2184
50°	2244	2167	2090
55°	2165	2084	2006
60°	2077	1983	1910
65°	1982	1883	1797
70°	1861	1762	1678
75°	1693	1622	1583
80°	1503	1457	1382
85°	1227	1170	1049

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2321 cd/sqm

TEST NUMBER: P930213

CATALOG NUMBER: DFN2DS-HX3F0-070DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.5	3.7
10°-20°	620.3	10.4
20°-30°	911.6	15.3
30°-40°	1058.8	17.8
40°-50°	1057.5	17.7
50°-60°	922.1	15.5
60°-70°	681.6	11.4
70°-80°	385.7	6.5
80°-90°	101.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1752.4	29.4
0°-40°	2811.2	47.2
0°-60°	4790.7	80.4
0°-90°	5959.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5959.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2342	2342	2342	2342	2342	
5°	2342	2334	2309	2327	2322	222
15°	2230	2216	2187	2196	2185	628
25°	2018	2000	1962	1966	1962	929
35°	1741	1719	1683	1669	1658	1087
45°	1417	1401	1367	1342	1333	1093
55°	1072	1059	1032	1005	993	959
65°	723	710	687	667	656	715
75°	378	374	362	349	354	404
85°	92	90	88	81	79	108
90°	0	0	0	0	0	

TEST NUMBER: P930213

CATALOG NUMBER: DFN2DS-HX3F0-070DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2342.4	2342.4	2342.4	2342.4	2342.4
2.5°	2356.1	2344.8	2319.9	2342.4	2338.1
5°	2342.4	2333.6	2308.8	2326.6	2322.3
7.5°	2326.6	2313.2	2288.4	2306.6	2302.0
10°	2302.0	2286.2	2259.2	2277.2	2270.5
12.5°	2268.1	2254.7	2227.7	2238.9	2234.4
15°	2229.9	2216.5	2187.1	2196.2	2184.9
17.5°	2182.5	2169.2	2139.8	2151.0	2139.8
20°	2130.6	2117.3	2085.8	2092.5	2083.6
22.5°	2079.0	2058.8	2029.3	2029.3	2024.8
25°	2018.2	2000.2	1962.0	1966.3	1962.0
27.5°	1950.5	1934.7	1905.6	1898.9	1887.6
30°	1883.1	1864.9	1831.3	1824.6	1815.5
32.5°	1810.9	1797.6	1761.5	1747.9	1738.7
35°	1741.2	1718.7	1682.6	1669.0	1657.7
37.5°	1662.3	1642.0	1605.9	1590.1	1578.9
40°	1581.3	1563.1	1527.0	1507.0	1497.9
42.5°	1502.4	1484.3	1448.4	1425.7	1412.3
45°	1416.8	1401.1	1367.1	1342.5	1333.4
47.5°	1333.4	1317.7	1281.6	1256.7	1243.4
50°	1245.5	1234.3	1202.7	1171.2	1160.0
52.5°	1160.0	1144.2	1115.1	1090.2	1074.4
55°	1072.2	1058.7	1031.7	1004.7	993.4
57.5°	984.4	973.1	943.7	916.7	907.6
60°	896.4	887.5	856.0	831.2	824.5
62.5°	810.8	795.1	772.6	750.2	741.1
65°	723.2	709.5	687.1	666.8	655.5
67.5°	633.0	621.6	601.5	585.7	576.6
70°	549.6	540.6	520.2	504.5	495.6
72.5°	464.1	455.0	443.8	428.0	421.3
75°	378.3	374.0	362.5	349.2	353.7
77.5°	301.9	292.7	288.2	281.5	274.9
80°	225.3	223.0	218.4	211.7	207.2
82.5°	153.2	153.2	151.0	142.0	142.0
85°	92.3	90.1	88.0	81.0	78.9
87.5°	40.6	36.1	31.6	24.9	22.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930213

CATALOG NUMBER: DFN2DS-HX3F0-070DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.75	16.36	15.12	16.68	16.99	14.31	15.92	14.67	16.23	16.55
	3H	16.50	17.96	16.88	18.28	18.64	16.01	17.46	16.39	17.79	18.15
	4H	17.15	18.52	17.55	18.86	19.24	16.65	18.02	17.05	18.37	18.75
	6H	17.62	18.88	18.03	19.25	19.64	17.11	18.38	17.53	18.75	19.14
	8H	17.76	18.97	18.18	19.36	19.76	17.26	18.47	17.68	18.86	19.26
	12H	17.85	19.01	18.28	19.39	19.82	17.34	18.50	17.77	18.88	19.31
4H	2H	15.31	16.68	15.71	17.03	17.40	14.96	16.33	15.36	16.68	17.05
	3H	17.29	18.43	17.70	18.83	19.23	16.88	18.03	17.29	18.42	18.82
	4H	18.06	19.10	18.49	19.51	19.95	17.64	18.67	18.07	19.09	19.52
	6H	18.66	19.56	19.11	20.00	20.46	18.23	19.13	18.68	19.57	20.03
	8H	18.85	19.70	19.31	20.14	20.60	18.41	19.26	18.87	19.70	20.17
	12H	18.98	19.74	19.46	20.22	20.69	18.53	19.29	19.01	19.76	20.23
8H	4H	18.34	19.18	18.80	19.63	20.09	17.96	18.81	18.42	19.25	19.72
	6H	19.05	19.75	19.54	20.24	20.72	18.67	19.37	19.16	19.86	20.34
	8H	19.31	19.94	19.82	20.45	20.93	18.92	19.55	19.43	20.06	20.54
	12H	19.51	20.07	20.02	20.56	21.12	19.10	19.65	19.60	20.14	20.71
12H	4H	18.36	19.12	18.84	19.60	20.07	18.00	18.76	18.48	19.23	19.70
	6H	19.10	19.73	19.61	20.23	20.72	18.73	19.36	19.24	19.87	20.35
	8H	19.41	19.97	19.92	20.46	21.02	19.03	19.59	19.54	20.08	20.64