

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930231

Luminaire Tested: DFN2DS-HX3F0-080DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930231
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-080DS935-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6811.2 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 84.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930231

CATALOG NUMBER: DFN2DS-HX3F0-080DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930231

CATALOG NUMBER: DFN2DS-HX3F0-080DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3101	3101	3101
5°	3113	3068	3086
10°	3095	3037	3052
15°	3056	2997	2995
20°	3002	2938	2935
25°	2948	2866	2866
30°	2879	2799	2775
35°	2814	2719	2679
40°	2733	2639	2588
45°	2653	2559	2497
50°	2565	2477	2389
55°	2475	2381	2293
60°	2373	2266	2183
65°	2265	2152	2053
70°	2127	2014	1918
75°	1935	1854	1809
80°	1718	1666	1580
85°	1401	1336	1197

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2653 cd/sqm

TEST NUMBER: P930231

CATALOG NUMBER: DFN2DS-HX3F0-080DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.0	3.7
10°-20°	708.9	10.4
20°-30°	1041.8	15.3
30°-40°	1210.0	17.8
40°-50°	1208.5	17.7
50°-60°	1053.8	15.5
60°-70°	779.0	11.4
70°-80°	440.7	6.5
80°-90°	116.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2002.7	29.4
0°-40°	3212.8	47.2
0°-60°	5475.1	80.4
0°-90°	6811.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6811.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2677	2677	2677	2677	2677	
5°	2677	2667	2639	2659	2654	254
15°	2548	2533	2500	2510	2497	718
25°	2306	2286	2242	2247	2242	1061
35°	1990	1964	1923	1907	1895	1243
45°	1619	1601	1562	1534	1524	1250
55°	1225	1210	1179	1148	1135	1096
65°	826	811	785	762	749	817
75°	432	427	414	399	404	462
85°	105	103	100	93	90	124
90°	0	0	0	0	0	

TEST NUMBER: P930231

CATALOG NUMBER: DFN2DS-HX3F0-080DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2677.0	2677.0	2677.0	2677.0	2677.0
2.5°	2692.6	2679.8	2651.4	2677.0	2672.1
5°	2677.0	2666.9	2638.6	2659.0	2654.1
7.5°	2659.0	2643.7	2615.3	2636.1	2630.9
10°	2630.9	2612.9	2582.0	2602.4	2594.9
12.5°	2592.1	2576.8	2545.9	2558.8	2553.6
15°	2548.4	2533.1	2499.5	2509.9	2497.1
17.5°	2494.3	2479.0	2445.4	2458.3	2445.4
20°	2435.1	2419.8	2383.7	2391.4	2381.3
22.5°	2376.1	2352.9	2319.2	2319.2	2314.1
25°	2306.4	2286.0	2242.3	2247.2	2242.3
27.5°	2229.1	2211.1	2177.8	2170.1	2157.3
30°	2152.2	2131.3	2092.9	2085.2	2074.8
32.5°	2069.7	2054.4	2013.1	1997.5	1987.2
35°	1989.9	1964.2	1923.0	1907.4	1894.6
37.5°	1899.7	1876.5	1835.3	1817.3	1804.5
40°	1807.2	1786.4	1745.2	1722.2	1711.8
42.5°	1717.1	1696.3	1655.3	1629.4	1614.1
45°	1619.3	1601.2	1562.4	1534.3	1524.0
47.5°	1524.0	1505.9	1464.7	1436.3	1421.0
50°	1423.5	1410.7	1374.5	1338.5	1325.7
52.5°	1325.7	1307.6	1274.3	1246.0	1227.9
55°	1225.4	1209.8	1179.1	1148.2	1135.3
57.5°	1125.0	1112.2	1078.5	1047.7	1037.2
60°	1024.4	1014.4	978.2	949.9	942.2
62.5°	926.6	908.7	883.0	857.3	846.9
65°	826.5	810.9	785.2	762.0	749.1
67.5°	723.4	710.4	687.4	669.4	659.0
70°	628.1	617.7	594.6	576.5	566.4
72.5°	530.4	520.0	507.1	489.2	481.5
75°	432.3	427.4	414.3	399.0	404.2
77.5°	344.9	334.5	329.4	321.7	314.1
80°	257.6	254.8	249.7	242.0	236.8
82.5°	175.1	175.1	172.6	162.2	162.2
85°	105.4	102.9	100.5	92.6	90.1
87.5°	46.4	41.3	36.0	28.4	25.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930231

CATALOG NUMBER: DFN2DS-HX3F0-080DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.22	16.83	15.58	17.14	17.45	14.77	16.38	15.14	16.70	17.01
	3H	16.96	18.42	17.34	18.75	19.11	16.47	17.93	16.85	18.25	18.62
	4H	17.61	18.98	18.01	19.33	19.70	17.12	18.49	17.51	18.83	19.21
	6H	18.08	19.35	18.49	19.71	20.10	17.58	18.85	17.99	19.21	19.60
	8H	18.22	19.43	18.65	19.82	20.22	17.72	18.93	18.14	19.32	19.72
	12H	18.31	19.47	18.74	19.86	20.28	17.80	18.96	18.23	19.34	19.77
4H	2H	15.78	17.14	16.17	17.49	17.87	15.42	16.79	15.82	17.14	17.52
	3H	17.75	18.90	18.16	19.29	19.69	17.34	18.49	17.75	18.89	19.29
	4H	18.53	19.56	18.96	19.98	20.41	18.10	19.14	18.53	19.55	19.99
	6H	19.12	20.03	19.58	20.47	20.92	18.69	19.60	19.15	20.04	20.49
	8H	19.31	20.16	19.77	20.60	21.07	18.87	19.72	19.34	20.16	20.63
	12H	19.44	20.20	19.92	20.68	21.15	18.99	19.75	19.47	20.23	20.70
8H	4H	18.80	19.65	19.26	20.09	20.55	18.43	19.27	18.89	19.71	20.18
	6H	19.51	20.22	20.01	20.71	21.18	19.13	19.84	19.63	20.32	20.80
	8H	19.77	20.40	20.28	20.91	21.40	19.38	20.01	19.89	20.52	21.01
	12H	19.97	20.53	20.48	21.02	21.58	19.56	20.12	20.07	20.61	21.17
12H	4H	18.83	19.59	19.31	20.06	20.53	18.46	19.22	18.94	19.70	20.17
	6H	19.56	20.19	20.07	20.70	21.18	19.19	19.82	19.70	20.33	20.82
	8H	19.87	20.43	20.38	20.92	21.48	19.50	20.05	20.00	20.54	21.11