

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930146

Luminaire Tested: DFN2DS-HX3F0-030DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930146
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-030DS950-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2409.7 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 28.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930146

CATALOG NUMBER: DFN2DS-HX3F0-030DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930146

CATALOG NUMBER: DFN2DS-HX3F0-030DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1357	1357	1357
5°	1362	1340	1348
10°	1352	1318	1307
15°	1336	1279	1242
20°	1315	1223	1162
25°	1293	1160	1084
30°	1262	1095	984
35°	1233	1024	897
40°	1203	951	795
45°	1167	869	703
50°	1131	785	613
55°	1094	696	527
60°	1051	602	437
65°	1003	506	398
70°	945	416	366
75°	873	380	342
80°	771	339	312
85°	605	267	267

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1167 cd/sqm

TEST NUMBER: P930146

CATALOG NUMBER: DFN2DS-HX3F0-030DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.8	4.6
10°-20°	301.5	12.5
20°-30°	423.2	17.6
30°-40°	461.4	19.1
40°-50°	424.0	17.6
50°-60°	333.0	13.8
60°-70°	216.8	9.0
70°-80°	111.6	4.6
80°-90°	28.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	834.5	34.6
0°-40°	1295.9	53.8
0°-60°	2052.9	85.2
0°-90°	2409.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2409.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1172	1172	1172	1172	1172	
5°	1172	1166	1153	1162	1159	111
15°	1114	1103	1067	1047	1036	314
25°	1012	978	908	864	848	465
35°	872	818	724	657	634	546
45°	713	642	530	455	429	550
55°	542	459	344	281	261	484
65°	366	280	184	148	145	363
75°	195	121	85	77	76	206
85°	46	23	20	20	20	55
90°	0	0	0	0	0	

TEST NUMBER: P930146

CATALOG NUMBER: DFN2DS-HX3F0-030DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1171.7	1171.7	1171.7	1171.7	1171.7
2.5°	1177.0	1171.7	1160.0	1170.7	1168.6
5°	1171.7	1166.4	1152.6	1162.2	1158.9
7.5°	1162.2	1155.8	1141.0	1145.2	1139.9
10°	1149.4	1142.0	1120.9	1117.6	1111.3
12.5°	1133.5	1124.0	1095.3	1089.0	1077.3
15°	1114.4	1102.7	1066.7	1046.6	1036.0
17.5°	1092.1	1075.2	1030.6	1007.4	990.4
20°	1066.7	1045.5	992.4	966.1	942.6
22.5°	1039.2	1014.7	953.2	917.2	901.3
25°	1011.6	977.6	907.7	864.2	848.2
27.5°	978.7	942.6	865.2	815.4	791.0
30°	943.8	903.4	818.6	764.6	735.9
32.5°	909.8	861.0	774.1	710.5	683.9
35°	871.7	817.5	724.2	657.4	634.1
37.5°	834.5	776.1	677.6	604.3	578.0
40°	795.3	731.7	628.8	553.5	526.0
42.5°	755.0	687.2	580.0	501.5	475.1
45°	712.6	641.5	530.2	454.8	429.4
47.5°	672.3	597.1	482.5	407.1	383.9
50°	627.8	552.4	435.8	362.6	340.4
52.5°	584.2	504.7	391.3	321.3	301.2
55°	541.8	459.1	344.5	281.0	260.9
57.5°	498.4	413.5	303.3	243.9	226.9
60°	453.8	369.0	259.8	205.7	188.8
62.5°	410.4	325.6	222.6	171.8	163.4
65°	365.8	279.9	184.5	148.5	145.2
67.5°	323.5	237.5	148.5	130.4	127.2
70°	278.9	196.2	122.9	112.4	108.1
72.5°	236.4	157.9	102.8	94.4	92.2
75°	195.0	120.9	84.9	77.4	76.4
77.5°	153.8	85.8	66.8	62.6	60.4
80°	115.6	61.5	50.8	46.7	46.7
82.5°	80.5	41.4	35.0	32.9	32.9
85°	45.5	23.2	20.1	20.1	20.1
87.5°	17.0	8.4	8.4	7.5	7.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930146

CATALOG NUMBER: DFN2DS-HX3F0-030DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.30	13.82	12.66	14.13	14.45	8.26	9.78	8.62	10.09	10.41
	3H	14.06	15.43	14.44	15.75	16.12	9.52	10.89	9.90	11.21	11.58
	4H	14.73	16.01	15.13	16.36	16.74	10.02	11.30	10.42	11.65	12.03
	6H	15.22	16.40	15.63	16.77	17.16	10.40	11.59	10.82	11.95	12.35
	8H	15.38	16.51	15.81	16.90	17.30	10.53	11.66	10.96	12.05	12.45
	12H	15.48	16.56	15.91	16.94	17.37	10.61	11.69	11.04	12.07	12.50
4H	2H	12.40	13.68	12.80	14.03	14.41	8.95	10.23	9.35	10.58	10.96
	3H	14.33	15.40	14.74	15.80	16.20	10.39	11.46	10.81	11.86	12.26
	4H	15.08	16.04	15.52	16.45	16.89	10.99	11.95	11.43	12.37	12.81
	6H	15.67	16.51	16.13	16.95	17.41	11.48	12.31	11.94	12.76	13.22
	8H	15.89	16.67	16.35	17.11	17.58	11.65	12.42	12.11	12.87	13.33
	12H	16.04	16.74	16.52	17.21	17.69	11.76	12.46	12.24	12.94	13.41
8H	4H	15.11	15.88	15.57	16.33	16.80	11.35	12.13	11.81	12.57	13.04
	6H	15.74	16.39	16.24	16.88	17.36	11.94	12.58	12.43	13.07	13.55
	8H	15.99	16.57	16.51	17.08	17.57	12.16	12.73	12.67	13.24	13.73
	12H	16.20	16.71	16.71	17.20	17.76	12.34	12.85	12.85	13.34	13.90
12H	4H	15.09	15.79	15.57	16.26	16.74	11.39	12.09	11.87	12.56	13.04
	6H	15.72	16.30	16.24	16.81	17.30	12.00	12.58	12.51	13.09	13.57
	8H	16.01	16.52	16.52	17.01	17.58	12.27	12.78	12.78	13.27	13.84

END OF REPORT