

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930236

Luminaire Tested: DFN2DS-HX3F0-080DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-080DS950-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6426.0 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 84.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930236

CATALOG NUMBER: DFN2DS-HX3F0-080DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930236

CATALOG NUMBER: DFN2DS-HX3F0-080DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3619	3619	3619
5°	3633	3574	3594
10°	3605	3516	3486
15°	3564	3411	3313
20°	3507	3263	3099
25°	3448	3094	2891
30°	3366	2920	2625
35°	3287	2731	2391
40°	3207	2535	2121
45°	3113	2316	1876
50°	3017	2095	1636
55°	2918	1856	1405
60°	2804	1605	1166
65°	2674	1349	1062
70°	2519	1111	976
75°	2328	1012	912
80°	2055	905	830
85°	1615	714	714

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3113 cd/sqm

TEST NUMBER: P930236

CATALOG NUMBER: DFN2DS-HX3F0-080DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.8	4.6
10°-20°	803.9	12.5
20°-30°	1128.6	17.6
30°-40°	1230.3	19.1
40°-50°	1130.8	17.6
50°-60°	888.0	13.8
60°-70°	578.0	9.0
70°-80°	297.5	4.6
80°-90°	76.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2225.4	34.6
0°-40°	3455.7	53.8
0°-60°	5474.5	85.2
0°-90°	6426.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6426.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3124	3124	3124	3124	3124	
5°	3124	3110	3074	3099	3091	296
15°	2972	2941	2845	2791	2763	837
25°	2698	2607	2420	2305	2262	1241
35°	2324	2180	1931	1753	1691	1455
45°	1900	1711	1414	1213	1145	1467
55°	1445	1224	919	749	696	1291
65°	976	746	492	396	387	967
75°	520	322	226	206	204	550
85°	122	62	54	54	54	146
90°	0	0	0	0	0	

TEST NUMBER: P930236

CATALOG NUMBER: DFN2DS-HX3F0-080DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3124.5	3124.5	3124.5	3124.5	3124.5
2.5°	3138.6	3124.5	3093.4	3121.8	3116.1
5°	3124.5	3110.5	3073.5	3099.0	3090.6
7.5°	3099.0	3082.2	3042.6	3053.8	3039.6
10°	3065.1	3045.4	2988.9	2980.2	2963.4
12.5°	3022.9	2997.4	2920.8	2904.0	2872.8
15°	2971.8	2940.7	2844.6	2791.0	2762.7
17.5°	2912.4	2867.1	2748.3	2686.3	2640.9
20°	2844.6	2787.9	2646.7	2576.2	2513.7
22.5°	2771.1	2706.0	2542.0	2445.9	2403.6
25°	2697.6	2607.1	2420.4	2304.7	2262.0
27.5°	2610.0	2513.7	2307.3	2174.4	2109.3
30°	2516.7	2409.0	2182.9	2038.8	1962.3
32.5°	2426.1	2296.0	2064.4	1894.5	1823.8
35°	2324.4	2180.1	1931.4	1753.3	1690.8
37.5°	2225.4	2069.7	1806.9	1611.6	1541.1
40°	2120.8	1951.2	1676.7	1476.0	1402.5
42.5°	2013.3	1832.4	1546.8	1337.5	1266.9
45°	1900.2	1710.6	1413.9	1212.9	1145.2
47.5°	1792.9	1592.1	1286.7	1085.7	1023.6
50°	1674.0	1473.3	1162.3	966.9	907.8
52.5°	1557.9	1345.8	1043.4	856.8	803.2
55°	1444.8	1224.3	918.9	749.4	695.7
57.5°	1329.0	1102.8	808.8	650.4	605.1
60°	1210.2	984.0	692.7	548.7	503.4
62.5°	1094.4	868.2	593.7	458.1	435.6
65°	975.6	746.4	492.0	396.0	387.3
67.5°	862.5	633.3	396.0	347.7	339.3
70°	743.7	523.2	327.9	299.7	288.3
72.5°	630.6	421.2	274.2	251.7	246.0
75°	520.2	322.2	226.2	206.4	203.7
77.5°	410.1	228.9	178.2	166.8	161.1
80°	308.1	164.1	135.6	124.5	124.5
82.5°	214.8	110.4	93.3	87.6	87.6
85°	121.5	62.1	53.7	53.7	53.7
87.5°	45.3	22.5	22.5	19.8	19.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930236

CATALOG NUMBER: DFN2DS-HX3F0-080DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.70	17.23	16.07	17.54	17.85	11.66	13.19	12.03	13.50	13.81
	3H	17.47	18.83	17.85	19.16	19.52	12.93	14.29	13.31	14.62	14.98
	4H	18.14	19.42	18.53	19.76	20.14	13.43	14.71	13.83	15.06	15.44
	6H	18.62	19.81	19.04	20.17	20.57	13.81	14.99	14.22	15.36	15.75
	8H	18.79	19.92	19.22	20.31	20.71	13.94	15.06	14.36	15.45	15.85
	12H	18.89	19.97	19.32	20.35	20.78	14.02	15.10	14.45	15.48	15.91
4H	2H	15.81	17.09	16.21	17.44	17.82	12.36	13.64	12.76	13.99	14.37
	3H	17.74	18.80	18.15	19.20	19.60	13.80	14.87	14.21	15.27	15.67
	4H	18.49	19.45	18.92	19.86	20.30	14.40	15.36	14.83	15.77	16.21
	6H	19.08	19.91	19.54	20.36	20.82	14.89	15.72	15.35	16.17	16.62
	8H	19.30	20.07	19.76	20.52	20.99	15.05	15.83	15.52	16.27	16.74
	12H	19.45	20.14	19.93	20.62	21.09	15.17	15.86	15.65	16.34	16.81
8H	4H	18.51	19.29	18.98	19.74	20.20	14.76	15.53	15.22	15.98	16.44
	6H	19.15	19.79	19.65	20.29	20.76	15.34	15.99	15.84	16.48	16.95
	8H	19.40	19.98	19.92	20.49	20.98	15.56	16.14	16.08	16.65	17.14
	12H	19.61	20.12	20.12	20.61	21.17	15.74	16.25	16.25	16.74	17.31
12H	4H	18.50	19.19	18.98	19.67	20.14	14.80	15.49	15.28	15.97	16.44
	6H	19.13	19.71	19.65	20.22	20.71	15.41	15.98	15.92	16.49	16.98
	8H	19.42	19.93	19.93	20.42	20.98	15.68	16.19	16.19	16.68	17.25