

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930402

Luminaire Tested: DFN2DS-HX4F0-120DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930402
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-120DS835-RLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10200.0 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 131
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930402

CATALOG NUMBER: DFN2DS-HX4F0-120DS835-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930402

CATALOG NUMBER: DFN2DS-HX4F0-120DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3688	3688	3688
5°	3702	3641	3662
10°	3673	3582	3552
15°	3631	3476	3376
20°	3573	3324	3157
25°	3513	3152	2946
30°	3430	2975	2674
35°	3349	2783	2436
40°	3267	2583	2161
45°	3172	2360	1911
50°	3074	2134	1667
55°	2973	1891	1432
60°	2857	1635	1188
65°	2725	1374	1082
70°	2566	1132	995
75°	2372	1032	929
80°	2094	921	846
85°	1646	727	727

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3172 cd/sqm

TEST NUMBER: P930402

CATALOG NUMBER: DFN2DS-HX4F0-120DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	464.8	4.6
10°-20°	1276.0	12.5
20°-30°	1791.5	17.6
30°-40°	1952.8	19.1
40°-50°	1794.9	17.6
50°-60°	1409.6	13.8
60°-70°	917.5	9.0
70°-80°	472.3	4.6
80°-90°	120.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3532.3	34.6
0°-40°	5485.2	53.8
0°-60°	8689.6	85.2
0°-90°	10200.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10200.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4960	4960	4960	4960	4960	
5°	4960	4937	4879	4919	4906	470
15°	4717	4668	4515	4430	4385	1329
25°	4282	4138	3842	3658	3590	1969
35°	3690	3460	3066	2783	2684	2309
45°	3016	2715	2244	1925	1818	2329
55°	2293	1943	1459	1190	1104	2049
65°	1549	1185	781	629	615	1535
75°	826	511	359	328	323	873
85°	193	99	85	85	85	231
90°	0	0	0	0	0	

TEST NUMBER: P930402

CATALOG NUMBER: DFN2DS-HX4F0-120DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4959.6	4959.6	4959.6	4959.6	4959.6
2.5°	4982.0	4959.6	4910.1	4955.3	4946.2
5°	4959.6	4937.2	4878.6	4919.1	4905.8
7.5°	4919.1	4892.4	4829.6	4847.2	4824.8
10°	4865.3	4833.9	4744.3	4730.5	4703.9
12.5°	4798.1	4757.7	4636.2	4609.6	4560.1
15°	4717.2	4667.7	4515.3	4430.0	4385.3
17.5°	4622.9	4551.0	4362.4	4263.9	4192.0
20°	4515.3	4425.3	4201.0	4089.1	3990.0
22.5°	4398.6	4295.3	4034.8	3882.4	3815.3
25°	4282.0	4138.1	3841.9	3658.1	3590.5
27.5°	4142.9	3990.0	3662.4	3451.5	3348.1
30°	3994.8	3823.9	3464.8	3236.2	3114.8
32.5°	3851.0	3644.3	3276.7	3007.2	2894.8
35°	3689.6	3460.5	3065.7	2782.9	2683.8
37.5°	3532.4	3285.3	2868.1	2558.1	2446.2
40°	3366.2	3097.2	2661.5	2342.9	2226.2
42.5°	3195.7	2908.6	2455.3	2122.9	2011.0
45°	3016.2	2715.3	2244.3	1925.3	1817.6
47.5°	2845.7	2527.2	2042.4	1723.4	1624.8
50°	2657.2	2338.6	1844.8	1534.8	1441.0
52.5°	2472.9	2136.2	1656.2	1360.0	1274.8
55°	2293.4	1943.4	1458.6	1189.5	1104.3
57.5°	2109.5	1750.5	1283.8	1032.4	960.5
60°	1921.0	1561.9	1099.5	871.0	799.1
62.5°	1737.2	1378.1	942.4	727.2	691.4
65°	1548.6	1184.8	781.0	628.6	614.8
67.5°	1369.1	1005.2	628.6	551.9	538.6
70°	1180.5	830.5	520.5	475.7	457.6
72.5°	1001.0	668.6	435.2	399.5	390.5
75°	825.7	511.4	359.1	327.6	323.3
77.5°	651.0	363.3	282.9	264.8	255.7
80°	489.1	260.5	215.2	197.6	197.6
82.5°	341.0	175.2	148.1	139.0	139.0
85°	192.9	98.6	85.2	85.2	85.2
87.5°	71.9	35.7	35.7	31.4	31.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930402

CATALOG NUMBER: DFN2DS-HX4F0-120DS835-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.77	17.29	16.13	17.60	17.92	11.73	13.25	12.09	13.56	13.88
	3H	17.53	18.90	17.91	19.23	19.59	12.99	14.36	13.37	14.69	15.05
	4H	18.20	19.48	18.60	19.83	20.21	13.50	14.78	13.90	15.13	15.50
	6H	18.69	19.87	19.10	20.24	20.63	13.88	15.06	14.29	15.43	15.82
	8H	18.85	19.98	19.28	20.37	20.77	14.00	15.13	14.43	15.52	15.92
	12H	18.96	20.04	19.39	20.42	20.85	14.08	15.16	14.51	15.54	15.97
4H	2H	15.87	17.15	16.27	17.50	17.88	12.43	13.71	12.82	14.05	14.43
	3H	17.81	18.87	18.22	19.27	19.67	13.87	14.93	14.28	15.33	15.73
	4H	18.56	19.51	18.99	19.93	20.37	14.47	15.42	14.90	15.84	16.28
	6H	19.15	19.98	19.60	20.42	20.88	14.96	15.79	15.41	16.23	16.69
	8H	19.36	20.14	19.83	20.58	21.05	15.12	15.89	15.58	16.34	16.81
	12H	19.52	20.21	20.00	20.69	21.16	15.23	15.93	15.72	16.41	16.88
8H	4H	18.58	19.36	19.04	19.80	20.27	14.82	15.60	15.28	16.04	16.51
	6H	19.22	19.86	19.71	20.35	20.83	15.41	16.05	15.90	16.54	17.02
	8H	19.47	20.04	19.98	20.55	21.04	15.63	16.21	16.14	16.72	17.20
	12H	19.67	20.18	20.18	20.67	21.24	15.81	16.32	16.32	16.81	17.37
12H	4H	18.56	19.26	19.05	19.74	20.21	14.86	15.56	15.35	16.04	16.51
	6H	19.20	19.78	19.71	20.29	20.77	15.47	16.05	15.98	16.56	17.05
	8H	19.48	19.99	19.99	20.48	21.05	15.74	16.25	16.25	16.75	17.31