

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930332

Luminaire Tested: DFN2DS-HX4F0-080DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930332
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-080DS840-RLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6806.8 lumens
Efficiency: N/A
Efficacy: 83.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930332

CATALOG NUMBER: DFN2DS-HX4F0-080DS840-RLL

Luminous Intensity Polar Plot



CATALOG NUMBER: DFN2DS-HX4F0-080DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86		
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	74		
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	64		
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	55		
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43		
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39		
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2461	2461	2461
5°	2470	2430	2444
10°	2451	2391	2370
15°	2423	2320	2253
20°	2384	2218	2107
25°	2344	2104	1966
30°	2289	1985	1785
35°	2235	1857	1626
40°	2180	1724	1442
45°	2117	1575	1276
50°	2051	1424	1112
55°	1984	1262	955
60°	1906	1091	793
65°	1818	917	722
70°	1713	755	664
75°	1583	688	620
80°	1397	615	564
85°	1098	485	485

MAXIMUM LUMINANCE 45°-90°:

Luminance: 2117 cd/sqm

TEST NUMBER: P930332

CATALOG NUMBER: DFN2DS-HX4F0-080DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	310.2	4.6
10°-20°	851.5	12.5
20°-30°	1195.5	17.6
30°-40°	1303.2	19.1
40°-50°	1197.8	17.6
50°-60°	940.7	13.8
60°-70°	612.3	9.0
70°-80°	315.2	4.6
80°-90°	80.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2357.2	34.6
0°-40°	3660.4	53.8
0°-60°	5798.9	85.2
0°-90°	6806.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6806.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3310	3310	3310	3310	3310	
5°	3310	3295	3256	3283	3274	314
15°	3148	3115	3013	2956	2926	887
25°	2858	2762	2564	2441	2396	1314
35°	2462	2309	2046	1857	1791	1541
45°	2013	1812	1498	1285	1213	1554
55°	1530	1297	973	794	737	1368
65°	1033	791	521	420	410	1025
75°	551	341	240	219	216	583
85°	129	66	57	57	57	154
90°	0	0	0	0	0	

TEST NUMBER: P930332

CATALOG NUMBER: DFN2DS-HX4F0-080DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3309.7	3309.7	3309.7	3309.7	3309.7
2.5°	3324.6	3309.7	3276.7	3306.8	3300.8
5°	3309.7	3294.8	3255.7	3282.7	3273.8
7.5°	3282.7	3264.9	3222.9	3234.7	3219.7
10°	3246.7	3225.8	3166.1	3156.9	3139.0
12.5°	3202.0	3175.0	3093.9	3076.1	3043.0
15°	3147.9	3114.9	3013.2	2956.4	2926.4
17.5°	3085.0	3037.0	2911.2	2845.4	2797.4
20°	3013.2	2953.2	2803.5	2728.8	2662.7
22.5°	2935.3	2866.4	2692.6	2590.9	2546.0
25°	2857.5	2761.6	2563.9	2441.2	2396.1
27.5°	2764.7	2662.7	2444.0	2303.3	2234.3
30°	2665.9	2551.7	2312.2	2159.7	2078.6
32.5°	2569.9	2432.0	2186.7	2006.8	1931.8
35°	2462.2	2309.3	2045.8	1857.2	1791.0
37.5°	2357.3	2192.4	1914.0	1707.1	1632.4
40°	2246.4	2066.9	1776.1	1563.5	1485.6
42.5°	2132.6	1941.0	1638.4	1416.7	1341.9
45°	2012.8	1812.0	1497.7	1284.8	1213.0
47.5°	1899.1	1686.5	1363.0	1150.0	1084.3
50°	1773.2	1560.7	1231.1	1024.2	961.6
52.5°	1650.2	1425.5	1105.2	907.6	850.7
55°	1530.4	1296.9	973.4	793.8	736.9
57.5°	1407.8	1168.2	856.8	689.0	640.9
60°	1281.9	1042.3	733.7	581.2	533.2
62.5°	1159.3	919.6	628.9	485.3	461.5
65°	1033.4	790.6	521.1	419.5	410.2
67.5°	913.6	670.9	419.5	368.3	359.5
70°	787.8	554.3	347.3	317.4	305.4
72.5°	668.0	446.1	290.5	266.7	260.6
75°	551.1	341.3	239.6	218.6	215.8
77.5°	434.4	242.4	188.8	176.7	170.7
80°	326.3	173.9	143.6	131.8	131.8
82.5°	227.5	116.9	98.8	92.8	92.8
85°	128.7	65.8	56.9	56.9	56.9
87.5°	47.9	23.8	23.8	21.0	21.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930332

CATALOG NUMBER: DFN2DS-HX4F0-080DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.36	15.89	14.73	16.20	16.51	10.32	11.85	10.69	12.16	12.47
	3H	16.13	17.49	16.51	17.82	18.18	11.59	12.95	11.97	13.28	13.64
	4H	16.80	18.08	17.20	18.42	18.80	12.09	13.37	12.49	13.72	14.10
	6H	17.28	18.47	17.70	18.83	19.23	12.47	13.66	12.88	14.02	14.41
	8H	17.45	18.58	17.88	18.97	19.37	12.60	13.72	13.02	14.11	14.51
	12H	17.55	18.63	17.98	19.01	19.44	12.68	13.76	13.11	14.14	14.57
4H	2H	14.47	15.75	14.87	16.10	16.48	11.02	12.30	11.42	12.65	13.03
	3H	16.40	17.46	16.81	17.86	18.26	12.46	13.53	12.87	13.93	14.33
	4H	17.15	18.11	17.58	18.52	18.96	13.06	14.02	13.49	14.43	14.87
	6H	17.74	18.57	18.20	19.02	19.48	13.55	14.38	14.01	14.82	15.28
	8H	17.96	18.73	18.42	19.18	19.65	13.71	14.49	14.18	14.93	15.40
	12H	18.11	18.80	18.59	19.28	19.75	13.83	14.52	14.31	15.00	15.47
8H	4H	17.17	17.95	17.64	18.40	18.86	13.42	14.19	13.88	14.64	15.10
	6H	17.81	18.45	18.31	18.95	19.42	14.00	14.64	14.50	15.14	15.61
	8H	18.06	18.64	18.58	19.15	19.64	14.22	14.80	14.74	15.31	15.80
	12H	18.27	18.78	18.78	19.27	19.83	14.40	14.91	14.91	15.40	15.97
12H	4H	17.16	17.85	17.64	18.33	18.80	13.46	14.15	13.94	14.63	15.10
	6H	17.79	18.37	18.31	18.88	19.37	14.07	14.64	14.58	15.15	15.64
	8H	18.08	18.59	18.59	19.08	19.64	14.34	14.85	14.85	15.34	15.91