

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930333

Luminaire Tested: DFN2DS-HX4F0-080DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930333
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-080DS850-FLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8783.3 lumens
Efficiency: N/A
Efficacy: 107.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930333

CATALOG NUMBER: DFN2DS-HX4F0-080DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930333

CATALOG NUMBER: DFN2DS-HX4F0-080DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2567	2567	2567
5°	2577	2540	2555
10°	2562	2514	2526
15°	2530	2481	2479
20°	2485	2432	2430
25°	2440	2372	2372
30°	2383	2317	2297
35°	2329	2251	2218
40°	2262	2184	2143
45°	2196	2119	2067
50°	2123	2050	1978
55°	2049	1971	1898
60°	1964	1876	1807
65°	1875	1781	1700
70°	1761	1667	1588
75°	1602	1535	1497
80°	1422	1378	1307
85°	1160	1106	991

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2196 cd/sqm

TEST NUMBER: P930333

CATALOG NUMBER: DFN2DS-HX4F0-080DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	324.9	3.7
10°-20°	914.2	10.4
20°-30°	1343.5	15.3
30°-40°	1560.4	17.8
40°-50°	1558.4	17.7
50°-60°	1358.9	15.5
60°-70°	1004.5	11.4
70°-80°	568.4	6.5
80°-90°	150.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2582.6	29.4
0°-40°	4143.0	47.2
0°-60°	7060.4	80.4
0°-90°	8783.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8783.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3452	3452	3452	3452	3452	
5°	3452	3439	3402	3429	3423	328
15°	3286	3267	3223	3237	3220	926
25°	2974	2948	2892	2898	2892	1369
35°	2566	2533	2480	2460	2443	1602
45°	2088	2065	2015	1979	1965	1612
55°	1580	1560	1520	1481	1464	1413
65°	1066	1046	1012	983	966	1054
75°	558	551	534	515	521	595
85°	136	133	130	119	116	160
90°	0	0	0	0	0	

TEST NUMBER: P930333

CATALOG NUMBER: DFN2DS-HX4F0-080DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3452.1	3452.1	3452.1	3452.1	3452.1
2.5°	3472.2	3455.6	3419.0	3452.1	3445.8
5°	3452.1	3439.1	3402.5	3428.9	3422.6
7.5°	3428.9	3409.2	3372.6	3399.3	3392.7
10°	3392.7	3369.4	3329.6	3355.9	3346.2
12.5°	3342.6	3322.9	3283.1	3299.6	3293.0
15°	3286.3	3266.6	3223.2	3236.6	3220.1
17.5°	3216.5	3196.8	3153.4	3170.1	3153.4
20°	3140.1	3120.4	3073.9	3083.8	3070.7
22.5°	3064.1	3034.1	2990.8	2990.8	2984.1
25°	2974.2	2947.8	2891.5	2897.8	2891.5
27.5°	2874.5	2851.3	2808.3	2798.5	2781.9
30°	2775.3	2748.4	2698.9	2689.0	2675.6
32.5°	2668.9	2649.2	2595.9	2575.9	2562.6
35°	2566.0	2533.0	2479.7	2459.7	2443.1
37.5°	2449.8	2419.8	2366.7	2343.4	2326.9
40°	2330.5	2303.6	2250.5	2220.9	2207.5
42.5°	2214.2	2187.4	2134.6	2101.1	2081.5
45°	2088.1	2064.8	2014.8	1978.6	1965.3
47.5°	1965.3	1942.0	1888.7	1852.1	1832.4
50°	1835.6	1819.1	1772.5	1726.0	1709.5
52.5°	1709.5	1686.2	1643.3	1606.7	1583.4
55°	1580.2	1560.1	1520.4	1480.6	1464.0
57.5°	1450.7	1434.2	1390.8	1351.0	1337.6
60°	1321.0	1308.1	1261.5	1224.9	1215.0
62.5°	1194.9	1171.8	1138.6	1105.6	1092.1
65°	1065.7	1045.7	1012.5	982.6	966.0
67.5°	932.9	916.0	886.4	863.2	849.8
70°	810.0	796.6	766.8	743.5	730.4
72.5°	683.9	670.6	654.0	630.8	620.9
75°	557.5	551.2	534.3	514.6	521.2
77.5°	444.8	431.4	424.7	414.9	405.0
80°	332.1	328.6	321.9	312.1	305.3
82.5°	225.8	225.8	222.6	209.2	209.2
85°	136.0	132.7	129.6	119.4	116.2
87.5°	59.9	53.2	46.5	36.6	33.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930333

CATALOG NUMBER: DFN2DS-HX4F0-080DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.56	16.17	14.92	16.48	16.80	14.11	15.72	14.48	16.04	16.35
	3H	16.31	17.76	16.68	18.09	18.45	15.82	17.27	16.19	17.60	17.96
	4H	16.95	18.32	17.35	18.67	19.05	16.46	17.83	16.86	18.18	18.55
	6H	17.42	18.69	17.83	19.06	19.45	16.92	18.19	17.33	18.56	18.95
	8H	17.57	18.78	17.99	19.17	19.57	17.06	18.27	17.49	18.66	19.06
	12H	17.66	18.82	18.09	19.20	19.63	17.14	18.30	17.57	18.69	19.11
4H	2H	15.12	16.49	15.52	16.84	17.21	14.77	16.13	15.16	16.48	16.86
	3H	17.09	18.24	17.50	18.64	19.04	16.69	17.83	17.10	18.23	18.63
	4H	17.87	18.91	18.30	19.32	19.76	17.45	18.48	17.88	18.90	19.33
	6H	18.47	19.37	18.92	19.81	20.27	18.03	18.94	18.49	19.38	19.84
	8H	18.66	19.50	19.12	19.94	20.41	18.22	19.06	18.68	19.51	19.97
	12H	18.79	19.55	19.27	20.02	20.49	18.34	19.10	18.82	19.57	20.04
8H	4H	18.14	18.99	18.60	19.43	19.90	17.77	18.62	18.23	19.06	19.52
	6H	18.86	19.56	19.35	20.05	20.52	18.48	19.18	18.97	19.67	20.14
	8H	19.12	19.75	19.63	20.25	20.74	18.73	19.36	19.23	19.86	20.35
	12H	19.32	19.87	19.82	20.37	20.93	18.90	19.46	19.41	19.95	20.51
12H	4H	18.17	18.93	18.65	19.40	19.87	17.80	18.56	18.28	19.04	19.51
	6H	18.90	19.53	19.41	20.04	20.53	18.53	19.17	19.04	19.67	20.16
	8H	19.22	19.77	19.72	20.27	20.83	18.84	19.40	19.35	19.89	20.45