

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930334

Luminaire Tested: DFN2DS-HX4F0-080DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930334
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-080DS850-RLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7541.2 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930334

CATALOG NUMBER: DFN2DS-HX4F0-080DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930334

CATALOG NUMBER: DFN2DS-HX4F0-080DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2727	2727	2727
5°	2737	2692	2707
10°	2716	2648	2626
15°	2685	2570	2496
20°	2642	2458	2334
25°	2597	2330	2178
30°	2536	2199	1977
35°	2476	2057	1801
40°	2416	1910	1598
45°	2345	1745	1413
50°	2272	1578	1232
55°	2198	1398	1058
60°	2112	1209	879
65°	2014	1016	800
70°	1897	837	736
75°	1754	763	687
80°	1548	681	626
85°	1217	537	537

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2345 cd/sqm

TEST NUMBER: P930334

CATALOG NUMBER: DFN2DS-HX4F0-080DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.7	4.6
10°-20°	943.4	12.5
20°-30°	1324.5	17.6
30°-40°	1443.8	19.1
40°-50°	1327.0	17.6
50°-60°	1042.1	13.8
60°-70°	678.3	9.0
70°-80°	349.2	4.6
80°-90°	89.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2611.6	34.6
0°-40°	4055.4	53.8
0°-60°	6424.5	85.2
0°-90°	7541.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7541.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3650	3607	3637	3627	348
15°	3488	3451	3338	3275	3242	983
25°	3166	3060	2840	2705	2655	1456
35°	2728	2558	2267	2058	1984	1707
45°	2230	2008	1659	1423	1344	1722
55°	1696	1437	1078	879	816	1515
65°	1145	876	577	465	454	1135
75°	610	378	266	242	239	646
85°	143	73	63	63	63	171
90°	0	0	0	0	0	

TEST NUMBER: P930334

CATALOG NUMBER: DFN2DS-HX4F0-080DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3666.8	3666.8	3666.8	3666.8	3666.8
2.5°	3683.3	3666.8	3630.2	3663.6	3656.9
5°	3666.8	3650.3	3606.9	3636.9	3627.0
7.5°	3636.9	3617.1	3570.6	3583.7	3567.1
10°	3597.0	3573.9	3507.7	3497.5	3477.7
12.5°	3547.5	3517.5	3427.7	3408.0	3371.4
15°	3487.6	3451.0	3338.3	3275.3	3242.2
17.5°	3417.8	3364.7	3225.3	3152.4	3099.2
20°	3338.3	3271.8	3106.0	3023.2	2949.9
22.5°	3252.0	3175.6	2983.1	2870.4	2820.7
25°	3165.8	3059.5	2840.5	2704.6	2654.6
27.5°	3062.9	2949.9	2707.7	2551.8	2475.4
30°	2953.5	2827.1	2561.7	2392.7	2302.8
32.5°	2847.1	2694.4	2422.6	2223.3	2140.3
35°	2727.8	2558.5	2266.6	2057.5	1984.2
37.5°	2611.6	2428.9	2120.5	1891.3	1808.6
40°	2488.8	2289.9	1967.7	1732.1	1645.9
42.5°	2362.7	2150.5	1815.2	1569.6	1486.7
45°	2230.0	2007.5	1659.3	1423.4	1343.9
47.5°	2104.0	1868.4	1510.0	1274.1	1201.3
50°	1964.5	1729.0	1364.0	1134.7	1065.3
52.5°	1828.3	1579.3	1224.4	1005.5	942.5
55°	1695.6	1436.8	1078.4	879.4	816.4
57.5°	1559.7	1294.2	949.2	763.3	710.1
60°	1420.2	1154.8	812.9	643.9	590.8
62.5°	1284.3	1018.8	696.8	537.6	511.2
65°	1144.9	875.9	577.3	464.8	454.5
67.5°	1012.2	743.3	464.8	408.0	398.2
70°	872.8	614.1	384.8	351.7	338.4
72.5°	740.0	494.3	321.8	295.4	288.7
75°	610.5	378.2	265.5	242.2	239.1
77.5°	481.3	268.6	209.2	195.7	189.1
80°	361.5	192.6	159.1	146.1	146.1
82.5°	252.1	129.5	109.5	102.8	102.8
85°	142.6	72.9	63.0	63.0	63.0
87.5°	53.1	26.4	26.4	23.3	23.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930334

CATALOG NUMBER: DFN2DS-HX4F0-080DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.72	16.24	15.08	16.55	16.87	10.68	12.20	11.05	12.52	12.83
	3H	16.49	17.85	16.86	18.18	18.54	11.95	13.31	12.32	13.64	14.00
	4H	17.15	18.43	17.55	18.78	19.16	12.45	13.73	12.85	14.08	14.45
	6H	17.64	18.82	18.05	19.19	19.58	12.83	14.01	13.24	14.38	14.77
	8H	17.81	18.93	18.23	19.32	19.72	12.95	14.08	13.38	14.47	14.87
	12H	17.91	18.99	18.34	19.37	19.80	13.03	14.11	13.46	14.49	14.92
4H	2H	14.82	16.10	15.22	16.45	16.83	11.38	12.66	11.78	13.00	13.38
	3H	16.76	17.82	17.17	18.22	18.62	12.82	13.88	13.23	14.28	14.68
	4H	17.51	18.46	17.94	18.88	19.32	13.42	14.37	13.85	14.79	15.23
	6H	18.10	18.93	18.56	19.37	19.83	13.91	14.74	14.36	15.18	15.64
	8H	18.31	19.09	18.78	19.53	20.00	14.07	14.85	14.53	15.29	15.76
	12H	18.47	19.16	18.95	19.64	20.11	14.19	14.88	14.67	15.36	15.83
8H	4H	17.53	18.31	17.99	18.75	19.22	13.77	14.55	14.24	14.99	15.46
	6H	18.17	18.81	18.66	19.30	19.78	14.36	15.00	14.86	15.49	15.97
	8H	18.42	18.99	18.93	19.50	19.99	14.58	15.16	15.09	15.67	16.15
	12H	18.62	19.13	19.13	19.62	20.19	14.76	15.27	15.27	15.76	16.33
12H	4H	17.52	18.21	18.00	18.69	19.16	13.82	14.51	14.30	14.99	15.46
	6H	18.15	18.73	18.66	19.24	19.72	14.42	15.00	14.94	15.51	16.00
	8H	18.43	18.94	18.94	19.44	20.00	14.70	15.20	15.20	15.70	16.26