

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929839

Luminaire Tested: DFN2DS-4P2F0-040DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929839
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P2F0-040DS950-FLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3742.2 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.07' x L: 2.07' x H: 0')
CIE Type: Direct

Input Watts (W): 43.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929839

CATALOG NUMBER: DFN2DS-4P2F0-040DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929839

CATALOG NUMBER: DFN2DS-4P2F0-040DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3683	3683	3683
5°	3697	3644	3665
10°	3675	3607	3625
15°	3630	3560	3557
20°	3565	3490	3486
25°	3501	3404	3404
30°	3419	3325	3296
35°	3342	3230	3182
40°	3246	3134	3075
45°	3150	3040	2965
50°	3047	2942	2837
55°	2939	2828	2723
60°	2818	2692	2593
65°	2691	2556	2439
70°	2527	2392	2278
75°	2299	2203	2149
80°	2040	1977	1876
85°	1663	1586	1422

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3150 cd/sqm

TEST NUMBER: P929839

CATALOG NUMBER: DFN2DS-4P2F0-040DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.4	3.7
10°-20°	389.5	10.4
20°-30°	572.4	15.3
30°-40°	664.8	17.8
40°-50°	664.0	17.7
50°-60°	579.0	15.5
60°-70°	428.0	11.4
70°-80°	242.2	6.5
80°-90°	63.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1100.3	29.4
0°-40°	1765.2	47.2
0°-60°	3008.1	80.4
0°-90°	3742.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3742.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1471	1471	1471	1471	1471	
5°	1471	1465	1450	1461	1458	140
15°	1400	1392	1373	1379	1372	394
25°	1267	1256	1232	1235	1232	583
35°	1093	1079	1056	1048	1041	683
45°	890	880	858	843	837	687
55°	673	665	648	631	624	602
65°	454	446	431	419	412	449
75°	238	235	228	219	222	254
85°	58	57	55	51	50	68
90°	0	0	0	0	0	

TEST NUMBER: P929839

CATALOG NUMBER: DFN2DS-4P2F0-040DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1470.8	1470.8	1470.8	1470.8	1470.8
2.5°	1479.4	1472.3	1456.7	1470.8	1468.2
5°	1470.8	1465.2	1449.6	1460.9	1458.2
7.5°	1460.9	1452.5	1436.9	1448.3	1445.5
10°	1445.5	1435.5	1418.6	1429.9	1425.6
12.5°	1424.1	1415.7	1398.8	1405.9	1402.9
15°	1400.1	1391.7	1373.3	1378.9	1372.0
17.5°	1370.4	1362.0	1343.6	1350.6	1343.6
20°	1337.8	1329.4	1309.7	1313.8	1308.4
22.5°	1305.4	1292.7	1274.2	1274.2	1271.4
25°	1267.2	1255.9	1231.9	1234.6	1231.9
27.5°	1224.7	1214.8	1196.6	1192.3	1185.3
30°	1182.4	1171.0	1149.9	1145.6	1140.0
32.5°	1137.1	1128.7	1106.0	1097.5	1091.8
35°	1093.3	1079.2	1056.5	1048.0	1040.9
37.5°	1043.8	1031.0	1008.3	998.5	991.4
40°	992.9	981.5	958.8	946.2	940.6
42.5°	943.4	932.0	909.5	895.2	886.8
45°	889.6	879.8	858.4	843.0	837.3
47.5°	837.3	827.3	804.8	789.2	780.8
50°	782.1	775.0	755.2	735.4	728.3
52.5°	728.3	718.5	700.2	684.6	674.6
55°	673.3	664.7	647.8	630.8	623.8
57.5°	618.0	611.0	592.5	575.6	569.9
60°	562.8	557.3	537.5	521.9	517.7
62.5°	509.2	499.2	485.2	471.0	465.3
65°	454.1	445.5	431.4	418.6	411.6
67.5°	397.5	390.3	377.7	367.8	362.1
70°	345.1	339.4	326.7	316.8	311.2
72.5°	291.4	285.7	278.7	268.8	264.5
75°	237.6	234.8	227.7	219.2	222.1
77.5°	189.5	183.8	181.0	176.7	172.6
80°	141.5	140.0	137.1	133.0	130.1
82.5°	96.2	96.2	94.9	89.1	89.1
85°	57.9	56.6	55.2	50.8	49.5
87.5°	25.5	22.7	19.8	15.6	14.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929839

CATALOG NUMBER: DFN2DS-4P2F0-040DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.81	17.42	16.18	17.74	18.05	15.37	16.98	15.73	17.29	17.61
	3H	17.56	19.02	17.94	19.34	19.70	17.07	18.53	17.45	18.85	19.21
	4H	18.21	19.58	18.61	19.93	20.30	17.71	19.08	18.11	19.43	19.81
	6H	18.68	19.95	19.09	20.31	20.70	18.18	19.44	18.59	19.81	20.20
	8H	18.82	20.03	19.25	20.42	20.82	18.32	19.53	18.74	19.92	20.32
	12H	18.91	20.07	19.34	20.45	20.88	18.40	19.56	18.83	19.94	20.37
4H	2H	16.37	17.74	16.77	18.09	18.47	16.02	17.39	16.42	17.74	18.11
	3H	18.35	19.49	18.76	19.89	20.29	17.94	19.09	18.35	19.49	19.89
	4H	19.12	20.16	19.56	20.57	21.01	18.70	19.74	19.13	20.15	20.59
	6H	19.72	20.63	20.17	21.07	21.52	19.29	20.19	19.74	20.63	21.09
	8H	19.91	20.76	20.37	21.20	21.66	19.47	20.32	19.93	20.76	21.23
	12H	20.04	20.80	20.52	21.28	21.75	19.59	20.35	20.07	20.83	21.29
8H	4H	19.40	20.24	19.86	20.69	21.15	19.02	19.87	19.48	20.31	20.78
	6H	20.11	20.81	20.61	21.30	21.78	19.73	20.43	20.22	20.92	21.40
	8H	20.37	21.00	20.88	21.51	21.99	19.98	20.61	20.49	21.12	21.60
	12H	20.57	21.13	21.08	21.62	22.18	20.16	20.72	20.66	21.21	21.77
12H	4H	19.42	20.18	19.90	20.66	21.13	19.06	19.82	19.54	20.29	20.76
	6H	20.16	20.79	20.67	21.30	21.78	19.79	20.42	20.30	20.93	21.41
	8H	20.47	21.03	20.98	21.52	22.08	20.09	20.65	20.60	21.14	21.70