

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929913

Luminaire Tested: DFN2DS-4P3F0-060DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929913
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-060DS830-FLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5595.4 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 65
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929913

CATALOG NUMBER: DFN2DS-4P3F0-060DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929913

CATALOG NUMBER: DFN2DS-4P3F0-060DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2506	2506	2506
5°	2516	2480	2494
10°	2501	2454	2467
15°	2470	2423	2420
20°	2426	2375	2372
25°	2382	2316	2316
30°	2326	2262	2243
35°	2274	2198	2165
40°	2209	2133	2092
45°	2144	2069	2018
50°	2073	2002	1931
55°	2000	1924	1853
60°	1918	1832	1764
65°	1831	1740	1659
70°	1719	1627	1550
75°	1564	1498	1462
80°	1389	1346	1276
85°	1132	1079	968

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2144 cd/sqm

TEST NUMBER: P929913

CATALOG NUMBER: DFN2DS-4P3F0-060DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.0	3.7
10°-20°	582.4	10.4
20°-30°	855.9	15.3
30°-40°	994.1	17.8
40°-50°	992.8	17.7
50°-60°	865.7	15.5
60°-70°	639.9	11.4
70°-80°	362.1	6.5
80°-90°	95.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1645.3	29.4
0°-40°	2639.3	47.2
0°-60°	4497.9	80.4
0°-90°	5595.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5595.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2199	2199	2199	2199	2199	
5°	2199	2191	2168	2184	2180	209
15°	2094	2081	2053	2062	2051	590
25°	1895	1878	1842	1846	1842	872
35°	1635	1614	1580	1567	1556	1021
45°	1330	1315	1284	1260	1252	1027
55°	1007	994	969	943	933	900
65°	679	666	645	626	615	671
75°	355	351	340	328	332	379
85°	87	85	82	76	74	102
90°	0	0	0	0	0	

TEST NUMBER: P929913

CATALOG NUMBER: DFN2DS-4P3F0-060DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2199.2	2199.2	2199.2	2199.2	2199.2
2.5°	2212.0	2201.5	2178.1	2199.2	2195.1
5°	2199.2	2190.9	2167.5	2184.4	2180.4
7.5°	2184.4	2171.9	2148.5	2165.6	2161.3
10°	2161.3	2146.5	2121.1	2138.0	2131.7
12.5°	2129.5	2116.9	2091.5	2102.1	2097.8
15°	2093.5	2081.0	2053.4	2061.9	2051.4
17.5°	2049.1	2036.6	2009.0	2019.5	2009.0
20°	2000.4	1987.9	1958.2	1964.5	1956.3
22.5°	1952.0	1932.9	1905.3	1905.3	1901.1
25°	1894.7	1878.0	1842.0	1846.0	1842.0
27.5°	1831.2	1816.5	1789.0	1782.8	1772.3
30°	1768.0	1750.9	1719.3	1713.0	1704.5
32.5°	1700.2	1687.7	1653.8	1641.0	1632.5
35°	1634.7	1613.6	1579.7	1566.9	1556.4
37.5°	1560.7	1541.6	1507.8	1492.9	1482.3
40°	1484.6	1467.5	1433.7	1414.9	1406.3
42.5°	1410.6	1393.5	1359.9	1338.6	1326.0
45°	1330.3	1315.4	1283.6	1260.5	1251.9
47.5°	1251.9	1237.1	1203.3	1179.9	1167.3
50°	1169.4	1158.8	1129.3	1099.6	1089.0
52.5°	1089.0	1074.3	1046.8	1023.6	1008.8
55°	1006.7	993.9	968.6	943.2	932.7
57.5°	924.2	913.6	886.0	860.7	852.1
60°	841.6	833.3	803.7	780.4	774.0
62.5°	761.2	746.4	725.3	704.2	695.8
65°	678.9	666.2	645.1	626.0	615.4
67.5°	594.3	583.6	564.7	549.9	541.4
70°	516.0	507.5	488.4	473.6	465.3
72.5°	435.7	427.2	416.6	401.9	395.5
75°	355.1	351.2	340.3	327.8	332.1
77.5°	283.4	274.9	270.5	264.3	258.0
80°	211.6	209.3	205.1	198.8	194.5
82.5°	143.8	143.8	141.8	133.3	133.3
85°	86.6	84.6	82.5	76.0	74.0
87.5°	38.2	33.9	29.6	23.4	21.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929913

CATALOG NUMBER: DFN2DS-4P3F0-060DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.47	16.09	14.84	16.40	16.71	14.03	15.64	14.40	15.96	16.27
	3H	16.22	17.68	16.60	18.01	18.37	15.73	17.19	16.11	17.51	17.88
	4H	16.87	18.24	17.27	18.59	18.96	16.38	17.75	16.77	18.09	18.47
	6H	17.34	18.61	17.75	18.97	19.36	16.84	18.11	17.25	18.47	18.86
	8H	17.48	18.69	17.91	19.08	19.48	16.98	18.19	17.41	18.58	18.98
	12H	17.57	18.73	18.00	19.12	19.54	17.06	18.22	17.49	18.60	19.03
4H	2H	15.04	16.40	15.43	16.75	17.13	14.68	16.05	15.08	16.40	16.78
	3H	17.01	18.16	17.42	18.55	18.95	16.60	17.75	17.01	18.15	18.55
	4H	17.79	18.82	18.22	19.24	19.67	17.36	18.40	17.79	18.81	19.25
	6H	18.38	19.29	18.84	19.73	20.19	17.95	18.86	18.41	19.30	19.75
	8H	18.57	19.42	19.03	19.86	20.33	18.13	18.98	18.60	19.42	19.89
	12H	18.70	19.46	19.18	19.94	20.41	18.25	19.01	18.73	19.49	19.96
8H	4H	18.06	18.91	18.52	19.35	19.81	17.69	18.53	18.15	18.97	19.44
	6H	18.77	19.48	19.27	19.97	20.44	18.39	19.10	18.89	19.58	20.06
	8H	19.03	19.66	19.54	20.17	20.66	18.64	19.27	19.15	19.78	20.27
	12H	19.23	19.79	19.74	20.28	20.84	18.82	19.38	19.33	19.87	20.43
12H	4H	18.09	18.85	18.57	19.32	19.79	17.72	18.48	18.20	18.96	19.43
	6H	18.82	19.45	19.33	19.96	20.44	18.45	19.08	18.96	19.59	20.08
	8H	19.13	19.69	19.64	20.18	20.74	18.76	19.31	19.26	19.80	20.37