

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929879

Luminaire Tested: DFN2DS-4P3F0-040DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929879
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-040DS835-FLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3960.0 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 40.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929879

CATALOG NUMBER: DFN2DS-4P3F0-040DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929879

CATALOG NUMBER: DFN2DS-4P3F0-040DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1774	1774	1774
5°	1780	1755	1765
10°	1770	1737	1746
15°	1748	1714	1713
20°	1717	1681	1679
25°	1686	1639	1639
30°	1646	1601	1587
35°	1609	1555	1532
40°	1563	1509	1481
45°	1517	1464	1428
50°	1467	1417	1366
55°	1416	1362	1312
60°	1357	1296	1249
65°	1296	1231	1175
70°	1217	1152	1097
75°	1107	1061	1035
80°	982	952	904
85°	802	764	685

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1517 cd/sqm

TEST NUMBER: P929879

CATALOG NUMBER: DFN2DS-4P3F0-040DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.5	3.7
10°-20°	412.2	10.4
20°-30°	605.7	15.3
30°-40°	703.5	17.8
40°-50°	702.6	17.7
50°-60°	612.7	15.5
60°-70°	452.9	11.4
70°-80°	256.2	6.5
80°-90°	67.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1164.4	29.4
0°-40°	1867.9	47.2
0°-60°	3183.2	80.4
0°-90°	3960.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3960.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1556	1556	1556	1556	1556	
5°	1556	1550	1534	1546	1543	148
15°	1482	1473	1453	1459	1452	417
25°	1341	1329	1304	1306	1304	617
35°	1157	1142	1118	1109	1102	722
45°	941	931	908	892	886	727
55°	712	703	686	668	660	637
65°	480	471	456	443	436	475
75°	251	248	241	232	235	268
85°	61	60	58	54	52	72
90°	0	0	0	0	0	

TEST NUMBER: P929879

CATALOG NUMBER: DFN2DS-4P3F0-040DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1556.4	1556.4	1556.4	1556.4	1556.4
2.5°	1565.5	1558.0	1541.5	1556.4	1553.6
5°	1556.4	1550.5	1534.0	1545.9	1543.1
7.5°	1545.9	1537.0	1520.5	1532.6	1529.6
10°	1529.6	1519.1	1501.2	1513.1	1508.6
12.5°	1507.0	1498.1	1480.2	1487.7	1484.6
15°	1481.6	1472.7	1453.2	1459.2	1451.8
17.5°	1450.2	1441.3	1421.8	1429.2	1421.8
20°	1415.7	1406.8	1385.9	1390.3	1384.5
22.5°	1381.4	1367.9	1348.4	1348.4	1345.4
25°	1340.9	1329.0	1303.6	1306.5	1303.6
27.5°	1296.0	1285.5	1266.2	1261.7	1254.3
30°	1251.2	1239.2	1216.8	1212.3	1206.3
32.5°	1203.3	1194.4	1170.4	1161.4	1155.3
35°	1156.9	1142.0	1118.0	1109.0	1101.5
37.5°	1104.5	1091.0	1067.0	1056.6	1049.1
40°	1050.7	1038.6	1014.6	1001.3	995.3
42.5°	998.3	986.2	962.4	947.3	938.4
45°	941.4	931.0	908.4	892.1	886.0
47.5°	886.0	875.5	851.6	835.1	826.2
50°	827.6	820.1	799.2	778.2	770.7
52.5°	770.7	760.3	740.9	724.4	713.9
55°	712.5	703.4	685.5	667.5	660.1
57.5°	654.0	646.6	627.0	609.1	603.1
60°	595.6	589.7	568.8	552.3	547.8
62.5°	538.8	528.3	513.4	498.4	492.4
65°	480.5	471.4	456.5	443.0	435.6
67.5°	420.6	413.0	399.7	389.2	383.2
70°	365.2	359.2	345.7	335.2	329.3
72.5°	308.4	302.3	294.9	284.4	279.9
75°	251.4	248.5	240.9	232.0	235.0
77.5°	200.5	194.5	191.5	187.0	182.6
80°	149.7	148.1	145.1	140.7	137.7
82.5°	101.8	101.8	100.4	94.3	94.3
85°	61.3	59.9	58.4	53.8	52.4
87.5°	27.0	24.0	21.0	16.5	14.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929879

CATALOG NUMBER: DFN2DS-4P3F0-040DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.27	14.88	13.64	15.20	15.51	12.83	14.44	13.19	14.75	15.07
	3H	15.02	16.48	15.40	16.80	17.17	14.53	15.99	14.91	16.31	16.67
	4H	15.67	17.04	16.07	17.39	17.76	15.18	16.54	15.57	16.89	17.27
	6H	16.14	17.41	16.55	17.77	18.16	15.64	16.91	16.05	17.27	17.66
	8H	16.28	17.49	16.71	17.88	18.28	15.78	16.99	16.20	17.38	17.78
	12H	16.37	17.53	16.80	17.91	18.34	15.86	17.02	16.29	17.40	17.83
4H	2H	13.83	15.20	14.23	15.55	15.93	13.48	14.85	13.88	15.20	15.57
	3H	15.81	16.96	16.22	17.35	17.75	15.40	16.55	15.81	16.95	17.35
	4H	16.59	17.62	17.02	18.04	18.47	16.16	17.20	16.59	17.61	18.05
	6H	17.18	18.09	17.64	18.53	18.98	16.75	17.65	17.20	18.10	18.55
	8H	17.37	18.22	17.83	18.66	19.13	16.93	17.78	17.39	18.22	18.69
	12H	17.50	18.26	17.98	18.74	19.21	17.05	17.81	17.53	18.29	18.76
8H	4H	16.86	17.71	17.32	18.15	18.61	16.48	17.33	16.95	17.77	18.24
	6H	17.57	18.28	18.07	18.76	19.24	17.19	17.89	17.69	18.38	18.86
	8H	17.83	18.46	18.34	18.97	19.46	17.44	18.07	17.95	18.58	19.06
	12H	18.03	18.59	18.54	19.08	19.64	17.62	18.18	18.13	18.67	19.23
12H	4H	16.89	17.65	17.37	18.12	18.59	16.52	17.28	17.00	17.76	18.23
	6H	17.62	18.25	18.13	18.76	19.24	17.25	17.88	17.76	18.39	18.87
	8H	17.93	18.49	18.44	18.98	19.54	17.55	18.11	18.06	18.60	19.16