

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930354

Luminaire Tested: DFN2DS-HX4F0-090DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930354
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-090DS927-RLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6058.8 lumens
Efficiency: N/A
Efficacy: 64.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 93.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930354

CATALOG NUMBER: DFN2DS-HX4F0-090DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930354

CATALOG NUMBER: DFN2DS-HX4F0-090DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2191	2191	2191
5°	2199	2163	2175
10°	2182	2128	2110
15°	2157	2065	2005
20°	2122	1975	1875
25°	2087	1872	1750
30°	2037	1767	1589
35°	1989	1653	1447
40°	1941	1535	1284
45°	1884	1402	1135
50°	1826	1268	990
55°	1766	1123	850
60°	1697	971	706
65°	1618	816	643
70°	1524	672	591
75°	1409	613	552
80°	1244	547	503
85°	977	432	432

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1884 cd/sqm

TEST NUMBER: P930354

CATALOG NUMBER: DFN2DS-HX4F0-090DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.1	4.6
10°-20°	758.0	12.5
20°-30°	1064.1	17.6
30°-40°	1160.0	19.1
40°-50°	1066.2	17.6
50°-60°	837.3	13.8
60°-70°	545.0	9.0
70°-80°	280.5	4.6
80°-90°	71.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2098.2	34.6
0°-40°	3258.2	53.8
0°-60°	5161.6	85.2
0°-90°	6058.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6058.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2946	2946	2946	2946	2946	
5°	2946	2933	2898	2922	2914	279
15°	2802	2773	2682	2631	2605	790
25°	2544	2458	2282	2173	2133	1170
35°	2192	2056	1821	1653	1594	1372
45°	1792	1613	1333	1144	1080	1384
55°	1362	1154	866	707	656	1217
65°	920	704	464	373	365	912
75°	490	304	213	195	192	519
85°	114	58	51	51	51	137
90°	0	0	0	0	0	

TEST NUMBER: P930354

CATALOG NUMBER: DFN2DS-HX4F0-090DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2946.0	2946.0	2946.0	2946.0	2946.0
2.5°	2959.3	2946.0	2916.5	2943.5	2938.1
5°	2946.0	2932.7	2897.9	2921.9	2914.0
7.5°	2921.9	2906.1	2868.8	2879.2	2865.9
10°	2890.0	2871.3	2818.2	2809.9	2794.1
12.5°	2850.1	2826.1	2753.9	2738.1	2708.6
15°	2802.0	2772.6	2682.1	2631.4	2604.9
17.5°	2746.0	2703.3	2591.3	2532.7	2490.0
20°	2682.1	2628.6	2495.4	2428.9	2370.1
22.5°	2612.8	2551.4	2396.7	2306.1	2266.3
25°	2543.5	2458.1	2282.1	2172.9	2132.8
27.5°	2460.9	2370.1	2175.5	2050.2	1988.8
30°	2372.9	2271.4	2058.1	1922.3	1850.2
32.5°	2287.5	2164.7	1946.3	1786.3	1719.5
35°	2191.6	2055.6	1821.0	1653.1	1594.2
37.5°	2098.2	1951.5	1703.7	1519.5	1453.1
40°	1999.6	1839.7	1580.9	1391.7	1322.4
42.5°	1898.3	1727.7	1458.4	1261.0	1194.5
45°	1791.7	1612.9	1333.1	1143.6	1079.7
47.5°	1690.4	1501.2	1213.2	1023.7	965.1
50°	1578.4	1389.1	1095.8	911.7	855.9
52.5°	1468.9	1268.9	983.8	807.8	757.2
55°	1362.2	1154.3	866.4	706.6	655.9
57.5°	1253.1	1039.8	762.6	613.2	570.6
60°	1141.0	927.7	653.2	517.3	474.6
62.5°	1031.9	818.6	559.8	432.0	410.7
65°	919.8	703.8	463.9	373.3	365.2
67.5°	813.2	597.1	373.3	327.8	319.9
70°	701.2	493.3	309.2	282.6	271.8
72.5°	594.6	397.1	258.5	237.3	232.0
75°	490.5	303.8	213.3	194.6	192.1
77.5°	386.7	215.8	168.0	157.3	151.9
80°	290.5	154.8	127.8	117.4	117.4
82.5°	202.5	104.1	88.0	82.6	82.6
85°	114.5	58.5	50.6	50.6	50.6
87.5°	42.7	21.2	21.2	18.7	18.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930354

CATALOG NUMBER: DFN2DS-HX4F0-090DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.96	15.48	14.32	15.79	16.11	9.92	11.44	10.28	11.75	12.07
	3H	15.72	17.09	16.10	17.42	17.78	11.18	12.55	11.56	12.88	13.24
	4H	16.39	17.67	16.79	18.02	18.40	11.69	12.97	12.09	13.32	13.69
	6H	16.88	18.06	17.29	18.43	18.82	12.07	13.25	12.48	13.62	14.01
	8H	17.04	18.17	17.47	18.56	18.96	12.19	13.32	12.62	13.71	14.11
	12H	17.15	18.23	17.58	18.61	19.04	12.27	13.35	12.70	13.73	14.16
4H	2H	14.06	15.34	14.46	15.69	16.07	10.62	11.90	11.01	12.24	12.62
	3H	16.00	17.06	16.41	17.46	17.86	12.06	13.12	12.47	13.52	13.92
	4H	16.75	17.70	17.18	18.12	18.56	12.66	13.61	13.09	14.03	14.47
	6H	17.34	18.17	17.79	18.61	19.07	13.15	13.98	13.60	14.42	14.88
	8H	17.55	18.33	18.02	18.77	19.24	13.31	14.09	13.77	14.53	15.00
	12H	17.71	18.40	18.19	18.88	19.35	13.43	14.12	13.91	14.60	15.07
8H	4H	16.77	17.55	17.23	17.99	18.46	13.01	13.79	13.47	14.23	14.70
	6H	17.41	18.05	17.90	18.54	19.02	13.60	14.24	14.09	14.73	15.21
	8H	17.66	18.23	18.17	18.74	19.23	13.82	14.40	14.33	14.91	15.39
	12H	17.86	18.37	18.37	18.86	19.43	14.00	14.51	14.51	15.00	15.56
12H	4H	16.75	17.45	17.24	17.93	18.40	13.05	13.75	13.54	14.23	14.70
	6H	17.39	17.97	17.90	18.48	18.96	13.66	14.24	14.18	14.75	15.24
	8H	17.67	18.18	18.18	18.67	19.24	13.93	14.44	14.44	14.94	15.50