

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929900

Luminaire Tested: DFN2DS-4P3F0-050DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929900
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-050DS840-RLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4254.3 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 51.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929900

CATALOG NUMBER: DFN2DS-4P3F0-050DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P929900

CATALOG NUMBER: DFN2DS-4P3F0-050DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86		
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	74		
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	64		
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	55		
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43		
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39		
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2357	2357	2357
5°	2366	2328	2341
10°	2348	2290	2270
15°	2321	2222	2158
20°	2284	2125	2018
25°	2246	2015	1883
30°	2193	1902	1709
35°	2141	1779	1557
40°	2089	1651	1381
45°	2028	1508	1222
50°	1965	1364	1066
55°	1901	1209	915
60°	1826	1045	759
65°	1741	878	692
70°	1641	723	636
75°	1516	659	594
80°	1339	589	541
85°	1053	464	464

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2028 cd/sqm

TEST NUMBER: P929900

CATALOG NUMBER: DFN2DS-4P3F0-050DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.9	4.6
10°-20°	532.2	12.5
20°-30°	747.2	17.6
30°-40°	814.5	19.1
40°-50°	748.6	17.6
50°-60°	587.9	13.8
60°-70°	382.7	9.0
70°-80°	197.0	4.6
80°-90°	50.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1473.3	34.6
0°-40°	2287.8	53.8
0°-60°	3624.3	85.2
0°-90°	4254.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4254.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2069	2069	2069	2069	2069	
5°	2069	2059	2035	2052	2046	196
15°	1968	1947	1883	1848	1829	554
25°	1786	1726	1602	1526	1498	821
35°	1539	1443	1279	1161	1119	963
45°	1258	1132	936	803	758	972
55°	957	810	608	496	461	855
65°	646	494	326	262	256	640
75°	344	213	150	137	135	364
85°	80	41	36	36	36	96
90°	0	0	0	0	0	

TEST NUMBER: P929900

CATALOG NUMBER: DFN2DS-4P3F0-050DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2068.6	2068.6	2068.6	2068.6	2068.6
2.5°	2077.9	2068.6	2047.9	2066.8	2063.0
5°	2068.6	2059.3	2034.8	2051.6	2046.1
7.5°	2051.6	2040.5	2014.3	2021.7	2012.3
10°	2029.2	2016.1	1978.8	1973.1	1961.9
12.5°	2001.2	1984.4	1933.7	1922.6	1901.9
15°	1967.5	1946.8	1883.3	1847.7	1829.0
17.5°	1928.1	1898.2	1819.5	1778.4	1748.3
20°	1883.3	1845.7	1752.2	1705.5	1664.2
22.5°	1834.6	1791.5	1682.9	1619.3	1591.3
25°	1785.9	1725.9	1602.4	1525.7	1497.5
27.5°	1727.9	1664.2	1527.5	1439.5	1396.5
30°	1666.2	1594.9	1445.1	1349.7	1299.1
32.5°	1606.2	1520.0	1366.7	1254.3	1207.4
35°	1538.8	1443.3	1278.7	1160.7	1119.4
37.5°	1473.3	1370.3	1196.3	1067.0	1020.3
40°	1404.0	1291.8	1110.0	977.2	928.5
42.5°	1332.9	1213.1	1024.0	885.4	838.7
45°	1258.1	1132.5	936.0	803.0	758.1
47.5°	1186.9	1054.1	851.9	718.8	677.7
50°	1108.3	975.4	769.5	640.1	601.0
52.5°	1031.4	891.0	690.8	567.3	531.7
55°	956.6	810.5	608.3	496.1	460.6
57.5°	879.9	730.1	535.4	430.6	400.6
60°	801.2	651.5	458.6	363.3	333.2
62.5°	724.5	574.8	393.1	303.3	288.4
65°	645.8	494.2	325.7	262.2	256.5
67.5°	571.0	419.3	262.2	230.2	224.6
70°	492.4	346.3	217.1	198.4	190.9
72.5°	417.5	278.9	181.6	166.7	162.9
75°	344.4	213.3	149.7	136.6	134.8
77.5°	271.5	151.6	118.0	110.4	106.6
80°	204.0	108.6	89.8	82.4	82.4
82.5°	142.2	73.1	61.8	58.0	58.0
85°	80.5	41.1	35.5	35.5	35.5
87.5°	30.0	14.9	14.9	13.1	13.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929900

CATALOG NUMBER: DFN2DS-4P3F0-050DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.21	15.74	14.58	16.05	16.36	10.17	11.70	10.54	12.01	12.32
	3H	15.98	17.34	16.36	17.67	18.03	11.44	12.81	11.82	13.13	13.49
	4H	16.65	17.93	17.05	18.28	18.65	11.94	13.22	12.34	13.57	13.95
	6H	17.13	18.32	17.55	18.68	19.08	12.32	13.50	12.73	13.87	14.26
	8H	17.30	18.43	17.73	18.82	19.22	12.45	13.57	12.87	13.96	14.36
	12H	17.40	18.48	17.83	18.86	19.29	12.53	13.61	12.96	13.99	14.42
4H	2H	14.32	15.60	14.72	15.95	16.33	10.87	12.15	11.27	12.50	12.88
	3H	16.25	17.31	16.66	17.71	18.12	12.31	13.38	12.72	13.78	14.18
	4H	17.00	17.96	17.43	18.37	18.81	12.91	13.87	13.34	14.28	14.72
	6H	17.59	18.42	18.05	18.87	19.33	13.40	14.23	13.86	14.67	15.13
	8H	17.81	18.58	18.27	19.03	19.50	13.56	14.34	14.03	14.78	15.25
	12H	17.96	18.66	18.44	19.13	19.60	13.68	14.37	14.16	14.85	15.32
8H	4H	17.02	17.80	17.49	18.25	18.71	13.27	14.04	13.73	14.49	14.96
	6H	17.66	18.31	18.16	18.80	19.27	13.85	14.50	14.35	14.99	15.46
	8H	17.91	18.49	18.43	19.00	19.49	14.07	14.65	14.59	15.16	15.65
	12H	18.12	18.63	18.63	19.12	19.68	14.25	14.76	14.76	15.25	15.82
12H	4H	17.01	17.70	17.49	18.18	18.65	13.31	14.00	13.79	14.48	14.95
	6H	17.64	18.22	18.16	18.73	19.22	13.92	14.49	14.43	15.00	15.49
	8H	17.93	18.44	18.44	18.93	19.49	14.19	14.70	14.70	15.19	15.76