

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929865

Luminaire Tested: DFN2DS-4P3F0-030DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929865
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-030DS850-FLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3293.8 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 28.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929865

CATALOG NUMBER: DFN2DS-4P3F0-030DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929865

CATALOG NUMBER: DFN2DS-4P3F0-030DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1475	1475	1475
5°	1481	1460	1468
10°	1472	1445	1452
15°	1454	1426	1425
20°	1428	1398	1396
25°	1402	1363	1363
30°	1369	1332	1320
35°	1339	1294	1274
40°	1300	1255	1232
45°	1262	1218	1188
50°	1220	1178	1137
55°	1177	1133	1091
60°	1129	1078	1039
65°	1078	1024	977
70°	1012	958	913
75°	920	882	861
80°	817	792	752
85°	667	635	570

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1262 cd/sqm

TEST NUMBER: P929865

CATALOG NUMBER: DFN2DS-4P3F0-030DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.8	3.7
10°-20°	342.8	10.4
20°-30°	503.8	15.3
30°-40°	585.2	17.8
40°-50°	584.4	17.7
50°-60°	509.6	15.5
60°-70°	376.7	11.4
70°-80°	213.1	6.5
80°-90°	56.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	968.5	29.4
0°-40°	1553.6	47.2
0°-60°	2647.7	80.4
0°-90°	3293.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3293.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1294	1294	1294	1294	1294	
5°	1294	1290	1276	1286	1283	123
15°	1232	1225	1209	1214	1208	347
25°	1115	1106	1084	1087	1084	513
35°	962	950	930	922	916	601
45°	783	774	756	742	737	604
55°	593	585	570	555	549	530
65°	400	392	380	368	362	395
75°	209	207	200	193	196	223
85°	51	50	49	45	44	60
90°	0	0	0	0	0	



TEST NUMBER: P929865

CATALOG NUMBER: DFN2DS-4P3F0-030DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1294.5	1294.5	1294.5	1294.5	1294.5
2.5°	1302.1	1295.9	1282.1	1294.5	1292.2
5°	1294.5	1289.7	1275.9	1285.9	1283.4
7.5°	1285.9	1278.5	1264.7	1274.8	1272.2
10°	1272.2	1263.5	1248.6	1258.5	1254.8
12.5°	1253.5	1246.1	1231.2	1237.3	1234.9
15°	1232.3	1225.0	1208.7	1213.7	1207.5
17.5°	1206.1	1198.8	1182.5	1188.7	1182.5
20°	1177.5	1170.1	1152.7	1156.4	1151.5
22.5°	1149.0	1137.8	1121.5	1121.5	1119.0
25°	1115.3	1105.5	1084.3	1086.7	1084.3
27.5°	1077.9	1069.2	1053.1	1049.4	1043.2
30°	1040.7	1030.7	1012.1	1008.3	1003.3
32.5°	1000.9	993.4	973.5	965.9	960.9
35°	962.3	949.9	929.9	922.4	916.1
37.5°	918.7	907.5	887.5	878.8	872.6
40°	873.9	863.9	843.9	832.9	827.9
42.5°	830.3	820.3	800.5	787.9	780.5
45°	783.1	774.3	755.6	741.9	736.9
47.5°	736.9	728.3	708.3	694.6	687.1
50°	688.4	682.1	664.7	647.3	641.1
52.5°	641.1	632.4	616.3	602.5	593.8
55°	592.6	585.1	570.1	555.3	549.1
57.5°	544.0	537.8	521.6	506.6	501.6
60°	495.4	490.5	473.1	459.3	455.7
62.5°	448.1	439.4	427.0	414.5	409.6
65°	399.7	392.1	379.7	368.5	362.3
67.5°	349.9	343.6	332.4	323.7	318.7
70°	303.8	298.8	287.6	278.8	273.9
72.5°	256.5	251.4	245.2	236.5	232.9
75°	209.0	206.7	200.4	193.0	195.5
77.5°	166.8	161.8	159.3	155.6	151.9
80°	124.5	123.2	120.7	117.0	114.6
82.5°	84.6	84.6	83.5	78.4	78.4
85°	51.0	49.8	48.6	44.8	43.6
87.5°	22.4	20.0	17.4	13.8	12.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929865

CATALOG NUMBER: DFN2DS-4P3F0-030DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.63	14.24	13.00	14.56	14.87	12.19	13.80	12.55	14.11	14.43
	3H	14.38	15.84	14.76	16.17	16.53	13.89	15.35	14.27	15.67	16.03
	4H	15.03	16.40	15.43	16.75	17.12	14.54	15.90	14.93	16.25	16.63
	6H	15.50	16.77	15.91	17.13	17.52	15.00	16.27	15.41	16.63	17.02
	8H	15.64	16.85	16.07	17.24	17.64	15.14	16.35	15.56	16.74	17.14
	12H	15.73	16.89	16.16	17.27	17.70	15.22	16.38	15.65	16.76	17.19
4H	2H	13.19	14.56	13.59	14.91	15.29	12.84	14.21	13.24	14.56	14.93
	3H	15.17	16.32	15.58	16.71	17.11	14.76	15.91	15.17	16.31	16.71
	4H	15.95	16.98	16.38	17.40	17.83	15.52	16.56	15.95	16.97	17.41
	6H	16.54	17.45	17.00	17.89	18.34	16.11	17.01	16.56	17.46	17.91
	8H	16.73	17.58	17.19	18.02	18.49	16.29	17.14	16.75	17.58	18.05
	12H	16.86	17.62	17.34	18.10	18.57	16.41	17.17	16.89	17.65	18.12
8H	4H	16.22	17.07	16.68	17.51	17.97	15.84	16.69	16.31	17.13	17.60
	6H	16.93	17.64	17.43	18.12	18.60	16.55	17.26	17.05	17.74	18.22
	8H	17.19	17.82	17.70	18.33	18.82	16.80	17.43	17.31	17.94	18.42
	12H	17.39	17.95	17.90	18.44	19.00	16.98	17.54	17.49	18.03	18.59
12H	4H	16.25	17.01	16.73	17.48	17.95	15.88	16.64	16.36	17.12	17.59
	6H	16.98	17.61	17.49	18.12	18.60	16.61	17.24	17.12	17.75	18.24
	8H	17.29	17.85	17.80	18.34	18.90	16.91	17.47	17.42	17.96	18.52