

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930304

Luminaire Tested: DFN2DS-HX4F0-060DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-060DS935-RLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4386.0 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930304

CATALOG NUMBER: DFN2DS-HX4F0-060DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930304

CATALOG NUMBER: DFN2DS-HX4F0-060DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1586	1586	1586
5°	1592	1566	1575
10°	1580	1540	1527
15°	1561	1495	1452
20°	1536	1429	1358
25°	1511	1355	1267
30°	1475	1279	1150
35°	1440	1197	1048
40°	1405	1111	929
45°	1364	1015	822
50°	1322	918	717
55°	1278	813	616
60°	1228	703	511
65°	1172	591	465
70°	1104	487	428
75°	1020	444	400
80°	901	396	364
85°	707	312	312

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1364 cd/sqm

TEST NUMBER: P930304

CATALOG NUMBER: DFN2DS-HX4F0-060DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.9	4.6
10°-20°	548.7	12.5
20°-30°	770.3	17.6
30°-40°	839.7	19.1
40°-50°	771.8	17.6
50°-60°	606.1	13.8
60°-70°	394.5	9.0
70°-80°	203.1	4.6
80°-90°	51.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1518.9	34.6
0°-40°	2358.6	53.8
0°-60°	3736.5	85.2
0°-90°	4386.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4386.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2133	2133	2133	2133	2133	
5°	2133	2123	2098	2115	2110	202
15°	2028	2007	1942	1905	1886	572
25°	1841	1779	1652	1573	1544	847
35°	1586	1488	1318	1197	1154	993
45°	1297	1168	965	828	782	1002
55°	986	836	627	512	475	881
65°	666	510	336	270	264	660
75°	355	220	154	141	139	376
85°	83	42	37	37	37	99
90°	0	0	0	0	0	

TEST NUMBER: P930304

CATALOG NUMBER: DFN2DS-HX4F0-060DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2132.6	2132.6	2132.6	2132.6	2132.6
2.5°	2142.3	2132.6	2111.3	2130.7	2126.9
5°	2132.6	2123.0	2097.8	2115.3	2109.5
7.5°	2115.3	2103.7	2076.7	2084.3	2074.7
10°	2092.0	2078.5	2040.1	2034.2	2022.6
12.5°	2063.2	2045.8	1993.6	1982.1	1960.8
15°	2028.4	2007.1	1941.5	1904.9	1885.6
17.5°	1987.9	1956.9	1875.8	1833.4	1802.6
20°	1941.5	1902.8	1806.4	1758.3	1715.7
22.5°	1891.4	1846.9	1735.0	1669.4	1640.5
25°	1841.3	1779.4	1652.1	1573.0	1544.0
27.5°	1781.5	1715.7	1574.8	1484.1	1439.7
30°	1717.8	1644.2	1489.9	1391.6	1339.4
32.5°	1655.9	1567.1	1409.0	1293.1	1244.8
35°	1586.5	1488.1	1318.3	1196.6	1154.0
37.5°	1518.9	1412.6	1233.3	1100.0	1051.9
40°	1447.5	1331.8	1144.4	1007.4	957.3
42.5°	1374.2	1250.7	1055.7	912.8	864.7
45°	1297.0	1167.5	965.1	827.8	781.6
47.5°	1223.7	1086.7	878.2	741.1	698.7
50°	1142.6	1005.6	793.3	660.0	619.6
52.5°	1063.3	918.6	712.2	584.8	548.2
55°	986.2	835.7	627.2	511.5	474.8
57.5°	907.1	752.7	552.0	443.9	413.0
60°	826.0	671.7	472.8	374.5	343.6
62.5°	747.0	592.6	405.2	312.7	297.3
65°	665.9	509.5	335.8	270.3	264.4
67.5°	588.7	432.2	270.3	237.4	231.6
70°	507.6	357.1	223.8	204.6	196.8
72.5°	430.4	287.5	187.1	171.8	167.9
75°	355.1	219.9	154.4	140.9	139.1
77.5°	279.9	156.3	121.6	113.9	110.0
80°	210.3	112.0	92.5	85.0	85.0
82.5°	146.6	75.3	63.6	59.8	59.8
85°	82.9	42.4	36.6	36.6	36.6
87.5°	31.0	15.4	15.4	13.5	13.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930304

CATALOG NUMBER: DFN2DS-HX4F0-060DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.84	14.36	13.20	14.67	14.99	8.80	10.32	9.16	10.63	10.95
	3H	14.60	15.97	14.98	16.29	16.66	10.06	11.43	10.44	11.76	12.12
	4H	15.27	16.55	15.67	16.90	17.28	10.56	11.84	10.96	12.19	12.57
	6H	15.76	16.94	16.17	17.31	17.70	10.95	12.13	11.36	12.49	12.89
	8H	15.92	17.05	16.35	17.44	17.84	11.07	12.20	11.50	12.59	12.99
	12H	16.03	17.10	16.46	17.49	17.92	11.15	12.23	11.58	12.61	13.04
4H	2H	12.94	14.22	13.34	14.57	14.95	9.49	10.77	9.89	11.12	11.50
	3H	14.87	15.94	15.28	16.34	16.74	10.94	12.00	11.35	12.40	12.80
	4H	15.62	16.58	16.06	17.00	17.43	11.54	12.49	11.97	12.91	13.35
	6H	16.22	17.05	16.67	17.49	17.95	12.02	12.86	12.48	13.30	13.76
	8H	16.43	17.21	16.89	17.65	18.12	12.19	12.96	12.65	13.41	13.87
	12H	16.58	17.28	17.06	17.76	18.23	12.30	13.00	12.79	13.48	13.95
8H	4H	15.65	16.42	16.11	16.87	17.34	11.89	12.67	12.35	13.11	13.58
	6H	16.29	16.93	16.78	17.42	17.90	12.48	13.12	12.97	13.61	14.09
	8H	16.54	17.11	17.05	17.62	18.11	12.70	13.27	13.21	13.78	14.27
	12H	16.74	17.25	17.25	17.74	18.31	12.88	13.39	13.39	13.88	14.44
12H	4H	15.63	16.33	16.11	16.80	17.28	11.93	12.63	12.41	13.11	13.58
	6H	16.27	16.84	16.78	17.35	17.84	12.54	13.12	13.05	13.63	14.11
	8H	16.55	17.06	17.06	17.55	18.12	12.81	13.32	13.32	13.81	14.38