

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929887

Luminaire Tested: DFN2DS-4P3F0-040DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929887
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-040DS930-FLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3227.4 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 40.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929887

CATALOG NUMBER: DFN2DS-4P3F0-040DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929887

CATALOG NUMBER: DFN2DS-4P3F0-040DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1446	1446	1446
5°	1451	1430	1439
10°	1443	1416	1423
15°	1425	1397	1396
20°	1399	1370	1368
25°	1374	1336	1336
30°	1342	1305	1294
35°	1312	1268	1249
40°	1274	1230	1207
45°	1236	1193	1164
50°	1196	1155	1114
55°	1154	1110	1069
60°	1106	1057	1018
65°	1056	1003	957
70°	992	939	894
75°	902	864	843
80°	801	776	736
85°	654	622	558

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1236 cd/sqm

TEST NUMBER: P929887

CATALOG NUMBER: DFN2DS-4P3F0-040DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	3.7
10°-20°	335.9	10.4
20°-30°	493.7	15.3
30°-40°	573.4	17.8
40°-50°	572.7	17.7
50°-60°	499.3	15.5
60°-70°	369.1	11.4
70°-80°	208.8	6.5
80°-90°	55.1	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	949.0	29.4
0°-40°	1522.3	47.2
0°-60°	2594.3	80.4
0°-90°	3227.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3227.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1268	1268	1268	1268	1268	
5°	1268	1264	1250	1260	1258	120
15°	1208	1200	1184	1189	1183	340
25°	1093	1083	1062	1065	1062	503
35°	943	931	911	904	898	589
45°	767	759	740	727	722	592
55°	581	573	559	544	538	519
65°	392	384	372	361	355	387
75°	205	202	196	189	192	219
85°	50	49	48	44	43	59
90°	0	0	0	0	0	

TEST NUMBER: P929887

CATALOG NUMBER: DFN2DS-4P3F0-040DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.5	1268.5	1268.5	1268.5	1268.5
2.5°	1275.9	1269.8	1256.3	1268.5	1266.2
5°	1268.5	1263.7	1250.2	1259.9	1257.6
7.5°	1259.9	1252.7	1239.2	1249.1	1246.6
10°	1246.6	1238.1	1223.5	1233.2	1229.5
12.5°	1228.2	1221.0	1206.4	1212.5	1209.9
15°	1207.5	1200.3	1184.4	1189.2	1183.2
17.5°	1181.9	1174.7	1158.8	1164.8	1158.8
20°	1153.8	1146.5	1129.5	1133.1	1128.4
22.5°	1125.8	1114.8	1098.9	1098.9	1096.5
25°	1092.8	1083.1	1062.4	1064.8	1062.4
27.5°	1056.2	1047.7	1032.0	1028.3	1022.3
30°	1019.7	1009.9	991.7	988.0	983.1
32.5°	980.7	973.4	953.9	946.5	941.6
35°	942.9	930.7	911.2	903.8	897.7
37.5°	900.2	889.2	869.6	861.1	855.0
40°	856.3	846.5	826.9	816.1	811.2
42.5°	813.6	803.8	784.4	772.0	764.8
45°	767.2	758.8	740.3	727.1	722.1
47.5°	722.1	713.5	694.1	680.6	673.4
50°	674.5	668.4	651.3	634.2	628.1
52.5°	628.1	619.6	603.8	590.4	581.8
55°	580.7	573.3	558.7	544.0	538.0
57.5°	533.0	527.0	511.0	496.4	491.5
60°	485.4	480.6	463.6	450.1	446.5
62.5°	439.1	430.6	418.4	406.2	401.3
65°	391.6	384.2	372.0	361.0	355.0
67.5°	342.8	336.6	325.8	317.2	312.3
70°	297.6	292.7	281.7	273.2	268.4
72.5°	251.3	246.4	240.3	231.8	228.1
75°	204.9	202.5	196.3	189.1	191.5
77.5°	163.4	158.5	156.1	152.4	148.8
80°	122.0	120.7	118.3	114.7	112.2
82.5°	83.0	83.0	81.8	76.9	76.9
85°	50.0	48.8	47.6	43.8	42.7
87.5°	22.0	19.6	17.1	13.4	12.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929887

CATALOG NUMBER: DFN2DS-4P3F0-040DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.56	14.17	12.93	14.49	14.80	12.12	13.73	12.48	14.04	14.36
	3H	14.31	15.77	14.69	16.09	16.45	13.82	15.28	14.20	15.60	15.96
	4H	14.96	16.33	15.36	16.68	17.05	14.46	15.83	14.86	16.18	16.56
	6H	15.43	16.70	15.84	17.06	17.45	14.93	16.20	15.34	16.56	16.95
	8H	15.57	16.78	16.00	17.17	17.57	15.07	16.28	15.49	16.67	17.07
	12H	15.66	16.82	16.09	17.20	17.63	15.15	16.31	15.58	16.69	17.12
4H	2H	13.12	14.49	13.52	14.84	15.22	12.77	14.14	13.17	14.49	14.86
	3H	15.10	16.24	15.51	16.64	17.04	14.69	15.84	15.10	16.24	16.64
	4H	15.87	16.91	16.31	17.32	17.76	15.45	16.49	15.88	16.90	17.34
	6H	16.47	17.38	16.93	17.82	18.27	16.04	16.94	16.49	17.38	17.84
	8H	16.66	17.51	17.12	17.95	18.41	16.22	17.07	16.68	17.51	17.98
	12H	16.79	17.55	17.27	18.03	18.50	16.34	17.10	16.82	17.58	18.05
8H	4H	16.15	16.99	16.61	17.44	17.90	15.77	16.62	16.23	17.06	17.53
	6H	16.86	17.57	17.36	18.05	18.53	16.48	17.18	16.97	17.67	18.15
	8H	17.12	17.75	17.63	18.26	18.75	16.73	17.36	17.24	17.87	18.35
	12H	17.32	17.88	17.83	18.37	18.93	16.91	17.47	17.42	17.96	18.52
12H	4H	16.17	16.93	16.65	17.41	17.88	15.81	16.57	16.29	17.05	17.51
	6H	16.91	17.54	17.42	18.05	18.53	16.54	17.17	17.05	17.68	18.16
	8H	17.22	17.78	17.73	18.27	18.83	16.84	17.40	17.35	17.89	18.45