

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929905

Luminaire Tested: DFN2DS-4P3F0-050DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929905
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-050DS930-FLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4034.2 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 51.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929905

CATALOG NUMBER: DFN2DS-4P3F0-050DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929905

CATALOG NUMBER: DFN2DS-4P3F0-050DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1807	1807	1807
5°	1814	1788	1798
10°	1803	1770	1778
15°	1781	1747	1745
20°	1749	1712	1710
25°	1718	1670	1670
30°	1677	1631	1617
35°	1640	1585	1561
40°	1592	1538	1508
45°	1546	1491	1455
50°	1495	1443	1392
55°	1442	1387	1336
60°	1383	1321	1272
65°	1320	1254	1196
70°	1239	1174	1118
75°	1128	1081	1054
80°	1001	970	921
85°	816	778	698

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1546 cd/sqm

TEST NUMBER: P929905

CATALOG NUMBER: DFN2DS-4P3F0-050DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.2	3.7
10°-20°	419.9	10.4
20°-30°	617.1	15.3
30°-40°	716.7	17.8
40°-50°	715.8	17.7
50°-60°	624.2	15.5
60°-70°	461.4	11.4
70°-80°	261.0	6.5
80°-90°	68.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1186.2	29.4
0°-40°	1902.9	47.2
0°-60°	3242.9	80.4
0°-90°	4034.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4034.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1586	1586	1586	1586	1586	
5°	1586	1580	1563	1575	1572	151
15°	1509	1500	1480	1487	1479	425
25°	1366	1354	1328	1331	1328	629
35°	1179	1163	1139	1130	1122	736
45°	959	948	925	909	903	740
55°	726	717	698	680	672	649
65°	490	480	465	451	444	484
75°	256	253	245	236	239	273
85°	62	61	60	55	53	73
90°	0	0	0	0	0	

TEST NUMBER: P929905

CATALOG NUMBER: DFN2DS-4P3F0-050DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1585.6	1585.6	1585.6	1585.6	1585.6
2.5°	1594.8	1587.2	1570.4	1585.6	1582.7
5°	1585.6	1579.6	1562.8	1574.9	1572.1
7.5°	1574.9	1565.9	1549.1	1561.4	1558.3
10°	1558.3	1547.6	1529.3	1541.4	1536.9
12.5°	1535.3	1526.3	1508.0	1515.6	1512.5
15°	1509.4	1500.3	1480.4	1486.6	1479.0
17.5°	1477.4	1468.3	1448.4	1456.0	1448.4
20°	1442.3	1433.3	1411.9	1416.4	1410.4
22.5°	1407.3	1393.6	1373.7	1373.7	1370.6
25°	1366.1	1354.0	1328.0	1331.0	1328.0
27.5°	1320.3	1309.6	1289.9	1285.3	1277.8
30°	1274.7	1262.4	1239.6	1235.1	1228.9
32.5°	1225.8	1216.8	1192.3	1183.1	1177.0
35°	1178.6	1163.4	1139.0	1129.8	1122.2
37.5°	1125.2	1111.5	1087.0	1076.4	1068.8
40°	1070.4	1058.1	1033.7	1020.1	1013.9
42.5°	1017.0	1004.7	980.4	965.0	956.0
45°	959.1	948.4	925.4	908.8	902.6
47.5°	902.6	891.9	867.6	850.7	841.7
50°	843.1	835.5	814.2	792.8	785.2
52.5°	785.2	774.5	754.8	738.0	727.3
55°	725.8	716.6	698.3	680.0	672.5
57.5°	666.3	658.7	638.8	620.5	614.3
60°	606.8	600.8	579.5	562.6	558.1
62.5°	548.9	538.2	523.0	507.7	501.6
65°	489.5	480.3	465.0	451.3	443.7
67.5°	428.5	420.8	407.2	396.5	390.3
70°	372.0	365.9	352.2	341.5	335.5
72.5°	314.2	308.0	300.4	289.7	285.2
75°	256.1	253.1	245.4	236.4	239.4
77.5°	204.3	198.1	195.1	190.5	186.1
80°	152.6	150.9	147.8	143.4	140.3
82.5°	103.7	103.7	102.2	96.1	96.1
85°	62.4	61.0	59.5	54.8	53.4
87.5°	27.5	24.4	21.4	16.8	15.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929905

CATALOG NUMBER: DFN2DS-4P3F0-050DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.34	14.95	13.70	15.26	15.58	12.89	14.50	13.26	14.82	15.13
	3H	15.09	16.54	15.47	16.87	17.23	14.60	16.05	14.97	16.38	16.74
	4H	15.73	17.10	16.13	17.45	17.83	15.24	16.61	15.64	16.96	17.33
	6H	16.20	17.47	16.61	17.84	18.23	15.70	16.97	16.11	17.34	17.73
	8H	16.35	17.56	16.77	17.95	18.35	15.84	17.05	16.27	17.44	17.84
	12H	16.44	17.60	16.87	17.98	18.41	15.93	17.09	16.35	17.47	17.90
4H	2H	13.90	15.27	14.30	15.62	15.99	13.55	14.91	13.94	15.26	15.64
	3H	15.87	17.02	16.28	17.42	17.82	15.47	16.61	15.88	17.01	17.41
	4H	16.65	17.69	17.08	18.10	18.54	16.23	17.26	16.66	17.68	18.11
	6H	17.25	18.15	17.70	18.59	19.05	16.81	17.72	17.27	18.16	18.62
	8H	17.44	18.28	17.90	18.73	19.19	17.00	17.84	17.46	18.29	18.75
	12H	17.57	18.33	18.05	18.80	19.27	17.12	17.88	17.60	18.35	18.82
8H	4H	16.92	17.77	17.38	18.21	18.68	16.55	17.40	17.01	17.84	18.30
	6H	17.64	18.34	18.13	18.83	19.30	17.26	17.96	17.75	18.45	18.92
	8H	17.90	18.53	18.41	19.03	19.52	17.51	18.14	18.02	18.64	19.13
	12H	18.10	18.65	18.60	19.15	19.71	17.68	18.24	18.19	18.73	19.29
12H	4H	16.95	17.71	17.43	18.19	18.65	16.58	17.34	17.07	17.82	18.29
	6H	17.68	18.31	18.19	18.82	19.31	17.31	17.95	17.82	18.45	18.94
	8H	18.00	18.55	18.50	19.05	19.61	17.62	18.18	18.13	18.67	19.23