

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930306

Luminaire Tested: DFN2DS-HX4F0-060DS940-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930306
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-060DS940-RLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4549.2 lumens
Efficiency: N/A
Efficacy: 77.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930306

CATALOG NUMBER: DFN2DS-HX4F0-060DS940-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930306

CATALOG NUMBER: DFN2DS-HX4F0-060DS940-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1645	1645	1645
5°	1651	1624	1633
10°	1638	1598	1584
15°	1620	1550	1506
20°	1593	1483	1408
25°	1567	1406	1314
30°	1530	1327	1193
35°	1494	1241	1087
40°	1457	1152	964
45°	1415	1053	852
50°	1371	952	743
55°	1326	843	638
60°	1274	729	530
65°	1215	613	482
70°	1145	505	444
75°	1058	460	414
80°	934	411	377
85°	734	324	324

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1415 cd/sqm

TEST NUMBER: P930306

CATALOG NUMBER: DFN2DS-HX4F0-060DS940-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.3	4.6
10°-20°	569.1	12.5
20°-30°	799.0	17.6
30°-40°	871.0	19.1
40°-50°	800.5	17.6
50°-60°	628.7	13.8
60°-70°	409.2	9.0
70°-80°	210.6	4.6
80°-90°	53.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1575.4	34.6
0°-40°	2446.4	53.8
0°-60°	3875.6	85.2
0°-90°	4549.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4549.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2212	2212	2212	2212	2212	
5°	2212	2202	2176	2194	2188	210
15°	2104	2082	2014	1976	1956	593
25°	1910	1846	1714	1632	1601	878
35°	1646	1543	1367	1241	1197	1030
45°	1345	1211	1001	859	811	1039
55°	1023	867	650	531	492	914
65°	691	528	348	280	274	685
75°	368	228	160	146	144	390
85°	86	44	38	38	38	103
90°	0	0	0	0	0	

TEST NUMBER: P930306

CATALOG NUMBER: DFN2DS-HX4F0-060DS940-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2212.0	2212.0	2212.0	2212.0	2212.0
2.5°	2222.0	2212.0	2189.9	2210.0	2206.0
5°	2212.0	2202.0	2175.9	2194.0	2188.0
7.5°	2194.0	2182.0	2154.0	2161.9	2151.9
10°	2169.9	2155.9	2116.0	2109.8	2097.9
12.5°	2140.0	2121.9	2067.7	2055.9	2033.8
15°	2103.9	2081.7	2013.8	1975.8	1955.8
17.5°	2061.9	2029.7	1945.6	1901.7	1869.6
20°	2013.8	1973.6	1873.6	1823.7	1779.5
22.5°	1961.8	1915.7	1799.5	1731.6	1701.6
25°	1909.8	1845.6	1713.5	1631.6	1601.4
27.5°	1847.8	1779.5	1633.4	1539.3	1493.3
30°	1781.7	1705.4	1545.3	1443.3	1389.2
32.5°	1717.5	1625.4	1461.5	1341.2	1291.1
35°	1645.6	1543.4	1367.3	1241.1	1197.0
37.5°	1575.5	1465.2	1279.2	1141.0	1091.0
40°	1501.3	1381.4	1187.0	1044.9	992.9
42.5°	1425.3	1297.2	1095.0	946.8	896.9
45°	1345.2	1211.0	1001.0	858.6	810.6
47.5°	1269.2	1127.1	910.9	768.6	724.7
50°	1185.1	1043.0	822.8	684.5	642.7
52.5°	1102.9	952.7	738.7	606.6	568.6
55°	1022.9	866.8	650.5	530.6	492.5
57.5°	940.9	780.7	572.6	460.5	428.3
60°	856.8	696.7	490.4	388.5	356.4
62.5°	774.8	614.7	420.3	324.3	308.4
65°	690.7	528.4	348.3	280.4	274.2
67.5°	610.6	448.3	280.4	246.2	240.2
70°	526.5	370.4	232.1	212.2	204.1
72.5°	446.4	298.2	194.1	178.2	174.1
75°	368.3	228.1	160.1	146.1	144.2
77.5°	290.3	162.1	126.1	118.1	114.1
80°	218.1	116.1	96.0	88.1	88.1
82.5°	152.1	78.1	66.0	62.0	62.0
85°	86.0	44.0	38.0	38.0	38.0
87.5°	32.1	16.0	16.0	14.0	14.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930306

CATALOG NUMBER: DFN2DS-HX4F0-060DS940-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.96	14.49	13.33	14.80	15.11	8.92	10.45	9.29	10.76	11.07
	3H	14.73	16.09	15.11	16.42	16.78	10.19	11.56	10.57	11.88	12.24
	4H	15.40	16.68	15.79	17.02	17.40	10.69	11.97	11.09	12.32	12.70
	6H	15.88	17.07	16.30	17.43	17.83	11.07	12.26	11.48	12.62	13.01
	8H	16.05	17.18	16.48	17.57	17.97	11.20	12.32	11.62	12.71	13.11
	12H	16.15	17.23	16.58	17.61	18.04	11.28	12.36	11.71	12.74	13.17
4H	2H	13.07	14.35	13.47	14.70	15.08	9.62	10.90	10.02	11.25	11.63
	3H	15.00	16.06	15.41	16.46	16.86	11.06	12.13	11.47	12.53	12.93
	4H	15.75	16.71	16.18	17.12	17.56	11.66	12.62	12.09	13.03	13.47
	6H	16.34	17.17	16.80	17.62	18.08	12.15	12.98	12.61	13.43	13.88
	8H	16.56	17.33	17.02	17.78	18.25	12.31	13.09	12.78	13.53	14.00
	12H	16.71	17.40	17.19	17.88	18.35	12.43	13.12	12.91	13.60	14.07
8H	4H	15.77	16.55	16.24	17.00	17.46	12.02	12.79	12.48	13.24	13.70
	6H	16.41	17.05	16.91	17.55	18.02	12.60	13.24	13.10	13.74	14.21
	8H	16.66	17.24	17.18	17.75	18.24	12.82	13.40	13.34	13.91	14.40
	12H	16.87	17.38	17.38	17.87	18.43	13.00	13.51	13.51	14.00	14.57
12H	4H	15.76	16.45	16.24	16.93	17.40	12.06	12.75	12.54	13.23	13.70
	6H	16.39	16.97	16.91	17.48	17.97	12.67	13.24	13.18	13.75	14.24
	8H	16.68	17.19	17.19	17.68	18.24	12.94	13.45	13.45	13.94	14.51

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7