

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930323

Luminaire Tested: DFN2DS-HX4F0-070DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930323
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-070DS940-FLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6181.6 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 71.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930323

CATALOG NUMBER: DFN2DS-HX4F0-070DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930323

CATALOG NUMBER: DFN2DS-HX4F0-070DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1806	1806	1806
5°	1813	1787	1798
10°	1803	1769	1778
15°	1780	1746	1745
20°	1749	1712	1710
25°	1717	1670	1670
30°	1677	1631	1617
35°	1639	1584	1561
40°	1592	1537	1508
45°	1545	1491	1454
50°	1494	1443	1392
55°	1442	1387	1336
60°	1383	1320	1272
65°	1320	1254	1196
70°	1239	1173	1118
75°	1127	1080	1054
80°	1001	970	920
85°	816	779	698

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1545 cd/sqm

TEST NUMBER: P930323

CATALOG NUMBER: DFN2DS-HX4F0-070DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.7	3.7
10°-20°	643.4	10.4
20°-30°	945.5	15.3
30°-40°	1098.2	17.8
40°-50°	1096.8	17.7
50°-60°	956.4	15.5
60°-70°	707.0	11.4
70°-80°	400.0	6.5
80°-90°	105.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1817.6	29.4
0°-40°	2915.8	47.2
0°-60°	4969.0	80.4
0°-90°	6181.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6181.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2430	2430	2430	2430	2430	
5°	2430	2420	2395	2413	2409	231
15°	2313	2299	2268	2278	2266	651
25°	2093	2075	2035	2040	2035	963
35°	1806	1783	1745	1731	1719	1128
45°	1470	1453	1418	1392	1383	1134
55°	1112	1098	1070	1042	1030	994
65°	750	736	713	692	680	742
75°	392	388	376	362	367	419
85°	96	94	91	84	82	112
90°	0	0	0	0	0	

TEST NUMBER: P930323

CATALOG NUMBER: DFN2DS-HX4F0-070DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2429.5	2429.5	2429.5	2429.5	2429.5
2.5°	2443.7	2432.0	2406.3	2429.5	2425.1
5°	2429.5	2420.4	2394.7	2413.2	2408.8
7.5°	2413.2	2399.3	2373.5	2392.4	2387.7
10°	2387.7	2371.3	2343.3	2361.9	2355.0
12.5°	2352.5	2338.6	2310.6	2322.2	2317.5
15°	2312.9	2299.0	2268.4	2277.9	2266.2
17.5°	2263.7	2249.9	2219.4	2231.1	2219.4
20°	2209.9	2196.1	2163.4	2170.3	2161.1
22.5°	2156.4	2135.4	2104.9	2104.9	2100.1
25°	2093.3	2074.6	2035.0	2039.5	2035.0
27.5°	2023.1	2006.7	1976.5	1969.5	1957.9
30°	1953.2	1934.3	1899.4	1892.5	1883.0
32.5°	1878.3	1864.5	1827.0	1812.9	1803.4
35°	1805.9	1782.7	1745.2	1731.1	1719.4
37.5°	1724.1	1703.1	1665.6	1649.3	1637.6
40°	1640.1	1621.3	1583.8	1563.1	1553.6
42.5°	1558.3	1539.5	1502.3	1478.8	1464.8
45°	1469.6	1453.2	1418.0	1392.5	1383.0
47.5°	1383.0	1366.7	1329.3	1303.5	1289.7
50°	1291.9	1280.2	1247.5	1214.8	1203.1
52.5°	1203.1	1186.8	1156.6	1130.8	1114.4
55°	1112.1	1098.1	1070.0	1042.0	1030.3
57.5°	1021.0	1009.3	978.8	950.8	941.4
60°	929.7	920.5	887.9	862.1	855.2
62.5°	841.0	824.7	801.4	778.1	768.6
65°	750.1	735.9	712.6	691.6	679.9
67.5°	656.6	644.7	623.9	607.5	598.1
70°	570.1	560.7	539.6	523.2	514.1
72.5°	481.3	472.0	460.3	443.9	437.0
75°	392.4	387.9	376.0	362.2	366.9
77.5°	313.1	303.6	298.9	292.0	285.1
80°	233.7	231.3	226.6	219.6	214.9
82.5°	158.9	158.9	156.6	147.3	147.3
85°	95.7	93.5	91.3	84.0	81.8
87.5°	42.1	37.5	32.7	25.8	23.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930323

CATALOG NUMBER: DFN2DS-HX4F0-070DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.34	14.95	13.70	15.26	15.58	12.89	14.50	13.26	14.82	15.13
	3H	15.09	16.54	15.46	16.87	17.23	14.60	16.05	14.97	16.38	16.74
	4H	15.73	17.10	16.13	17.45	17.83	15.24	16.61	15.64	16.96	17.33
	6H	16.20	17.47	16.61	17.84	18.23	15.70	16.97	16.11	17.33	17.73
	8H	16.35	17.56	16.77	17.95	18.34	15.84	17.05	16.27	17.44	17.84
	12H	16.44	17.60	16.87	17.98	18.41	15.92	17.08	16.35	17.47	17.89
4H	2H	13.90	15.27	14.30	15.61	15.99	13.54	14.91	13.94	15.26	15.64
	3H	15.87	17.02	16.28	17.42	17.82	15.47	16.61	15.88	17.01	17.41
	4H	16.65	17.69	17.08	18.10	18.54	16.23	17.26	16.66	17.68	18.11
	6H	17.25	18.15	17.70	18.59	19.05	16.81	17.72	17.27	18.16	18.62
	8H	17.44	18.28	17.90	18.72	19.19	17.00	17.84	17.46	18.29	18.75
	12H	17.57	18.33	18.05	18.80	19.27	17.12	17.88	17.60	18.35	18.82
8H	4H	16.92	17.77	17.38	18.21	18.68	16.55	17.40	17.01	17.84	18.30
	6H	17.64	18.34	18.13	18.83	19.30	17.26	17.96	17.75	18.45	18.92
	8H	17.90	18.53	18.41	19.03	19.52	17.50	18.14	18.01	18.64	19.13
	12H	18.10	18.65	18.60	19.14	19.71	17.68	18.24	18.19	18.73	19.29
12H	4H	16.95	17.71	17.43	18.18	18.65	16.58	17.34	17.06	17.82	18.29
	6H	17.68	18.31	18.19	18.82	19.31	17.31	17.95	17.82	18.45	18.94
	8H	18.00	18.55	18.50	19.04	19.61	17.62	18.18	18.13	18.67	19.23