

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930396

Luminaire Tested: DFN2DS-HX4F0-110DS940-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930396
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX4F0-110DS940-RLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8340.2 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.09' x L: 3.54' x H: 0')
CIE Type: Direct

Input Watts (W): 117.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930396

CATALOG NUMBER: DFN2DS-HX4F0-110DS940-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930396

CATALOG NUMBER: DFN2DS-HX4F0-110DS940-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3015	3015	3015
5°	3027	2977	2994
10°	3004	2929	2904
15°	2969	2842	2760
20°	2921	2718	2582
25°	2872	2577	2409
30°	2805	2432	2187
35°	2738	2275	1992
40°	2672	2112	1767
45°	2593	1930	1563
50°	2513	1745	1363
55°	2431	1546	1171
60°	2336	1337	972
65°	2228	1124	884
70°	2098	925	814
75°	1940	843	760
80°	1712	754	692
85°	1345	595	595

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2593 cd/sqm

TEST NUMBER: P930396

CATALOG NUMBER: DFN2DS-HX4F0-110DS940-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	380.1	4.6
10°-20°	1043.4	12.5
20°-30°	1464.8	17.6
30°-40°	1596.8	19.1
40°-50°	1467.6	17.6
50°-60°	1152.6	13.8
60°-70°	750.2	9.0
70°-80°	386.2	4.6
80°-90°	98.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2888.3	34.6
0°-40°	4485.0	53.8
0°-60°	7105.2	85.2
0°-90°	8340.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8340.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4055	4055	4055	4055	4055	
5°	4055	4037	3989	4022	4011	385
15°	3857	3817	3692	3622	3586	1087
25°	3501	3384	3141	2991	2936	1610
35°	3017	2830	2507	2276	2194	1888
45°	2466	2220	1835	1574	1486	1905
55°	1875	1589	1193	973	903	1676
65°	1266	969	639	514	503	1255
75°	675	418	294	268	264	714
85°	158	81	70	70	70	189
90°	0	0	0	0	0	

TEST NUMBER: P930396

CATALOG NUMBER: DFN2DS-HX4F0-110DS940-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4055.3	4055.3	4055.3	4055.3	4055.3
2.5°	4073.6	4055.3	4014.8	4051.8	4044.4
5°	4055.3	4037.0	3989.1	4022.2	4011.3
7.5°	4022.2	4000.4	3949.0	3963.4	3945.0
10°	3978.2	3952.5	3879.3	3868.0	3846.2
12.5°	3923.3	3890.2	3790.9	3769.1	3728.6
15°	3857.1	3816.6	3692.0	3622.3	3585.7
17.5°	3780.0	3721.2	3567.0	3486.4	3427.6
20°	3692.0	3618.4	3435.0	3343.5	3262.5
22.5°	3596.6	3512.1	3299.2	3174.5	3119.6
25°	3501.2	3383.6	3141.4	2991.1	2935.8
27.5°	3387.5	3262.5	2994.6	2822.1	2737.6
30°	3266.4	3126.6	2833.1	2646.1	2546.8
32.5°	3148.8	2979.8	2679.2	2458.9	2367.0
35°	3016.8	2829.5	2506.8	2275.5	2194.5
37.5°	2888.4	2686.3	2345.2	2091.7	2000.2
40°	2752.4	2532.5	2176.2	1915.7	1820.3
42.5°	2613.0	2378.3	2007.6	1735.8	1644.3
45°	2466.3	2220.2	1835.1	1574.2	1486.3
47.5°	2326.9	2066.4	1670.0	1409.1	1328.5
50°	2172.6	1912.2	1508.5	1255.0	1178.2
52.5°	2022.0	1746.7	1354.2	1112.1	1042.3
55°	1875.2	1589.0	1192.6	972.6	903.0
57.5°	1724.9	1431.3	1049.7	844.2	785.3
60°	1570.7	1277.2	899.0	712.2	653.4
62.5°	1420.4	1126.9	770.6	594.6	565.3
65°	1266.2	968.7	638.6	514.0	502.6
67.5°	1119.5	822.0	514.0	451.3	440.4
70°	965.2	679.1	425.6	389.0	374.2
72.5°	818.4	546.7	355.9	326.7	319.2
75°	675.2	418.2	293.6	267.9	264.4
77.5°	532.3	297.1	231.3	216.5	209.1
80°	399.9	213.0	176.0	161.6	161.6
82.5°	278.8	143.3	121.1	113.7	113.7
85°	157.7	80.6	69.7	69.7	69.7
87.5°	58.8	29.2	29.2	25.7	25.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930396

CATALOG NUMBER: DFN2DS-HX4F0-110DS940-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.07	16.59	15.43	16.90	17.22	11.03	12.55	11.40	12.87	13.18
	3H	16.83	18.20	17.21	18.53	18.89	12.30	13.66	12.67	13.99	14.35
	4H	17.50	18.78	17.90	19.13	19.51	12.80	14.08	13.20	14.43	14.80
	6H	17.99	19.17	18.40	19.54	19.93	13.18	14.36	13.59	14.73	15.12
	8H	18.16	19.28	18.58	19.67	20.07	13.30	14.43	13.73	14.82	15.22
	12H	18.26	19.34	18.69	19.72	20.15	13.38	14.46	13.81	14.84	15.27
4H	2H	15.17	16.45	15.57	16.80	17.18	11.73	13.01	12.13	13.36	13.73
	3H	17.11	18.17	17.52	18.57	18.97	13.17	14.23	13.58	14.63	15.03
	4H	17.86	18.81	18.29	19.23	19.67	13.77	14.72	14.20	15.14	15.58
	6H	18.45	19.28	18.91	19.72	20.18	14.26	15.09	14.71	15.53	15.99
	8H	18.66	19.44	19.13	19.88	20.35	14.42	15.20	14.88	15.64	16.11
	12H	18.82	19.51	19.30	19.99	20.46	14.54	15.23	15.02	15.71	16.18
8H	4H	17.88	18.66	18.34	19.10	19.57	14.12	14.90	14.59	15.34	15.81
	6H	18.52	19.16	19.01	19.65	20.13	14.71	15.35	15.21	15.84	16.32
	8H	18.77	19.34	19.28	19.85	20.34	14.93	15.51	15.44	16.02	16.50
	12H	18.97	19.48	19.48	19.97	20.54	15.11	15.62	15.62	16.11	16.68
12H	4H	17.86	18.56	18.35	19.04	19.51	14.17	14.86	14.65	15.34	15.81
	6H	18.50	19.08	19.01	19.59	20.07	14.77	15.35	15.29	15.86	16.35
	8H	18.78	19.29	19.29	19.79	20.35	15.05	15.56	15.55	16.05	16.61

END OF REPORT