

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929969

Luminaire Tested: DFN2DS-4P4F0-050DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929969
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-050DS835-FLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4950.0 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 50.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929969

CATALOG NUMBER: DFN2DS-4P4F0-050DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929969

CATALOG NUMBER: DFN2DS-4P4F0-050DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1262	1262	1262
5°	1267	1249	1256
10°	1260	1236	1242
15°	1244	1220	1219
20°	1222	1196	1195
25°	1200	1166	1166
30°	1172	1139	1130
35°	1145	1107	1090
40°	1112	1074	1054
45°	1080	1042	1016
50°	1044	1008	972
55°	1007	969	933
60°	966	923	889
65°	922	876	836
70°	866	820	781
75°	788	755	736
80°	699	678	643
85°	570	543	488

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1080 cd/sqm

TEST NUMBER: P929969

CATALOG NUMBER: DFN2DS-4P4F0-050DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.1	3.7
10°-20°	515.2	10.4
20°-30°	757.2	15.3
30°-40°	879.4	17.8
40°-50°	878.3	17.7
50°-60°	765.8	15.5
60°-70°	566.1	11.4
70°-80°	320.3	6.5
80°-90°	84.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1455.5	29.4
0°-40°	2334.9	47.2
0°-60°	3979.0	80.4
0°-90°	4950.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4950.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1946	1938	1918	1932	1929	185
15°	1852	1841	1816	1824	1815	522
25°	1676	1661	1630	1633	1630	771
35°	1446	1428	1398	1386	1377	903
45°	1177	1164	1136	1115	1108	908
55°	891	879	857	834	825	796
65°	601	589	571	554	544	594
75°	314	311	301	290	294	335
85°	77	75	73	67	66	90
90°	0	0	0	0	0	

TEST NUMBER: P929969

CATALOG NUMBER: DFN2DS-4P4F0-050DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1945.5	1945.5	1945.5	1945.5	1945.5
2.5°	1956.8	1947.5	1926.9	1945.5	1942.0
5°	1945.5	1938.2	1917.5	1932.4	1928.9
7.5°	1932.4	1921.3	1900.7	1915.8	1912.0
10°	1912.0	1898.9	1876.5	1891.3	1885.8
12.5°	1883.8	1872.7	1850.3	1859.6	1855.8
15°	1852.0	1840.9	1816.5	1824.1	1814.7
17.5°	1812.7	1801.6	1777.2	1786.5	1777.2
20°	1769.7	1758.6	1732.4	1737.9	1730.6
22.5°	1726.8	1709.9	1685.5	1685.5	1681.7
25°	1676.2	1661.3	1629.5	1633.1	1629.5
27.5°	1620.0	1606.9	1582.7	1577.1	1567.8
30°	1564.0	1549.0	1521.0	1515.4	1507.9
32.5°	1504.1	1493.0	1463.0	1451.7	1444.2
35°	1446.1	1427.5	1397.5	1386.2	1376.9
37.5°	1380.6	1363.8	1333.8	1320.7	1311.4
40°	1313.4	1298.3	1268.3	1251.6	1244.1
42.5°	1247.9	1232.8	1203.0	1184.1	1173.0
45°	1176.8	1163.7	1135.5	1115.1	1107.5
47.5°	1107.5	1094.4	1064.5	1043.8	1032.7
50°	1034.5	1025.2	999.0	972.8	963.4
52.5°	963.4	950.3	926.1	905.5	892.4
55°	890.6	879.3	856.8	834.4	825.1
57.5°	817.5	808.2	783.8	761.4	753.8
60°	744.5	737.2	711.0	690.3	684.8
62.5°	673.5	660.4	641.7	623.0	615.5
65°	600.6	589.3	570.6	553.8	544.4
67.5°	525.8	516.3	499.6	486.5	478.9
70°	456.5	449.0	432.1	419.0	411.7
72.5°	385.5	377.9	368.6	355.5	349.9
75°	314.2	310.6	301.1	290.0	293.8
77.5°	250.7	243.1	239.4	233.8	228.3
80°	187.2	185.2	181.4	175.9	172.1
82.5°	127.2	127.2	125.4	117.9	117.9
85°	76.6	74.8	73.0	67.3	65.5
87.5°	33.7	30.0	26.2	20.6	18.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929969

CATALOG NUMBER: DFN2DS-4P4F0-050DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.09	13.70	12.46	14.02	14.33	11.65	13.26	12.01	13.57	13.89
	3H	13.84	15.30	14.22	15.62	15.98	13.35	14.80	13.73	15.13	15.49
	4H	14.49	15.86	14.89	16.20	16.58	13.99	15.36	14.39	15.71	16.09
	6H	14.96	16.23	15.37	16.59	16.98	14.46	15.72	14.87	16.09	16.48
	8H	15.10	16.31	15.52	16.70	17.10	14.60	15.81	15.02	16.20	16.60
	12H	15.19	16.35	15.62	16.73	17.16	14.68	15.84	15.11	16.22	16.65
4H	2H	12.65	14.02	13.05	14.37	14.74	12.30	13.67	12.70	14.02	14.39
	3H	14.63	15.77	15.04	16.17	16.57	14.22	15.37	14.63	15.76	16.16
	4H	15.40	16.44	15.83	16.85	17.29	14.98	16.02	15.41	16.43	16.87
	6H	16.00	16.90	16.45	17.35	17.80	15.57	16.47	16.02	16.91	17.37
	8H	16.19	17.04	16.65	17.48	17.94	15.75	16.60	16.21	17.04	17.51
	12H	16.32	17.08	16.80	17.56	18.03	15.87	16.63	16.35	17.11	17.57
8H	4H	15.68	16.52	16.14	16.97	17.43	15.30	16.15	15.76	16.59	17.06
	6H	16.39	17.09	16.88	17.58	18.06	16.01	16.71	16.50	17.20	17.68
	8H	16.65	17.28	17.16	17.79	18.27	16.26	16.89	16.77	17.40	17.88
	12H	16.85	17.41	17.36	17.90	18.46	16.44	17.00	16.94	17.49	18.05
12H	4H	15.70	16.46	16.18	16.94	17.41	15.34	16.10	15.82	16.57	17.04
	6H	16.44	17.07	16.95	17.58	18.06	16.07	16.70	16.58	17.21	17.69
	8H	16.75	17.31	17.26	17.80	18.36	16.37	16.93	16.88	17.42	17.98