

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930006

Luminaire Tested: DFN2DS-4P4F0-070DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-070DS835-RLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5950.0 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 74.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930006

CATALOG NUMBER: DFN2DS-4P4F0-070DS835-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930006

CATALOG NUMBER: DFN2DS-4P4F0-070DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92	90	88	86
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82	79	76	74
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74	69	66	64
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66	62	57	55
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60	55	51	49
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55	50	45	43
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51	45	41	39
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47	41	37	35
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44	38	34	32
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1877	1877	1877
5°	1884	1853	1864
10°	1870	1823	1808
15°	1848	1769	1718
20°	1818	1692	1607
25°	1788	1604	1499
30°	1746	1514	1361
35°	1704	1416	1240
40°	1663	1315	1100
45°	1614	1201	973
50°	1564	1086	848
55°	1513	962	729
60°	1454	832	605
65°	1387	699	550
70°	1306	576	506
75°	1207	525	473
80°	1066	469	431
85°	837	370	370

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1614 cd/sqm

TEST NUMBER: P930006

CATALOG NUMBER: DFN2DS-4P4F0-070DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.1	4.6
10°-20°	744.3	12.5
20°-30°	1045.0	17.6
30°-40°	1139.2	19.1
40°-50°	1047.0	17.6
50°-60°	822.3	13.8
60°-70°	535.2	9.0
70°-80°	275.5	4.6
80°-90°	70.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2060.5	34.6
0°-40°	3199.7	53.8
0°-60°	5068.9	85.2
0°-90°	5950.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5950.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2893	2893	2893	2893	2893	
5°	2893	2880	2846	2870	2862	274
15°	2752	2723	2634	2584	2558	775
25°	2498	2414	2241	2134	2094	1149
35°	2152	2019	1788	1623	1566	1347
45°	1760	1584	1309	1123	1060	1359
55°	1338	1134	851	694	644	1195
65°	903	691	456	367	359	896
75°	482	298	209	191	189	509
85°	112	58	50	50	50	135
90°	0	0	0	0	0	

TEST NUMBER: P930006

CATALOG NUMBER: DFN2DS-4P4F0-070DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2893.1	2893.1	2893.1	2893.1	2893.1
2.5°	2906.1	2893.1	2864.2	2890.6	2885.3
5°	2893.1	2880.0	2845.9	2869.5	2861.7
7.5°	2869.5	2853.9	2817.3	2827.5	2814.5
10°	2838.1	2819.8	2767.5	2759.5	2743.9
12.5°	2798.9	2775.3	2704.5	2688.9	2660.0
15°	2751.7	2722.8	2633.9	2584.2	2558.1
17.5°	2696.7	2654.8	2544.8	2487.2	2445.3
20°	2633.9	2581.4	2450.6	2385.3	2327.5
22.5°	2565.9	2505.6	2353.6	2264.7	2225.6
25°	2497.8	2413.9	2241.1	2133.9	2094.5
27.5°	2416.7	2327.5	2136.4	2013.4	1953.1
30°	2330.3	2230.6	2021.1	1887.8	1817.0
32.5°	2246.4	2125.9	1911.4	1754.2	1688.6
35°	2152.2	2018.6	1788.4	1623.4	1565.6
37.5°	2060.6	1916.4	1673.1	1492.2	1427.0
40°	1963.6	1806.7	1552.5	1366.7	1298.6
42.5°	1864.2	1696.7	1432.2	1238.3	1173.1
45°	1759.5	1583.9	1309.2	1123.1	1060.3
47.5°	1660.0	1474.2	1191.4	1005.3	947.8
50°	1550.0	1364.2	1076.1	895.3	840.6
52.5°	1442.5	1246.1	966.1	793.3	743.6
55°	1337.8	1133.6	850.8	693.9	644.2
57.5°	1230.6	1021.1	748.9	602.2	560.3
60°	1120.6	911.1	641.4	508.1	466.1
62.5°	1013.3	803.9	549.7	424.2	403.3
65°	903.3	691.1	455.6	366.7	358.6
67.5°	798.6	586.4	366.7	321.9	314.2
70°	688.6	484.4	303.6	277.5	266.9
72.5°	583.9	390.0	253.9	233.1	227.8
75°	481.7	298.3	209.4	191.1	188.6
77.5°	379.7	211.9	165.0	154.4	149.2
80°	285.3	151.9	125.6	115.3	115.3
82.5°	198.9	102.2	86.4	81.1	81.1
85°	112.5	57.5	49.7	49.7	49.7
87.5°	41.9	20.8	20.8	18.3	18.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930006

CATALOG NUMBER: DFN2DS-4P4F0-070DS835-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.42	14.94	13.79	15.26	15.57	9.38	10.90	9.75	11.22	11.53
	3H	15.19	16.55	15.57	16.88	17.24	10.65	12.01	11.03	12.34	12.70
	4H	15.85	17.13	16.25	17.48	17.86	11.15	12.43	11.55	12.78	13.16
	6H	16.34	17.53	16.75	17.89	18.28	11.53	12.71	11.94	13.08	13.47
	8H	16.51	17.63	16.93	18.02	18.43	11.66	12.78	12.08	13.17	13.57
	12H	16.61	17.69	17.04	18.07	18.50	11.74	12.81	12.17	13.20	13.63
4H	2H	13.53	14.81	13.93	15.16	15.53	10.08	11.36	10.48	11.71	12.09
	3H	15.46	16.52	15.87	16.92	17.32	11.52	12.58	11.93	12.98	13.38
	4H	16.21	17.17	16.64	17.58	18.02	12.12	13.08	12.55	13.49	13.93
	6H	16.80	17.63	17.26	18.08	18.53	12.61	13.44	13.07	13.88	14.34
	8H	17.01	17.79	17.48	18.24	18.70	12.77	13.55	13.23	13.99	14.46
	12H	17.17	17.86	17.65	18.34	18.81	12.89	13.58	13.37	14.06	14.53
8H	4H	16.23	17.01	16.70	17.45	17.92	12.47	13.25	12.94	13.70	14.16
	6H	16.87	17.51	17.37	18.00	18.48	13.06	13.70	13.56	14.19	14.67
	8H	17.12	17.70	17.63	18.21	18.70	13.28	13.86	13.80	14.37	14.86
	12H	17.32	17.83	17.83	18.33	18.89	13.46	13.97	13.97	14.46	15.03
12H	4H	16.22	16.91	16.70	17.39	17.86	12.52	13.21	13.00	13.69	14.16
	6H	16.85	17.43	17.36	17.94	18.43	13.12	13.70	13.64	14.21	14.70
	8H	17.14	17.65	17.65	18.14	18.70	13.40	13.91	13.91	14.40	14.96