

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930474

Luminaire Tested: DFN2DS-PN2F0-050DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930474
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-050DS835-RLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4250.0 lumens
Efficiency: N/A
Efficacy: 78.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 54
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930474

CATALOG NUMBER: DFN2DS-PN2F0-050DS835-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930474

CATALOG NUMBER: DFN2DS-PN2F0-050DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92	90	88	86
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82	79	76	74
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74	69	66	64
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66	62	57	55
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60	55	51	49
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55	50	45	43
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51	45	41	39
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47	41	37	35
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44	38	34	32
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4476	4476	4476
5°	4493	4420	4444
10°	4458	4348	4310
15°	4407	4219	4097
20°	4336	4034	3832
25°	4264	3826	3575
30°	4163	3611	3246
35°	4065	3377	2957
40°	3966	3135	2623
45°	3850	2864	2320
50°	3731	2590	2023
55°	3608	2295	1737
60°	3467	1984	1442
65°	3307	1668	1313
70°	3115	1374	1208
75°	2880	1252	1127
80°	2542	1119	1027
85°	1998	882	882

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3850 cd/sqm

TEST NUMBER: P930474

CATALOG NUMBER: DFN2DS-PN2F0-050DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.7	4.6
10°-20°	531.7	12.5
20°-30°	746.5	17.6
30°-40°	813.7	19.1
40°-50°	747.9	17.6
50°-60°	587.3	13.8
60°-70°	382.3	9.0
70°-80°	196.8	4.6
80°-90°	50.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1471.8	34.6
0°-40°	2285.5	53.8
0°-60°	3620.7	85.2
0°-90°	4250.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4250.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2066	2066	2066	2066	2066	
5°	2066	2057	2033	2050	2044	196
15°	1966	1945	1881	1846	1827	554
25°	1784	1724	1601	1524	1496	821
35°	1537	1442	1277	1160	1118	962
45°	1257	1131	935	802	757	971
55°	956	810	608	496	460	854
65°	645	494	325	262	256	640
75°	344	213	150	136	135	364
85°	80	41	36	36	36	96
90°	0	0	0	0	0	

TEST NUMBER: P930474

CATALOG NUMBER: DFN2DS-PN2F0-050DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2066.5	2066.5	2066.5	2066.5	2066.5
2.5°	2075.8	2066.5	2045.9	2064.7	2060.9
5°	2066.5	2057.2	2032.8	2049.6	2044.1
7.5°	2049.6	2038.5	2012.3	2019.7	2010.3
10°	2027.2	2014.1	1976.8	1971.1	1959.9
12.5°	1999.2	1982.4	1931.8	1920.7	1900.0
15°	1965.5	1944.9	1881.4	1845.9	1827.2
17.5°	1926.2	1896.3	1817.7	1776.6	1746.6
20°	1881.4	1843.9	1750.4	1703.8	1662.5
22.5°	1832.8	1789.7	1681.2	1617.7	1589.7
25°	1784.1	1724.2	1600.8	1524.2	1496.0
27.5°	1726.2	1662.5	1526.0	1438.1	1395.1
30°	1664.5	1593.3	1443.7	1348.4	1297.8
32.5°	1604.6	1518.5	1365.3	1253.0	1206.2
35°	1537.3	1441.9	1277.4	1159.5	1118.3
37.5°	1471.8	1368.9	1195.1	1065.9	1019.3
40°	1402.6	1290.5	1108.9	976.2	927.6
42.5°	1331.6	1211.9	1023.0	884.5	837.9
45°	1256.8	1131.4	935.1	802.2	757.3
47.5°	1185.7	1053.0	851.0	718.1	677.0
50°	1107.2	974.4	768.7	639.5	600.4
52.5°	1030.4	890.1	690.1	566.7	531.2
55°	955.6	809.7	607.7	495.6	460.1
57.5°	879.0	729.4	534.9	430.2	400.2
60°	800.4	650.8	458.1	362.9	332.9
62.5°	723.8	574.2	392.7	303.0	288.1
65°	645.2	493.7	325.4	261.9	256.2
67.5°	570.4	418.9	261.9	230.0	224.4
70°	491.9	346.0	216.9	198.2	190.7
72.5°	417.1	278.6	181.4	166.5	162.7
75°	344.1	213.1	149.6	136.5	134.7
77.5°	271.2	151.4	117.9	110.3	106.5
80°	203.8	108.5	89.7	82.3	82.3
82.5°	142.1	73.0	61.7	57.9	57.9
85°	80.4	41.1	35.5	35.5	35.5
87.5°	30.0	14.9	14.9	13.1	13.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930474

CATALOG NUMBER: DFN2DS-PN2F0-050DS835-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.44	17.96	16.81	18.28	18.59	12.40	13.92	12.77	14.24	14.55
	3H	18.21	19.57	18.58	19.90	20.26	13.67	15.03	14.05	15.36	15.72
	4H	18.87	20.15	19.27	20.50	20.88	14.17	15.45	14.57	15.80	16.18
	6H	19.36	20.55	19.77	20.91	21.30	14.55	15.73	14.96	16.10	16.49
	8H	19.53	20.65	19.95	21.04	21.44	14.67	15.80	15.10	16.19	16.59
	12H	19.63	20.71	20.06	21.09	21.52	14.76	15.83	15.19	16.22	16.64
4H	2H	16.55	17.83	16.95	18.18	18.55	13.10	14.38	13.50	14.73	15.11
	3H	18.48	19.54	18.89	19.94	20.34	14.54	15.60	14.95	16.00	16.40
	4H	19.23	20.19	19.66	20.60	21.04	15.14	16.10	15.57	16.51	16.95
	6H	19.82	20.65	20.28	21.09	21.55	15.63	16.46	16.09	16.90	17.36
	8H	20.03	20.81	20.50	21.26	21.72	15.79	16.57	16.25	17.01	17.48
	12H	20.19	20.88	20.67	21.36	21.83	15.91	16.60	16.39	17.08	17.55
8H	4H	19.25	20.03	19.72	20.47	20.94	15.49	16.27	15.96	16.72	17.18
	6H	19.89	20.53	20.39	21.02	21.50	16.08	16.72	16.58	17.21	17.69
	8H	20.14	20.72	20.65	21.23	21.71	16.30	16.88	16.82	17.39	17.88
	12H	20.34	20.85	20.85	21.35	21.91	16.48	16.99	16.99	17.48	18.05
12H	4H	19.24	19.93	19.72	20.41	20.88	15.54	16.23	16.02	16.71	17.18
	6H	19.87	20.45	20.38	20.96	21.45	16.14	16.72	16.66	17.23	17.72
	8H	20.16	20.67	20.67	21.16	21.72	16.42	16.93	16.93	17.42	17.98