

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929989

Luminaire Tested: DFN2DS-4P4F0-060DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929989
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-060DS840-FLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5945.9 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 62
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929989

CATALOG NUMBER: DFN2DS-4P4F0-060DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929989

CATALOG NUMBER: DFN2DS-4P4F0-060DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1516	1516	1516
5°	1522	1500	1509
10°	1513	1485	1492
15°	1494	1465	1464
20°	1468	1437	1435
25°	1441	1401	1401
30°	1407	1369	1357
35°	1376	1329	1310
40°	1336	1290	1266
45°	1297	1251	1220
50°	1254	1211	1168
55°	1210	1164	1121
60°	1160	1108	1067
65°	1107	1052	1004
70°	1040	984	938
75°	946	907	885
80°	840	814	772
85°	685	653	586

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1297 cd/sqm

TEST NUMBER: P929989

CATALOG NUMBER: DFN2DS-4P4F0-060DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.0	3.7
10°-20°	618.9	10.4
20°-30°	909.5	15.3
30°-40°	1056.3	17.8
40°-50°	1055.0	17.7
50°-60°	919.9	15.5
60°-70°	680.0	11.4
70°-80°	384.8	6.5
80°-90°	101.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1748.3	29.4
0°-40°	2804.6	47.2
0°-60°	4779.6	80.4
0°-90°	5945.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5945.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2337	2337	2337	2337	2337	
5°	2337	2328	2303	2321	2317	222
15°	2225	2211	2182	2191	2180	627
25°	2013	1996	1957	1962	1957	926
35°	1737	1715	1679	1665	1654	1085
45°	1414	1398	1364	1339	1330	1091
55°	1070	1056	1029	1002	991	956
65°	721	708	686	665	654	713
75°	377	373	362	348	353	403
85°	92	90	88	81	79	108
90°	0	0	0	0	0	

TEST NUMBER: P929989

CATALOG NUMBER: DFN2DS-4P4F0-060DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2336.9	2336.9	2336.9	2336.9	2336.9
2.5°	2350.5	2339.3	2314.5	2336.9	2332.6
5°	2336.9	2328.1	2303.3	2321.2	2316.9
7.5°	2321.2	2307.9	2283.1	2301.2	2296.7
10°	2296.7	2281.0	2254.0	2271.9	2265.2
12.5°	2262.9	2249.4	2222.5	2233.7	2229.2
15°	2224.6	2211.3	2182.0	2191.1	2179.9
17.5°	2177.5	2164.2	2134.8	2145.9	2134.8
20°	2125.7	2112.4	2080.9	2087.6	2078.8
22.5°	2074.3	2054.0	2024.6	2024.6	2020.1
25°	2013.4	1995.6	1957.4	1961.7	1957.4
27.5°	1945.9	1930.2	1901.1	1894.5	1883.3
30°	1878.8	1860.6	1827.0	1820.3	1811.2
32.5°	1806.7	1793.4	1757.4	1743.7	1734.7
35°	1737.1	1714.7	1678.7	1665.1	1653.9
37.5°	1658.5	1638.1	1602.2	1586.4	1575.2
40°	1577.6	1559.5	1523.5	1503.5	1494.4
42.5°	1498.9	1480.8	1445.0	1422.4	1409.0
45°	1413.6	1397.8	1364.0	1339.4	1330.3
47.5°	1330.3	1314.6	1278.7	1253.9	1240.4
50°	1242.6	1231.4	1200.0	1168.5	1157.3
52.5°	1157.3	1141.5	1112.4	1087.7	1072.0
55°	1069.8	1056.2	1029.2	1002.3	991.1
57.5°	982.1	970.9	941.5	914.6	905.5
60°	894.3	885.5	854.1	829.2	822.5
62.5°	808.9	793.2	770.8	748.3	739.3
65°	721.4	707.9	685.5	665.2	654.0
67.5°	631.5	620.1	600.1	584.4	575.3
70°	548.3	539.3	519.0	503.3	494.5
72.5°	463.0	454.0	442.7	427.0	420.3
75°	377.4	373.2	361.7	348.3	352.9
77.5°	301.1	292.1	287.5	280.9	274.2
80°	224.8	222.4	217.9	211.2	206.7
82.5°	152.9	152.9	150.7	141.6	141.6
85°	92.0	89.9	87.7	80.8	78.7
87.5°	40.5	36.0	31.4	24.8	22.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929989

CATALOG NUMBER: DFN2DS-4P4F0-060DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.73	14.34	13.09	14.65	14.97	12.28	13.89	12.65	14.21	14.52
	3H	14.48	15.93	14.86	16.26	16.62	13.99	15.44	14.36	15.77	16.13
	4H	15.12	16.49	15.52	16.84	17.22	14.63	16.00	15.03	16.35	16.72
	6H	15.59	16.86	16.00	17.23	17.62	15.09	16.36	15.50	16.73	17.12
	8H	15.74	16.95	16.16	17.34	17.74	15.23	16.44	15.66	16.83	17.23
	12H	15.83	16.99	16.26	17.37	17.80	15.32	16.48	15.74	16.86	17.29
4H	2H	13.29	14.66	13.69	15.01	15.38	12.94	14.31	13.33	14.65	15.03
	3H	15.26	16.41	15.67	16.81	17.21	14.86	16.00	15.27	16.40	16.80
	4H	16.04	17.08	16.47	17.49	17.93	15.62	16.65	16.05	17.07	17.50
	6H	16.64	17.54	17.09	17.98	18.44	16.20	17.11	16.66	17.55	18.01
	8H	16.83	17.67	17.29	18.12	18.58	16.39	17.23	16.85	17.68	18.14
	12H	16.96	17.72	17.44	18.19	18.66	16.51	17.27	16.99	17.74	18.21
8H	4H	16.31	17.16	16.77	17.60	18.07	15.94	16.79	16.40	17.23	17.69
	6H	17.03	17.73	17.52	18.22	18.69	16.65	17.35	17.14	17.84	18.31
	8H	17.29	17.92	17.80	18.43	18.91	16.90	17.53	17.41	18.03	18.52
	12H	17.49	18.05	17.99	18.54	19.10	17.07	17.63	17.58	18.12	18.68
12H	4H	16.34	17.10	16.82	17.58	18.05	15.98	16.74	16.46	17.21	17.68
	6H	17.07	17.71	17.58	18.21	18.70	16.70	17.34	17.21	17.84	18.33
	8H	17.39	17.95	17.89	18.44	19.00	17.01	17.57	17.52	18.06	18.62