

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930479

Luminaire Tested: DFN2DS-PN2F0-050DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930479
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-050DS927-FLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3920.4 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 54
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930479

CATALOG NUMBER: DFN2DS-PN2F0-050DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930479

CATALOG NUMBER: DFN2DS-PN2F0-050DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3337	3337	3337
5°	3350	3302	3321
10°	3330	3269	3285
15°	3289	3226	3223
20°	3231	3163	3159
25°	3173	3084	3084
30°	3098	3013	2987
35°	3028	2926	2883
40°	2941	2840	2786
45°	2855	2755	2687
50°	2761	2666	2571
55°	2664	2562	2468
60°	2554	2439	2350
65°	2438	2316	2210
70°	2289	2167	2065
75°	2082	1996	1947
80°	1850	1792	1700
85°	1508	1436	1290

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2855 cd/sqm

TEST NUMBER: P930479

CATALOG NUMBER: DFN2DS-PN2F0-050DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.0	3.7
10°-20°	408.0	10.4
20°-30°	599.7	15.3
30°-40°	696.5	17.8
40°-50°	695.6	17.7
50°-60°	606.6	15.5
60°-70°	448.4	11.4
70°-80°	253.7	6.5
80°-90°	67.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1152.7	29.4
0°-40°	1849.2	47.2
0°-60°	3151.4	80.4
0°-90°	3920.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3920.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1541	1541	1541	1541	1541	
5°	1541	1535	1519	1530	1528	146
15°	1467	1458	1439	1445	1437	413
25°	1328	1316	1291	1293	1291	611
35°	1145	1131	1107	1098	1090	715
45°	932	922	899	883	877	719
55°	705	696	679	661	654	631
65°	476	467	452	439	431	470
75°	249	246	238	230	233	266
85°	61	59	58	53	52	71
90°	0	0	0	0	0	

TEST NUMBER: P930479

CATALOG NUMBER: DFN2DS-PN2F0-050DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1540.8	1540.8	1540.8	1540.8	1540.8
2.5°	1549.8	1542.4	1526.1	1540.8	1538.1
5°	1540.8	1535.1	1518.7	1530.5	1527.7
7.5°	1530.5	1521.7	1505.4	1517.3	1514.3
10°	1514.3	1503.9	1486.2	1497.9	1493.6
12.5°	1492.0	1483.2	1465.4	1472.8	1469.8
15°	1466.8	1458.0	1438.7	1444.7	1437.2
17.5°	1435.7	1426.9	1407.5	1414.9	1407.5
20°	1401.6	1392.8	1372.1	1376.4	1370.6
22.5°	1367.6	1354.2	1334.9	1334.9	1331.9
25°	1327.6	1315.7	1290.6	1293.4	1290.6
27.5°	1283.0	1272.7	1253.5	1249.1	1241.7
30°	1238.7	1226.8	1204.6	1200.2	1194.3
32.5°	1191.2	1182.5	1158.7	1149.7	1143.8
35°	1145.3	1130.6	1106.8	1097.9	1090.5
37.5°	1093.4	1080.1	1056.4	1046.0	1038.6
40°	1040.2	1028.3	1004.5	991.3	985.3
42.5°	988.3	976.4	952.8	937.8	929.0
45°	932.0	921.7	899.3	883.2	877.1
47.5°	877.1	866.8	843.1	826.7	817.9
50°	819.3	812.0	791.2	770.5	763.0
52.5°	763.0	752.6	733.5	717.2	706.8
55°	705.4	696.4	678.6	660.8	653.5
57.5°	647.5	640.1	620.8	603.0	597.0
60°	589.6	583.9	563.1	546.7	542.4
62.5°	533.4	523.0	508.2	493.4	487.5
65°	475.7	466.7	451.9	438.6	431.2
67.5°	416.4	408.9	395.7	385.3	379.3
70°	361.5	355.6	342.2	331.8	326.1
72.5°	305.3	299.3	291.9	281.6	277.1
75°	248.8	246.0	238.5	229.7	232.7
77.5°	198.6	192.5	189.6	185.2	180.8
80°	148.3	146.7	143.7	139.3	136.3
82.5°	100.7	100.7	99.3	93.4	93.4
85°	60.7	59.2	57.8	53.3	51.9
87.5°	26.7	23.8	20.8	16.3	14.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930479

CATALOG NUMBER: DFN2DS-PN2F0-050DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.47	17.08	15.83	17.39	17.71	15.03	16.64	15.39	16.95	17.26
	3H	17.22	18.67	17.60	19.00	19.36	16.73	18.18	17.11	18.51	18.87
	4H	17.87	19.24	18.26	19.58	19.96	17.37	18.74	17.77	19.09	19.46
	6H	18.34	19.60	18.75	19.97	20.36	17.83	19.10	18.25	19.47	19.86
	8H	18.48	19.69	18.90	20.08	20.48	17.98	19.19	18.40	19.58	19.97
	12H	18.57	19.73	19.00	20.11	20.54	18.06	19.22	18.49	19.60	20.03
4H	2H	16.03	17.40	16.43	17.75	18.12	15.68	17.05	16.08	17.39	17.77
	3H	18.01	19.15	18.41	19.55	19.95	17.60	18.74	18.01	19.14	19.54
	4H	18.78	19.82	19.21	20.23	20.67	18.36	19.39	18.79	19.81	20.24
	6H	19.38	20.28	19.83	20.72	21.18	18.95	19.85	19.40	20.29	20.75
	8H	19.57	20.41	20.03	20.86	21.32	19.13	19.98	19.59	20.42	20.88
	12H	19.70	20.46	20.18	20.94	21.40	19.25	20.01	19.73	20.48	20.95
8H	4H	19.05	19.90	19.52	20.34	20.81	18.68	19.53	19.14	19.97	20.44
	6H	19.77	20.47	20.26	20.96	21.44	19.39	20.09	19.88	20.58	21.05
	8H	20.03	20.66	20.54	21.17	21.65	19.64	20.27	20.15	20.77	21.26
	12H	20.23	20.79	20.74	21.28	21.84	19.82	20.37	20.32	20.86	21.43
12H	4H	19.08	19.84	19.56	20.32	20.79	18.72	19.48	19.20	19.95	20.42
	6H	19.81	20.45	20.32	20.95	21.44	19.45	20.08	19.96	20.59	21.07
	8H	20.13	20.69	20.64	21.18	21.74	19.75	20.31	20.26	20.80	21.36