

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930009

Luminaire Tested: DFN2DS-4P4F0-070DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-070DS850-FLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7685.4 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 74.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930009

CATALOG NUMBER: DFN2DS-4P4F0-070DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930009

CATALOG NUMBER: DFN2DS-4P4F0-070DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1960	1960	1960
5°	1967	1939	1950
10°	1956	1919	1929
15°	1931	1894	1892
20°	1897	1857	1855
25°	1863	1811	1811
30°	1819	1769	1754
35°	1778	1718	1693
40°	1727	1668	1636
45°	1676	1617	1578
50°	1621	1565	1510
55°	1564	1505	1449
60°	1500	1432	1379
65°	1432	1360	1298
70°	1344	1272	1212
75°	1223	1172	1143
80°	1086	1052	998
85°	886	845	757

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1676 cd/sqm

TEST NUMBER: P930009

CATALOG NUMBER: DFN2DS-4P4F0-070DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.3	3.7
10°-20°	799.9	10.4
20°-30°	1175.6	15.3
30°-40°	1365.3	17.8
40°-50°	1363.6	17.7
50°-60°	1189.1	15.5
60°-70°	879.0	11.4
70°-80°	497.3	6.5
80°-90°	131.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2259.8	29.4
0°-40°	3625.1	47.2
0°-60°	6177.8	80.4
0°-90°	7685.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7685.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3021	3021	3021	3021	3021	
5°	3021	3009	2977	3000	2995	287
15°	2876	2858	2820	2832	2818	810
25°	2602	2579	2530	2536	2530	1198
35°	2245	2216	2170	2152	2138	1402
45°	1827	1807	1763	1731	1720	1410
55°	1383	1365	1330	1296	1281	1236
65°	933	915	886	860	845	922
75°	488	482	467	450	456	521
85°	119	116	114	104	102	140
90°	0	0	0	0	0	

TEST NUMBER: P930009

CATALOG NUMBER: DFN2DS-4P4F0-070DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3020.6	3020.6	3020.6	3020.6	3020.6
2.5°	3038.2	3023.7	2991.6	3020.6	3015.0
5°	3020.6	3009.3	2977.2	3000.3	2994.7
7.5°	3000.3	2983.0	2950.9	2974.4	2968.6
10°	2968.6	2948.2	2913.3	2936.5	2927.9
12.5°	2924.8	2907.6	2872.8	2887.2	2881.3
15°	2875.5	2858.2	2820.3	2832.1	2817.5
17.5°	2814.4	2797.2	2759.3	2773.8	2759.3
20°	2747.5	2730.4	2689.7	2698.3	2686.9
22.5°	2681.0	2654.8	2616.9	2616.9	2611.0
25°	2602.5	2579.3	2530.1	2535.6	2530.1
27.5°	2515.2	2494.9	2457.3	2448.7	2434.1
30°	2428.4	2404.9	2361.5	2352.9	2341.1
32.5°	2335.2	2318.0	2271.5	2253.9	2242.2
35°	2245.3	2216.3	2169.8	2152.2	2137.7
37.5°	2143.6	2117.4	2070.8	2050.5	2036.0
40°	2039.1	2015.7	1969.1	1943.3	1931.5
42.5°	1937.4	1914.0	1867.8	1838.5	1821.2
45°	1827.1	1806.8	1763.0	1731.3	1719.5
47.5°	1719.5	1699.2	1652.6	1620.6	1603.4
50°	1606.2	1591.6	1550.9	1510.3	1495.8
52.5°	1495.8	1475.5	1437.9	1405.9	1385.5
55°	1382.7	1365.2	1330.4	1295.5	1281.0
57.5°	1269.4	1254.8	1216.9	1182.1	1170.4
60°	1155.9	1144.5	1103.9	1071.8	1063.2
62.5°	1045.6	1025.3	996.3	967.4	955.6
65°	932.6	914.9	886.0	859.8	845.3
67.5°	816.3	801.6	775.6	755.3	743.6
70°	708.8	697.1	670.8	650.5	639.1
72.5°	598.4	586.8	572.2	551.9	543.3
75°	487.8	482.3	467.4	450.3	456.1
77.5°	389.3	377.5	371.6	363.0	354.4
80°	290.6	287.6	281.7	273.0	267.2
82.5°	197.5	197.5	194.7	183.1	183.1
85°	119.0	116.2	113.5	104.5	101.7
87.5°	52.3	46.6	40.7	32.1	28.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930009

CATALOG NUMBER: DFN2DS-4P4F0-070DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.62	15.23	13.98	15.54	15.86	13.18	14.79	13.54	15.10	15.41
	3H	15.37	16.82	15.75	17.15	17.51	14.88	16.33	15.26	16.66	17.02
	4H	16.02	17.39	16.41	17.73	18.11	15.52	16.89	15.92	17.24	17.61
	6H	16.49	17.75	16.90	18.12	18.51	15.98	17.25	16.40	17.62	18.01
	8H	16.63	17.84	17.05	18.23	18.63	16.13	17.34	16.55	17.73	18.12
	12H	16.72	17.88	17.15	18.26	18.69	16.21	17.37	16.64	17.75	18.18
4H	2H	14.18	15.55	14.58	15.90	16.27	13.83	15.20	14.23	15.54	15.92
	3H	16.16	17.30	16.57	17.70	18.10	15.75	16.89	16.16	17.29	17.69
	4H	16.93	17.97	17.36	18.38	18.82	16.51	17.54	16.94	17.96	18.39
	6H	17.53	18.43	17.98	18.87	19.33	17.10	18.00	17.55	18.44	18.90
	8H	17.72	18.56	18.18	19.01	19.47	17.28	18.13	17.74	18.57	19.03
	12H	17.85	18.61	18.33	19.09	19.56	17.40	18.16	17.88	18.63	19.10
8H	4H	17.21	18.05	17.67	18.49	18.96	16.83	17.68	17.29	18.12	18.59
	6H	17.92	18.62	18.41	19.11	19.59	17.54	18.24	18.03	18.73	19.20
	8H	18.18	18.81	18.69	19.32	19.80	17.79	18.42	18.30	18.92	19.41
	12H	18.38	18.94	18.89	19.43	19.99	17.97	18.52	18.47	19.01	19.58
12H	4H	17.23	17.99	17.71	18.47	18.94	16.87	17.63	17.35	18.10	18.57
	6H	17.96	18.60	18.47	19.10	19.59	17.60	18.23	18.11	18.73	19.22
	8H	18.28	18.84	18.79	19.33	19.89	17.90	18.46	18.41	18.95	19.51

END OF REPORT