

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930027

Luminaire Tested: DFN2DS-4P4F0-080DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930027
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-080DS850-FLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8783.3 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 86.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930027

CATALOG NUMBER: DFN2DS-4P4F0-080DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930027

CATALOG NUMBER: DFN2DS-4P4F0-080DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2240	2240	2240
5°	2248	2216	2229
10°	2235	2193	2204
15°	2207	2165	2163
20°	2168	2122	2120
25°	2129	2070	2070
30°	2079	2022	2004
35°	2032	1964	1935
40°	1974	1906	1869
45°	1916	1848	1803
50°	1853	1789	1725
55°	1787	1720	1656
60°	1714	1637	1576
65°	1636	1554	1483
70°	1536	1454	1385
75°	1397	1339	1306
80°	1241	1203	1141
85°	1012	965	865

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1916 cd/sqm

TEST NUMBER: P930027

CATALOG NUMBER: DFN2DS-4P4F0-080DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	324.9	3.7
10°-20°	914.2	10.4
20°-30°	1343.5	15.3
30°-40°	1560.4	17.8
40°-50°	1558.4	17.7
50°-60°	1358.9	15.5
60°-70°	1004.5	11.4
70°-80°	568.4	6.5
80°-90°	150.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2582.6	29.4
0°-40°	4143.0	47.2
0°-60°	7060.4	80.4
0°-90°	8783.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8783.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3452	3452	3452	3452	3452	
5°	3452	3439	3402	3429	3423	328
15°	3286	3267	3223	3237	3220	926
25°	2974	2948	2892	2898	2892	1369
35°	2566	2533	2480	2460	2443	1602
45°	2088	2065	2015	1979	1965	1612
55°	1580	1560	1520	1481	1464	1413
65°	1066	1046	1012	983	966	1054
75°	558	551	534	515	521	595
85°	136	133	130	119	116	160
90°	0	0	0	0	0	

TEST NUMBER: P930027

CATALOG NUMBER: DFN2DS-4P4F0-080DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3452.1	3452.1	3452.1	3452.1	3452.1
2.5°	3472.2	3455.6	3419.0	3452.1	3445.8
5°	3452.1	3439.1	3402.5	3428.9	3422.6
7.5°	3428.9	3409.2	3372.6	3399.3	3392.7
10°	3392.7	3369.4	3329.6	3355.9	3346.2
12.5°	3342.6	3322.9	3283.1	3299.6	3293.0
15°	3286.3	3266.6	3223.2	3236.6	3220.1
17.5°	3216.5	3196.8	3153.4	3170.1	3153.4
20°	3140.1	3120.4	3073.9	3083.8	3070.7
22.5°	3064.1	3034.1	2990.8	2990.8	2984.1
25°	2974.2	2947.8	2891.5	2897.8	2891.5
27.5°	2874.5	2851.3	2808.3	2798.5	2781.9
30°	2775.3	2748.4	2698.9	2689.0	2675.6
32.5°	2668.9	2649.2	2595.9	2575.9	2562.6
35°	2566.0	2533.0	2479.7	2459.7	2443.1
37.5°	2449.8	2419.8	2366.7	2343.4	2326.9
40°	2330.5	2303.6	2250.5	2220.9	2207.5
42.5°	2214.2	2187.4	2134.6	2101.1	2081.5
45°	2088.1	2064.8	2014.8	1978.6	1965.3
47.5°	1965.3	1942.0	1888.7	1852.1	1832.4
50°	1835.6	1819.1	1772.5	1726.0	1709.5
52.5°	1709.5	1686.2	1643.3	1606.7	1583.4
55°	1580.2	1560.1	1520.4	1480.6	1464.0
57.5°	1450.7	1434.2	1390.8	1351.0	1337.6
60°	1321.0	1308.1	1261.5	1224.9	1215.0
62.5°	1194.9	1171.8	1138.6	1105.6	1092.1
65°	1065.7	1045.7	1012.5	982.6	966.0
67.5°	932.9	916.0	886.4	863.2	849.8
70°	810.0	796.6	766.8	743.5	730.4
72.5°	683.9	670.6	654.0	630.8	620.9
75°	557.5	551.2	534.3	514.6	521.2
77.5°	444.8	431.4	424.7	414.9	405.0
80°	332.1	328.6	321.9	312.1	305.3
82.5°	225.8	225.8	222.6	209.2	209.2
85°	136.0	132.7	129.6	119.4	116.2
87.5°	59.9	53.2	46.5	36.6	33.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930027

CATALOG NUMBER: DFN2DS-4P4F0-080DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.08	15.69	14.45	16.01	16.32	13.64	15.25	14.00	15.56	15.88
	3H	15.83	17.29	16.21	17.62	17.98	15.34	16.80	15.72	17.12	17.48
	4H	16.48	17.85	16.88	18.20	18.57	15.99	17.35	16.38	17.70	18.08
	6H	16.95	18.22	17.36	18.58	18.97	16.45	17.72	16.86	18.08	18.47
	8H	17.09	18.30	17.52	18.69	19.09	16.59	17.80	17.01	18.19	18.59
	12H	17.18	18.34	17.61	18.72	19.15	16.67	17.83	17.10	18.21	18.64
4H	2H	14.64	16.01	15.04	16.36	16.74	14.29	15.66	14.69	16.01	16.38
	3H	16.62	17.77	17.03	18.16	18.56	16.21	17.36	16.62	17.76	18.16
	4H	17.40	18.43	17.83	18.85	19.28	16.97	18.01	17.40	18.42	18.86
	6H	17.99	18.90	18.45	19.34	19.79	17.56	18.46	18.01	18.91	19.36
	8H	18.18	19.03	18.64	19.47	19.94	17.74	18.59	18.20	19.03	19.50
	12H	18.31	19.07	18.79	19.55	20.02	17.86	18.62	18.34	19.10	19.57
8H	4H	17.67	18.52	18.13	18.96	19.42	17.30	18.14	17.76	18.58	19.05
	6H	18.38	19.09	18.88	19.57	20.05	18.00	18.71	18.50	19.19	19.67
	8H	18.64	19.27	19.15	19.78	20.27	18.25	18.88	18.76	19.39	19.87
	12H	18.84	19.40	19.35	19.89	20.45	18.43	18.99	18.94	19.48	20.04
12H	4H	17.70	18.46	18.18	18.93	19.40	17.33	18.09	17.81	18.57	19.04
	6H	18.43	19.06	18.94	19.57	20.05	18.06	18.69	18.57	19.20	19.69
	8H	18.74	19.30	19.25	19.79	20.35	18.36	18.92	18.87	19.41	19.97