

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930497

Luminaire Tested: DFN2DS-PN2F0-060DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930497
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-060DS927-FLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4704.5 lumens
Efficiency: N/A
Efficacy: 69.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 67.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930497

CATALOG NUMBER: DFN2DS-PN2F0-060DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930497

CATALOG NUMBER: DFN2DS-PN2F0-060DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4005	4005	4005
5°	4020	3962	3986
10°	3997	3922	3942
15°	3947	3871	3867
20°	3877	3795	3791
25°	3807	3701	3701
30°	3718	3615	3584
35°	3634	3512	3460
40°	3529	3408	3343
45°	3426	3306	3224
50°	3313	3199	3085
55°	3196	3075	2961
60°	3065	2927	2819
65°	2925	2780	2652
70°	2748	2601	2477
75°	2499	2394	2336
80°	2219	2150	2039
85°	1809	1725	1548

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3426 cd/sqm

TEST NUMBER: P930497

CATALOG NUMBER: DFN2DS-PN2F0-060DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.0	3.7
10°-20°	489.7	10.4
20°-30°	719.6	15.3
30°-40°	835.8	17.8
40°-50°	834.7	17.7
50°-60°	727.9	15.5
60°-70°	538.1	11.4
70°-80°	304.4	6.5
80°-90°	80.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1383.3	29.4
0°-40°	2219.1	47.2
0°-60°	3781.7	80.4
0°-90°	4704.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4704.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1849	1849	1849	1849	1849	
5°	1849	1842	1822	1837	1833	176
15°	1760	1750	1726	1734	1725	496
25°	1593	1579	1549	1552	1549	733
35°	1374	1357	1328	1317	1308	858
45°	1118	1106	1079	1060	1053	863
55°	846	836	814	793	784	757
65°	571	560	542	526	517	564
75°	299	295	286	276	279	319
85°	73	71	69	64	62	86
90°	0	0	0	0	0	

TEST NUMBER: P930497

CATALOG NUMBER: DFN2DS-PN2F0-060DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1849.0	1849.0	1849.0	1849.0	1849.0
2.5°	1859.8	1850.9	1831.3	1849.0	1845.6
5°	1849.0	1842.0	1822.4	1836.6	1833.2
7.5°	1836.6	1826.0	1806.4	1820.7	1817.2
10°	1817.2	1804.7	1783.3	1797.5	1792.2
12.5°	1790.4	1779.8	1758.5	1767.3	1763.8
15°	1760.1	1749.6	1726.4	1733.6	1724.7
17.5°	1722.8	1712.3	1689.1	1697.9	1689.1
20°	1681.9	1671.4	1646.4	1651.7	1644.7
22.5°	1641.2	1625.1	1601.9	1601.9	1598.3
25°	1593.0	1578.9	1548.7	1552.1	1548.7
27.5°	1539.6	1527.2	1504.2	1498.9	1490.1
30°	1486.5	1472.1	1445.6	1440.3	1433.0
32.5°	1429.5	1418.9	1390.4	1379.7	1372.5
35°	1374.4	1356.7	1328.2	1317.4	1308.5
37.5°	1312.2	1296.1	1267.7	1255.2	1246.3
40°	1248.2	1233.9	1205.4	1189.6	1182.4
42.5°	1185.9	1171.6	1143.3	1125.4	1114.8
45°	1118.5	1105.9	1079.2	1059.8	1052.6
47.5°	1052.6	1040.1	1011.7	992.1	981.4
50°	983.2	974.3	949.4	924.5	915.6
52.5°	915.6	903.2	880.1	860.6	848.2
55°	846.4	835.6	814.3	793.0	784.2
57.5°	777.0	768.2	745.0	723.7	716.4
60°	707.6	700.6	675.7	656.1	650.8
62.5°	640.0	627.6	609.8	592.1	585.0
65°	570.8	560.1	542.4	526.3	517.4
67.5°	499.7	490.6	474.8	462.4	455.2
70°	433.9	426.7	410.7	398.2	391.2
72.5°	366.3	359.2	350.3	337.9	332.6
75°	298.6	295.3	286.1	275.6	279.2
77.5°	238.2	231.1	227.5	222.2	216.9
80°	177.9	176.0	172.4	167.1	163.5
82.5°	120.9	120.9	119.2	112.1	112.1
85°	72.8	71.1	69.4	63.9	62.3
87.5°	32.1	28.5	24.9	19.6	17.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930497

CATALOG NUMBER: DFN2DS-PN2F0-060DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.10	17.71	16.47	18.03	18.34	15.66	17.27	16.02	17.58	17.90
	3H	17.85	19.31	18.23	19.63	20.00	17.36	18.82	17.74	19.14	19.50
	4H	18.50	19.87	18.90	20.22	20.59	18.01	19.37	18.40	19.72	20.10
	6H	18.97	20.24	19.38	20.60	20.99	18.47	19.74	18.88	20.10	20.49
	8H	19.11	20.32	19.54	20.71	21.11	18.61	19.82	19.03	20.21	20.61
	12H	19.20	20.36	19.63	20.74	21.17	18.69	19.85	19.12	20.23	20.66
4H	2H	16.66	18.03	17.06	18.38	18.76	16.31	17.68	16.71	18.03	18.40
	3H	18.64	19.79	19.05	20.18	20.58	18.23	19.38	18.64	19.78	20.18
	4H	19.42	20.45	19.85	20.87	21.30	18.99	20.03	19.42	20.44	20.88
	6H	20.01	20.92	20.47	21.36	21.81	19.58	20.48	20.03	20.93	21.38
	8H	20.20	21.05	20.66	21.49	21.96	19.76	20.61	20.22	21.05	21.52
	12H	20.33	21.09	20.81	21.57	22.04	19.88	20.64	20.36	21.12	21.59
8H	4H	19.69	20.54	20.15	20.98	21.44	19.31	20.16	19.78	20.60	21.07
	6H	20.40	21.11	20.90	21.59	22.07	20.02	20.72	20.52	21.21	21.69
	8H	20.66	21.29	21.17	21.80	22.29	20.27	20.90	20.78	21.41	21.89
	12H	20.86	21.42	21.37	21.91	22.47	20.45	21.01	20.96	21.50	22.06
12H	4H	19.71	20.47	20.20	20.95	21.42	19.35	20.11	19.83	20.59	21.06
	6H	20.45	21.08	20.96	21.59	22.07	20.08	20.71	20.59	21.22	21.70
	8H	20.76	21.32	21.27	21.81	22.37	20.38	20.94	20.89	21.43	21.99