

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930481

Luminaire Tested: DFN2DS-PN2F0-050DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930481
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-050DS930-FLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4034.2 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 54
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930481

CATALOG NUMBER: DFN2DS-PN2F0-050DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930481

CATALOG NUMBER: DFN2DS-PN2F0-050DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3434	3434	3434
5°	3447	3398	3418
10°	3427	3363	3380
15°	3384	3319	3316
20°	3324	3254	3251
25°	3265	3174	3174
30°	3188	3100	3073
35°	3116	3012	2967
40°	3026	2923	2867
45°	2938	2835	2765
50°	2841	2743	2646
55°	2741	2637	2539
60°	2629	2510	2418
65°	2509	2383	2274
70°	2356	2230	2125
75°	2143	2054	2003
80°	1903	1843	1750
85°	1551	1479	1327

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2938 cd/sqm

TEST NUMBER: P930481

CATALOG NUMBER: DFN2DS-PN2F0-050DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.2	3.7
10°-20°	419.9	10.4
20°-30°	617.1	15.3
30°-40°	716.7	17.8
40°-50°	715.8	17.7
50°-60°	624.2	15.5
60°-70°	461.4	11.4
70°-80°	261.0	6.5
80°-90°	68.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1186.2	29.4
0°-40°	1902.9	47.2
0°-60°	3242.9	80.4
0°-90°	4034.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4034.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1586	1586	1586	1586	1586	
5°	1586	1580	1563	1575	1572	151
15°	1509	1500	1480	1487	1479	425
25°	1366	1354	1328	1331	1328	629
35°	1179	1163	1139	1130	1122	736
45°	959	948	925	909	903	740
55°	726	717	698	680	672	649
65°	490	480	465	451	444	484
75°	256	253	245	236	239	273
85°	62	61	60	55	53	73
90°	0	0	0	0	0	

TEST NUMBER: P930481

CATALOG NUMBER: DFN2DS-PN2F0-050DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1585.6	1585.6	1585.6	1585.6	1585.6
2.5°	1594.8	1587.2	1570.4	1585.6	1582.7
5°	1585.6	1579.6	1562.8	1574.9	1572.1
7.5°	1574.9	1565.9	1549.1	1561.4	1558.3
10°	1558.3	1547.6	1529.3	1541.4	1536.9
12.5°	1535.3	1526.3	1508.0	1515.6	1512.5
15°	1509.4	1500.3	1480.4	1486.6	1479.0
17.5°	1477.4	1468.3	1448.4	1456.0	1448.4
20°	1442.3	1433.3	1411.9	1416.4	1410.4
22.5°	1407.3	1393.6	1373.7	1373.7	1370.6
25°	1366.1	1354.0	1328.0	1331.0	1328.0
27.5°	1320.3	1309.6	1289.9	1285.3	1277.8
30°	1274.7	1262.4	1239.6	1235.1	1228.9
32.5°	1225.8	1216.8	1192.3	1183.1	1177.0
35°	1178.6	1163.4	1139.0	1129.8	1122.2
37.5°	1125.2	1111.5	1087.0	1076.4	1068.8
40°	1070.4	1058.1	1033.7	1020.1	1013.9
42.5°	1017.0	1004.7	980.4	965.0	956.0
45°	959.1	948.4	925.4	908.8	902.6
47.5°	902.6	891.9	867.6	850.7	841.7
50°	843.1	835.5	814.2	792.8	785.2
52.5°	785.2	774.5	754.8	738.0	727.3
55°	725.8	716.6	698.3	680.0	672.5
57.5°	666.3	658.7	638.8	620.5	614.3
60°	606.8	600.8	579.5	562.6	558.1
62.5°	548.9	538.2	523.0	507.7	501.6
65°	489.5	480.3	465.0	451.3	443.7
67.5°	428.5	420.8	407.2	396.5	390.3
70°	372.0	365.9	352.2	341.5	335.5
72.5°	314.2	308.0	300.4	289.7	285.2
75°	256.1	253.1	245.4	236.4	239.4
77.5°	204.3	198.1	195.1	190.5	186.1
80°	152.6	150.9	147.8	143.4	140.3
82.5°	103.7	103.7	102.2	96.1	96.1
85°	62.4	61.0	59.5	54.8	53.4
87.5°	27.5	24.4	21.4	16.8	15.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930481

CATALOG NUMBER: DFN2DS-PN2F0-050DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.57	17.18	15.93	17.49	17.81	15.12	16.74	15.49	17.05	17.36
	3H	17.32	18.77	17.70	19.10	19.46	16.83	18.28	17.20	18.61	18.97
	4H	17.97	19.33	18.36	19.68	20.06	17.47	18.84	17.87	19.19	19.56
	6H	18.43	19.70	18.85	20.07	20.46	17.93	19.20	18.34	19.57	19.96
	8H	18.58	19.79	19.00	20.18	20.58	18.08	19.29	18.50	19.67	20.07
	12H	18.67	19.83	19.10	20.21	20.64	18.16	19.32	18.59	19.70	20.13
4H	2H	16.13	17.50	16.53	17.85	18.22	15.78	17.15	16.17	17.49	17.87
	3H	18.10	19.25	18.51	19.65	20.05	17.70	18.84	18.11	19.24	19.64
	4H	18.88	19.92	19.31	20.33	20.77	18.46	19.49	18.89	19.91	20.34
	6H	19.48	20.38	19.93	20.82	21.28	19.05	19.95	19.50	20.39	20.85
	8H	19.67	20.51	20.13	20.96	21.42	19.23	20.08	19.69	20.52	20.98
	12H	19.80	20.56	20.28	21.03	21.50	19.35	20.11	19.83	20.58	21.05
8H	4H	19.15	20.00	19.62	20.44	20.91	18.78	19.63	19.24	20.07	20.53
	6H	19.87	20.57	20.36	21.06	21.54	19.49	20.19	19.98	20.68	21.15
	8H	20.13	20.76	20.64	21.27	21.75	19.74	20.37	20.25	20.87	21.36
	12H	20.33	20.89	20.83	21.38	21.94	19.92	20.47	20.42	20.96	21.52
12H	4H	19.18	19.94	19.66	20.42	20.89	18.82	19.58	19.30	20.05	20.52
	6H	19.91	20.55	20.42	21.05	21.54	19.55	20.18	20.06	20.68	21.17
	8H	20.23	20.79	20.73	21.28	21.84	19.85	20.41	20.36	20.90	21.46