

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929958

Luminaire Tested: DFN2DS-4P4F0-040DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929958
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-040DS927-RLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2692.8 lumens
Efficiency: N/A
Efficacy: 68.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 39.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929958

CATALOG NUMBER: DFN2DS-4P4F0-040DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P929958

CATALOG NUMBER: DFN2DS-4P4F0-040DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	849	849	849
5°	853	839	843
10°	846	825	818
15°	836	801	778
20°	823	766	727
25°	809	726	679
30°	790	685	616
35°	771	641	561
40°	753	595	498
45°	731	544	440
50°	708	492	384
55°	685	436	330
60°	658	377	274
65°	628	317	249
70°	591	261	229
75°	546	238	214
80°	482	212	195
85°	379	167	167

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 731 cd/sqm

TEST NUMBER: P929958

CATALOG NUMBER: DFN2DS-4P4F0-040DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	4.6
10°-20°	336.9	12.5
20°-30°	473.0	17.6
30°-40°	515.5	19.1
40°-50°	473.8	17.6
50°-60°	372.1	13.8
60°-70°	242.2	9.0
70°-80°	124.7	4.6
80°-90°	31.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	932.5	34.6
0°-40°	1448.1	53.8
0°-60°	2294.1	85.2
0°-90°	2692.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2692.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1309	1309	1309	1309	1309	
5°	1309	1303	1288	1299	1295	124
15°	1245	1232	1192	1170	1158	351
25°	1130	1092	1014	966	948	520
35°	974	914	809	735	708	610
45°	796	717	592	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	61
90°	0	0	0	0	0	

TEST NUMBER: P929958

CATALOG NUMBER: DFN2DS-4P4F0-040DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.3	1309.3	1309.3	1309.3	1309.3
2.5°	1315.3	1309.3	1296.3	1308.2	1305.8
5°	1309.3	1303.4	1288.0	1298.6	1295.2
7.5°	1298.6	1291.6	1275.0	1279.6	1273.8
10°	1284.5	1276.1	1252.5	1248.8	1241.9
12.5°	1266.7	1256.0	1224.0	1216.9	1203.8
15°	1245.3	1232.3	1192.0	1169.5	1157.7
17.5°	1220.5	1201.5	1151.6	1125.7	1106.7
20°	1192.0	1168.3	1109.0	1079.5	1053.4
22.5°	1161.2	1134.0	1065.2	1024.9	1007.3
25°	1130.4	1092.5	1014.2	965.8	947.9
27.5°	1093.8	1053.4	966.9	911.2	883.9
30°	1054.6	1009.5	914.7	854.3	822.3
32.5°	1016.7	962.1	865.0	793.9	764.2
35°	974.1	913.6	809.3	734.7	708.5
37.5°	932.6	867.3	757.2	675.3	645.8
40°	888.7	817.7	702.7	618.6	587.7
42.5°	843.6	767.8	648.2	560.4	530.9
45°	796.3	716.8	592.5	508.3	479.9
47.5°	751.3	667.2	539.2	455.0	428.9
50°	701.5	617.4	487.0	405.2	380.4
52.5°	652.8	564.0	437.3	359.0	336.5
55°	605.5	513.1	385.1	314.0	291.5
57.5°	556.9	462.1	338.9	272.5	253.6
60°	507.1	412.3	290.3	229.9	211.0
62.5°	458.6	363.8	248.8	192.0	182.6
65°	408.8	312.8	206.2	165.9	162.3
67.5°	361.5	265.4	165.9	145.7	142.2
70°	311.7	219.2	137.4	125.6	120.8
72.5°	264.3	176.5	114.9	105.5	103.1
75°	218.0	135.0	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.7	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929958

CATALOG NUMBER: DFN2DS-4P4F0-040DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.67	12.19	11.03	12.50	12.82	6.63	8.15	6.99	8.46	8.78
	3H	12.43	13.80	12.81	14.13	14.49	7.89	9.26	8.27	9.59	9.95
	4H	13.10	14.38	13.50	14.73	15.11	8.39	9.68	8.79	10.02	10.40
	6H	13.59	14.77	14.00	15.14	15.53	8.78	9.96	9.19	10.33	10.72
	8H	13.75	14.88	14.18	15.27	15.67	8.90	10.03	9.33	10.42	10.82
	12H	13.86	14.94	14.29	15.32	15.75	8.98	10.06	9.41	10.44	10.87
4H	2H	10.77	12.05	11.17	12.40	12.78	7.32	8.60	7.72	8.95	9.33
	3H	12.70	13.77	13.12	14.17	14.57	8.77	9.83	9.18	10.23	10.63
	4H	13.45	14.41	13.89	14.83	15.27	9.37	10.32	9.80	10.74	11.18
	6H	14.05	14.88	14.50	15.32	15.78	9.85	10.69	10.31	11.13	11.59
	8H	14.26	15.04	14.72	15.48	15.95	10.02	10.79	10.48	11.24	11.71
	12H	14.41	15.11	14.90	15.59	16.06	10.13	10.83	10.62	11.31	11.78
8H	4H	13.48	14.26	13.94	14.70	15.17	9.72	10.50	10.18	10.94	11.41
	6H	14.12	14.76	14.61	15.25	15.73	10.31	10.95	10.80	11.44	11.92
	8H	14.37	14.94	14.88	15.45	15.94	10.53	11.10	11.04	11.61	12.10
	12H	14.57	15.08	15.08	15.57	16.14	10.71	11.22	11.22	11.71	12.27
12H	4H	13.46	14.16	13.95	14.64	15.11	9.76	10.46	10.25	10.94	11.41
	6H	14.10	14.67	14.61	15.18	15.67	10.37	10.95	10.88	11.46	11.95
	8H	14.38	14.89	14.89	15.38	15.95	10.64	11.15	11.15	11.65	12.21