

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929997

Luminaire Tested: DFN2DS-4P4F0-060DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929997
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-060DS935-FLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5108.4 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 62
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929997

CATALOG NUMBER: DFN2DS-4P4F0-060DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929997

CATALOG NUMBER: DFN2DS-4P4F0-060DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1303	1303	1303
5°	1308	1289	1296
10°	1300	1276	1282
15°	1284	1259	1258
20°	1261	1234	1233
25°	1238	1204	1204
30°	1209	1176	1166
35°	1182	1142	1125
40°	1148	1108	1087
45°	1114	1075	1049
50°	1077	1041	1003
55°	1040	1000	963
60°	997	952	917
65°	951	904	862
70°	894	846	806
75°	813	779	760
80°	722	699	664
85°	588	560	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1114 cd/sqm

TEST NUMBER: P929997

CATALOG NUMBER: DFN2DS-4P4F0-060DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	3.7
10°-20°	531.7	10.4
20°-30°	781.4	15.3
30°-40°	907.5	17.8
40°-50°	906.4	17.7
50°-60°	790.4	15.5
60°-70°	584.3	11.4
70°-80°	330.6	6.5
80°-90°	87.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1502.1	29.4
0°-40°	2409.6	47.2
0°-60°	4106.3	80.4
0°-90°	5108.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5108.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2008	2008	2008	2008	2008	
5°	2008	2000	1979	1994	1991	191
15°	1911	1900	1875	1882	1873	538
25°	1730	1714	1682	1685	1682	796
35°	1492	1473	1442	1430	1421	932
45°	1214	1201	1172	1151	1143	937
55°	919	907	884	861	852	822
65°	620	608	589	572	562	613
75°	324	321	311	299	303	346
85°	79	77	75	69	68	93
90°	0	0	0	0	0	

TEST NUMBER: P929997

CATALOG NUMBER: DFN2DS-4P4F0-060DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2007.8	2007.8	2007.8	2007.8	2007.8
2.5°	2019.5	2009.8	1988.5	2007.8	2004.1
5°	2007.8	2000.2	1978.9	1994.3	1990.6
7.5°	1994.3	1982.8	1961.5	1977.1	1973.2
10°	1973.2	1959.7	1936.5	1951.9	1946.1
12.5°	1944.1	1932.6	1909.5	1919.1	1915.2
15°	1911.3	1899.8	1874.6	1882.5	1872.8
17.5°	1870.8	1859.3	1834.1	1843.7	1834.1
20°	1826.3	1814.9	1787.8	1793.5	1786.0
22.5°	1782.1	1764.6	1739.4	1739.4	1735.6
25°	1729.8	1714.5	1681.6	1685.3	1681.6
27.5°	1671.8	1658.3	1633.3	1627.6	1618.0
30°	1614.1	1598.5	1569.7	1563.9	1556.1
32.5°	1552.2	1540.8	1509.8	1498.1	1490.4
35°	1492.4	1473.2	1442.2	1430.5	1420.9
37.5°	1424.8	1407.4	1376.5	1362.9	1353.3
40°	1355.4	1339.8	1308.9	1291.7	1283.9
42.5°	1287.8	1272.2	1241.5	1222.1	1210.5
45°	1214.5	1200.9	1171.8	1150.8	1142.9
47.5°	1142.9	1129.4	1098.6	1077.2	1065.7
50°	1067.6	1058.0	1031.0	1003.9	994.2
52.5°	994.2	980.7	955.7	934.5	921.0
55°	919.1	907.4	884.3	861.1	851.5
57.5°	843.7	834.1	808.9	785.8	778.0
60°	768.3	760.8	733.8	712.4	706.7
62.5°	695.0	681.5	662.2	642.9	635.2
65°	619.8	608.2	588.9	571.5	561.8
67.5°	542.6	532.8	515.6	502.1	494.2
70°	471.1	463.4	445.9	432.4	424.8
72.5°	397.8	390.0	380.4	366.9	361.1
75°	324.2	320.6	310.7	299.3	303.2
77.5°	258.7	250.9	247.0	241.3	235.6
80°	193.2	191.1	187.2	181.5	177.6
82.5°	131.3	131.3	129.4	121.7	121.7
85°	79.0	77.2	75.3	69.4	67.6
87.5°	34.8	31.0	27.0	21.3	19.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929997

CATALOG NUMBER: DFN2DS-4P4F0-060DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.20	13.81	12.57	14.13	14.44	11.76	13.37	12.12	13.68	14.00
	3H	13.95	15.41	14.33	15.73	16.09	13.46	14.91	13.84	15.24	15.60
	4H	14.60	15.97	15.00	16.31	16.69	14.10	15.47	14.50	15.82	16.20
	6H	15.07	16.34	15.48	16.70	17.09	14.57	15.83	14.98	16.20	16.59
	8H	15.21	16.42	15.63	16.81	17.21	14.71	15.92	15.13	16.31	16.71
	12H	15.30	16.46	15.73	16.84	17.27	14.79	15.95	15.22	16.33	16.76
4H	2H	12.76	14.13	13.16	14.48	14.85	12.41	13.78	12.81	14.13	14.50
	3H	14.74	15.88	15.15	16.28	16.68	14.33	15.48	14.74	15.87	16.27
	4H	15.51	16.55	15.94	16.96	17.40	15.09	16.13	15.52	16.54	16.98
	6H	16.11	17.01	16.56	17.46	17.91	15.68	16.58	16.13	17.02	17.48
	8H	16.30	17.15	16.76	17.59	18.05	15.86	16.71	16.32	17.15	17.62
	12H	16.43	17.19	16.91	17.67	18.14	15.98	16.74	16.46	17.21	17.68
8H	4H	15.79	16.63	16.25	17.08	17.54	15.41	16.26	15.87	16.70	17.17
	6H	16.50	17.20	16.99	17.69	18.17	16.12	16.82	16.61	17.31	17.79
	8H	16.76	17.39	17.27	17.90	18.38	16.37	17.00	16.88	17.51	17.99
	12H	16.96	17.52	17.47	18.01	18.57	16.55	17.10	17.05	17.60	18.16
12H	4H	15.81	16.57	16.29	17.05	17.52	15.45	16.21	15.93	16.68	17.15
	6H	16.55	17.18	17.06	17.68	18.17	16.18	16.81	16.69	17.32	17.80
	8H	16.86	17.42	17.37	17.91	18.47	16.48	17.04	16.99	17.53	18.09

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7