

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930467

Luminaire Tested: DFN2DS-PN2F0-040DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930467
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-040DS940-FLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3532.3 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930467

CATALOG NUMBER: DFN2DS-PN2F0-040DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930467

CATALOG NUMBER: DFN2DS-PN2F0-040DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3007	3007	3007
5°	3018	2975	2992
10°	3001	2945	2960
15°	2963	2907	2904
20°	2911	2849	2847
25°	2858	2779	2779
30°	2791	2715	2691
35°	2729	2637	2598
40°	2650	2559	2510
45°	2572	2482	2421
50°	2487	2402	2317
55°	2400	2309	2223
60°	2301	2198	2116
65°	2197	2087	1992
70°	2063	1953	1860
75°	1876	1798	1754
80°	1665	1614	1532
85°	1359	1295	1161

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2572 cd/sqm

TEST NUMBER: P930467

CATALOG NUMBER: DFN2DS-PN2F0-040DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.7	3.7
10°-20°	367.6	10.4
20°-30°	540.3	15.3
30°-40°	627.5	17.8
40°-50°	626.8	17.7
50°-60°	546.5	15.5
60°-70°	404.0	11.4
70°-80°	228.6	6.5
80°-90°	60.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1038.6	29.4
0°-40°	1666.2	47.2
0°-60°	2839.4	80.4
0°-90°	3532.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3532.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1388	1383	1368	1379	1376	132
15°	1322	1314	1296	1302	1295	372
25°	1196	1186	1163	1165	1163	550
35°	1032	1019	997	989	982	644
45°	840	830	810	796	790	648
55°	636	627	612	595	589	568
65°	429	420	407	395	389	424
75°	224	222	215	207	210	239
85°	55	53	52	48	47	64
90°	0	0	0	0	0	

TEST NUMBER: P930467

CATALOG NUMBER: DFN2DS-PN2F0-040DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1396.4	1389.7	1375.0	1388.3	1385.8
5°	1388.3	1383.0	1368.3	1378.9	1376.4
7.5°	1378.9	1371.0	1356.3	1367.1	1364.4
10°	1364.4	1355.0	1339.1	1349.7	1345.7
12.5°	1344.2	1336.3	1320.3	1327.0	1324.3
15°	1321.6	1313.6	1296.3	1301.6	1295.0
17.5°	1293.6	1285.6	1268.2	1274.8	1268.2
20°	1262.8	1254.9	1236.2	1240.1	1235.0
22.5°	1232.2	1220.2	1202.8	1202.8	1200.1
25°	1196.1	1185.5	1162.8	1165.4	1162.8
27.5°	1156.0	1146.7	1129.5	1125.4	1118.8
30°	1116.1	1105.4	1085.4	1081.4	1076.0
32.5°	1073.3	1065.4	1044.0	1036.0	1030.5
35°	1032.0	1018.7	997.3	989.2	982.5
37.5°	985.2	973.2	951.8	942.5	935.8
40°	937.2	926.4	905.0	893.2	887.8
42.5°	890.5	879.7	858.5	845.0	837.1
45°	839.7	830.5	810.3	795.8	790.3
47.5°	790.3	780.9	759.6	744.9	737.0
50°	738.2	731.5	712.9	694.2	687.5
52.5°	687.5	678.2	660.9	646.2	636.8
55°	635.6	627.4	611.5	595.4	588.8
57.5°	583.4	576.8	559.3	543.3	538.0
60°	531.3	526.0	507.4	492.7	488.6
62.5°	480.6	471.2	458.0	444.6	439.2
65°	428.6	420.5	407.2	395.2	388.6
67.5°	375.2	368.4	356.5	347.2	341.8
70°	325.8	320.4	308.4	299.0	293.7
72.5°	275.1	269.7	263.1	253.7	249.7
75°	224.2	221.7	214.9	206.9	209.6
77.5°	178.8	173.5	170.8	166.8	162.9
80°	133.5	132.1	129.4	125.5	122.8
82.5°	90.8	90.8	89.6	84.1	84.1
85°	54.7	53.4	52.1	48.0	46.7
87.5°	24.1	21.4	18.7	14.7	13.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930467

CATALOG NUMBER: DFN2DS-PN2F0-040DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.11	16.72	15.47	17.03	17.35	14.66	16.27	15.03	16.59	16.90
	3H	16.86	18.31	17.23	18.64	19.00	16.37	17.82	16.74	18.15	18.51
	4H	17.50	18.87	17.90	19.22	19.60	17.01	18.38	17.41	18.73	19.10
	6H	17.97	19.24	18.38	19.61	20.00	17.47	18.74	17.88	19.10	19.50
	8H	18.12	19.33	18.54	19.72	20.12	17.61	18.82	18.04	19.21	19.61
	12H	18.21	19.37	18.64	19.75	20.18	17.69	18.85	18.12	19.24	19.66
4H	2H	15.67	17.04	16.07	17.39	17.76	15.32	16.68	15.71	17.03	17.41
	3H	17.64	18.79	18.05	19.19	19.59	17.24	18.38	17.65	18.78	19.18
	4H	18.42	19.46	18.85	19.87	20.31	18.00	19.03	18.43	19.45	19.88
	6H	19.02	19.92	19.47	20.36	20.82	18.58	19.49	19.04	19.93	20.39
	8H	19.21	20.05	19.67	20.49	20.96	18.77	19.61	19.23	20.06	20.52
	12H	19.34	20.10	19.82	20.57	21.04	18.88	19.64	19.37	20.12	20.59
8H	4H	18.69	19.54	19.15	19.98	20.45	18.32	19.17	18.78	19.61	20.07
	6H	19.41	20.11	19.90	20.60	21.07	19.03	19.73	19.52	20.22	20.69
	8H	19.67	20.30	20.18	20.80	21.29	19.27	19.91	19.78	20.41	20.90
	12H	19.87	20.42	20.37	20.91	21.48	19.45	20.01	19.96	20.50	21.06
12H	4H	18.72	19.48	19.20	19.96	20.42	18.35	19.11	18.83	19.59	20.06
	6H	19.45	20.08	19.96	20.59	21.08	19.08	19.72	19.59	20.22	20.71
	8H	19.77	20.32	20.27	20.81	21.38	19.39	19.95	19.90	20.44	21.00