

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930504

Luminaire Tested: DFN2DS-PN2F0-060DS940-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930504
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-060DS940-RLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4549.2 lumens
Efficiency: N/A
Efficacy: 67.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 67.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930504

CATALOG NUMBER: DFN2DS-PN2F0-060DS940-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930504

CATALOG NUMBER: DFN2DS-PN2F0-060DS940-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4791	4791	4791
5°	4809	4731	4757
10°	4772	4654	4614
15°	4718	4515	4385
20°	4642	4318	4102
25°	4564	4095	3827
30°	4456	3865	3474
35°	4351	3615	3165
40°	4245	3356	2807
45°	4120	3066	2483
50°	3993	2772	2166
55°	3863	2456	1860
60°	3711	2124	1544
65°	3540	1785	1405
70°	3334	1470	1292
75°	3082	1340	1207
80°	2720	1197	1099
85°	2137	944	944

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4120 cd/sqm

TEST NUMBER: P930504

CATALOG NUMBER: DFN2DS-PN2F0-060DS940-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.3	4.6
10°-20°	569.1	12.5
20°-30°	799.0	17.6
30°-40°	871.0	19.1
40°-50°	800.5	17.6
50°-60°	628.7	13.8
60°-70°	409.2	9.0
70°-80°	210.6	4.6
80°-90°	53.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1575.4	34.6
0°-40°	2446.4	53.8
0°-60°	3875.6	85.2
0°-90°	4549.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4549.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2212	2212	2212	2212	2212	
5°	2212	2202	2176	2194	2188	210
15°	2104	2082	2014	1976	1956	593
25°	1910	1846	1714	1632	1601	878
35°	1646	1543	1367	1241	1197	1030
45°	1345	1211	1001	859	811	1039
55°	1023	867	650	531	492	914
65°	691	528	348	280	274	685
75°	368	228	160	146	144	390
85°	86	44	38	38	38	103
90°	0	0	0	0	0	

TEST NUMBER: P930504

CATALOG NUMBER: DFN2DS-PN2F0-060DS940-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2212.0	2212.0	2212.0	2212.0	2212.0
2.5°	2222.0	2212.0	2189.9	2210.0	2206.0
5°	2212.0	2202.0	2175.9	2194.0	2188.0
7.5°	2194.0	2182.0	2154.0	2161.9	2151.9
10°	2169.9	2155.9	2116.0	2109.8	2097.9
12.5°	2140.0	2121.9	2067.7	2055.9	2033.8
15°	2103.9	2081.7	2013.8	1975.8	1955.8
17.5°	2061.9	2029.7	1945.6	1901.7	1869.6
20°	2013.8	1973.6	1873.6	1823.7	1779.5
22.5°	1961.8	1915.7	1799.5	1731.6	1701.6
25°	1909.8	1845.6	1713.5	1631.6	1601.4
27.5°	1847.8	1779.5	1633.4	1539.3	1493.3
30°	1781.7	1705.4	1545.3	1443.3	1389.2
32.5°	1717.5	1625.4	1461.5	1341.2	1291.1
35°	1645.6	1543.4	1367.3	1241.1	1197.0
37.5°	1575.5	1465.2	1279.2	1141.0	1091.0
40°	1501.3	1381.4	1187.0	1044.9	992.9
42.5°	1425.3	1297.2	1095.0	946.8	896.9
45°	1345.2	1211.0	1001.0	858.6	810.6
47.5°	1269.2	1127.1	910.9	768.6	724.7
50°	1185.1	1043.0	822.8	684.5	642.7
52.5°	1102.9	952.7	738.7	606.6	568.6
55°	1022.9	866.8	650.5	530.6	492.5
57.5°	940.9	780.7	572.6	460.5	428.3
60°	856.8	696.7	490.4	388.5	356.4
62.5°	774.8	614.7	420.3	324.3	308.4
65°	690.7	528.4	348.3	280.4	274.2
67.5°	610.6	448.3	280.4	246.2	240.2
70°	526.5	370.4	232.1	212.2	204.1
72.5°	446.4	298.2	194.1	178.2	174.1
75°	368.3	228.1	160.1	146.1	144.2
77.5°	290.3	162.1	126.1	118.1	114.1
80°	218.1	116.1	96.0	88.1	88.1
82.5°	152.1	78.1	66.0	62.0	62.0
85°	86.0	44.0	38.0	38.0	38.0
87.5°	32.1	16.0	16.0	14.0	14.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930504

CATALOG NUMBER: DFN2DS-PN2F0-060DS940-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.68	18.20	17.04	18.51	18.83	12.64	14.16	13.00	14.47	14.79
	3H	18.44	19.81	18.82	20.14	20.50	13.90	15.27	14.28	15.60	15.96
	4H	19.11	20.39	19.51	20.74	21.12	14.41	15.69	14.81	16.04	16.41
	6H	19.60	20.78	20.01	21.15	21.54	14.79	15.97	15.20	16.34	16.73
	8H	19.76	20.89	20.19	21.28	21.68	14.91	16.04	15.34	16.43	16.83
	12H	19.87	20.95	20.30	21.33	21.76	14.99	16.07	15.42	16.45	16.88
4H	2H	16.78	18.06	17.18	18.41	18.79	13.33	14.62	13.73	14.96	15.34
	3H	18.72	19.78	19.13	20.18	20.58	14.78	15.84	15.19	16.24	16.64
	4H	19.46	20.42	19.90	20.84	21.28	15.38	16.33	15.81	16.75	17.19
	6H	20.06	20.89	20.51	21.33	21.79	15.87	16.70	16.32	17.14	17.60
	8H	20.27	21.05	20.73	21.49	21.96	16.03	16.80	16.49	17.25	17.72
	12H	20.42	21.12	20.91	21.60	22.07	16.14	16.84	16.63	17.32	17.79
8H	4H	19.49	20.27	19.95	20.71	21.18	15.73	16.51	16.19	16.95	17.42
	6H	20.13	20.77	20.62	21.26	21.74	16.32	16.96	16.81	17.45	17.93
	8H	20.38	20.95	20.89	21.46	21.95	16.54	17.11	17.05	17.62	18.11
	12H	20.58	21.09	21.09	21.58	22.15	16.72	17.23	17.23	17.72	18.28
12H	4H	19.47	20.17	19.96	20.65	21.12	15.77	16.47	16.26	16.95	17.42
	6H	20.11	20.68	20.62	21.19	21.68	16.38	16.96	16.89	17.47	17.96
	8H	20.39	20.90	20.90	21.39	21.96	16.65	17.16	17.16	17.66	18.22