

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930469

Luminaire Tested: DFN2DS-PN2F0-040DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930469
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-040DS950-FLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3742.2 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930469

CATALOG NUMBER: DFN2DS-PN2F0-040DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930469

CATALOG NUMBER: DFN2DS-PN2F0-040DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3186	3186	3186
5°	3198	3152	3170
10°	3179	3120	3135
15°	3139	3079	3076
20°	3083	3019	3016
25°	3028	2944	2944
30°	2957	2876	2851
35°	2891	2793	2752
40°	2807	2711	2659
45°	2725	2629	2565
50°	2635	2545	2454
55°	2542	2446	2356
60°	2438	2328	2243
65°	2327	2211	2109
70°	2185	2069	1971
75°	1988	1905	1859
80°	1765	1710	1623
85°	1439	1372	1230

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2725 cd/sqm

TEST NUMBER: P930469

CATALOG NUMBER: DFN2DS-PN2F0-040DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.4	3.7
10°-20°	389.5	10.4
20°-30°	572.4	15.3
30°-40°	664.8	17.8
40°-50°	664.0	17.7
50°-60°	579.0	15.5
60°-70°	428.0	11.4
70°-80°	242.2	6.5
80°-90°	63.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1100.3	29.4
0°-40°	1765.2	47.2
0°-60°	3008.1	80.4
0°-90°	3742.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3742.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1471	1471	1471	1471	1471	
5°	1471	1465	1450	1461	1458	140
15°	1400	1392	1373	1379	1372	394
25°	1267	1256	1232	1235	1232	583
35°	1093	1079	1056	1048	1041	683
45°	890	880	858	843	837	687
55°	673	665	648	631	624	602
65°	454	446	431	419	412	449
75°	238	235	228	219	222	254
85°	58	57	55	51	50	68
90°	0	0	0	0	0	

TEST NUMBER: P930469

CATALOG NUMBER: DFN2DS-PN2F0-040DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1470.8	1470.8	1470.8	1470.8	1470.8
2.5°	1479.4	1472.3	1456.7	1470.8	1468.2
5°	1470.8	1465.2	1449.6	1460.9	1458.2
7.5°	1460.9	1452.5	1436.9	1448.3	1445.5
10°	1445.5	1435.5	1418.6	1429.9	1425.6
12.5°	1424.1	1415.7	1398.8	1405.9	1402.9
15°	1400.1	1391.7	1373.3	1378.9	1372.0
17.5°	1370.4	1362.0	1343.6	1350.6	1343.6
20°	1337.8	1329.4	1309.7	1313.8	1308.4
22.5°	1305.4	1292.7	1274.2	1274.2	1271.4
25°	1267.2	1255.9	1231.9	1234.6	1231.9
27.5°	1224.7	1214.8	1196.6	1192.3	1185.3
30°	1182.4	1171.0	1149.9	1145.6	1140.0
32.5°	1137.1	1128.7	1106.0	1097.5	1091.8
35°	1093.3	1079.2	1056.5	1048.0	1040.9
37.5°	1043.8	1031.0	1008.3	998.5	991.4
40°	992.9	981.5	958.8	946.2	940.6
42.5°	943.4	932.0	909.5	895.2	886.8
45°	889.6	879.8	858.4	843.0	837.3
47.5°	837.3	827.3	804.8	789.2	780.8
50°	782.1	775.0	755.2	735.4	728.3
52.5°	728.3	718.5	700.2	684.6	674.6
55°	673.3	664.7	647.8	630.8	623.8
57.5°	618.0	611.0	592.5	575.6	569.9
60°	562.8	557.3	537.5	521.9	517.7
62.5°	509.2	499.2	485.2	471.0	465.3
65°	454.1	445.5	431.4	418.6	411.6
67.5°	397.5	390.3	377.7	367.8	362.1
70°	345.1	339.4	326.7	316.8	311.2
72.5°	291.4	285.7	278.7	268.8	264.5
75°	237.6	234.8	227.7	219.2	222.1
77.5°	189.5	183.8	181.0	176.7	172.6
80°	141.5	140.0	137.1	133.0	130.1
82.5°	96.2	96.2	94.9	89.1	89.1
85°	57.9	56.6	55.2	50.8	49.5
87.5°	25.5	22.7	19.8	15.6	14.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930469

CATALOG NUMBER: DFN2DS-PN2F0-040DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.31	16.92	15.67	17.23	17.55	14.86	16.47	15.23	16.79	17.10
	3H	17.06	18.51	17.43	18.84	19.20	16.57	18.02	16.94	18.35	18.71
	4H	17.70	19.07	18.10	19.42	19.80	17.21	18.58	17.61	18.93	19.30
	6H	18.17	19.44	18.58	19.81	20.20	17.67	18.94	18.08	19.31	19.70
	8H	18.32	19.53	18.74	19.92	20.32	17.81	19.02	18.24	19.41	19.81
	12H	18.41	19.57	18.84	19.95	20.38	17.89	19.05	18.32	19.44	19.87
4H	2H	15.87	17.24	16.27	17.59	17.96	15.52	16.88	15.91	17.23	17.61
	3H	17.84	18.99	18.25	19.39	19.79	17.44	18.58	17.85	18.98	19.38
	4H	18.62	19.66	19.05	20.07	20.51	18.20	19.23	18.63	19.65	20.08
	6H	19.22	20.12	19.67	20.56	21.02	18.78	19.69	19.24	20.13	20.59
	8H	19.41	20.25	19.87	20.70	21.16	18.97	19.81	19.43	20.26	20.72
	12H	19.54	20.30	20.02	20.77	21.24	19.09	19.85	19.57	20.32	20.79
8H	4H	18.89	19.74	19.35	20.18	20.65	18.52	19.37	18.98	19.81	20.27
	6H	19.61	20.31	20.10	20.80	21.27	19.23	19.93	19.72	20.42	20.89
	8H	19.87	20.50	20.38	21.00	21.49	19.48	20.11	19.99	20.61	21.10
	12H	20.07	20.62	20.57	21.12	21.68	19.65	20.21	20.16	20.70	21.26
12H	4H	18.92	19.68	19.40	20.16	20.62	18.55	19.31	19.04	19.79	20.26
	6H	19.65	20.29	20.16	20.79	21.28	19.28	19.92	19.79	20.42	20.91
	8H	19.97	20.52	20.47	21.02	21.58	19.59	20.15	20.10	20.64	21.20

END OF REPORT