

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929981

Luminaire Tested: DFN2DS-4P4F0-050DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929981
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-050DS940-FLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4415.4 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 50.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929981

CATALOG NUMBER: DFN2DS-4P4F0-050DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929981

CATALOG NUMBER: DFN2DS-4P4F0-050DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1126	1126	1126
5°	1130	1114	1120
10°	1123	1103	1108
15°	1110	1088	1087
20°	1090	1067	1066
25°	1070	1040	1040
30°	1045	1016	1008
35°	1022	987	973
40°	992	958	940
45°	963	929	906
50°	931	899	867
55°	899	864	832
60°	862	823	793
65°	822	781	745
70°	772	731	697
75°	703	673	657
80°	624	604	573
85°	508	485	435

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 963 cd/sqm

TEST NUMBER: P929981

CATALOG NUMBER: DFN2DS-4P4F0-050DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.3	3.7
10°-20°	459.6	10.4
20°-30°	675.4	15.3
30°-40°	784.4	17.8
40°-50°	783.4	17.7
50°-60°	683.1	15.5
60°-70°	505.0	11.4
70°-80°	285.7	6.5
80°-90°	75.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1298.3	29.4
0°-40°	2082.7	47.2
0°-60°	3549.3	80.4
0°-90°	4415.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4415.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1735	1735	1735	1735	1735	
5°	1735	1729	1710	1724	1721	165
15°	1652	1642	1620	1627	1619	465
25°	1495	1482	1454	1457	1454	688
35°	1290	1273	1247	1236	1228	806
45°	1050	1038	1013	995	988	810
55°	794	784	764	744	736	710
65°	536	526	509	494	486	530
75°	280	277	269	259	262	299
85°	68	67	65	60	58	80
90°	0	0	0	0	0	

TEST NUMBER: P929981

CATALOG NUMBER: DFN2DS-4P4F0-050DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1735.4	1735.4	1735.4	1735.4	1735.4
2.5°	1745.5	1737.2	1718.8	1735.4	1732.3
5°	1735.4	1728.9	1710.4	1723.7	1720.6
7.5°	1723.7	1713.8	1695.4	1708.9	1705.5
10°	1705.5	1693.8	1673.8	1687.0	1682.1
12.5°	1680.3	1670.4	1650.5	1658.8	1655.4
15°	1652.0	1642.1	1620.3	1627.1	1618.7
17.5°	1616.9	1607.0	1585.3	1593.6	1585.3
20°	1578.6	1568.7	1545.3	1550.2	1543.7
22.5°	1540.3	1525.2	1503.5	1503.5	1500.1
25°	1495.2	1481.9	1453.5	1456.7	1453.5
27.5°	1445.0	1433.4	1411.8	1406.8	1398.5
30°	1395.1	1381.7	1356.7	1351.7	1345.0
32.5°	1341.7	1331.8	1305.0	1294.9	1288.2
35°	1289.9	1273.3	1246.6	1236.5	1228.2
37.5°	1231.5	1216.5	1189.7	1178.1	1169.8
40°	1171.6	1158.1	1131.3	1116.4	1109.7
42.5°	1113.1	1099.7	1073.1	1056.2	1046.3
45°	1049.7	1038.0	1012.9	994.7	987.9
47.5°	987.9	976.2	949.5	931.1	921.2
50°	922.8	914.5	891.1	867.7	859.4
52.5°	859.4	847.7	826.1	807.7	796.0
55°	794.4	784.3	764.3	744.3	736.0
57.5°	729.2	720.9	699.1	679.2	672.4
60°	664.1	657.6	634.2	615.7	610.8
62.5°	600.8	589.1	572.4	555.7	549.0
65°	535.7	525.7	509.0	494.0	485.6
67.5°	469.0	460.5	445.6	434.0	427.2
70°	407.2	400.5	385.4	373.7	367.2
72.5°	343.9	337.1	328.8	317.1	312.1
75°	280.3	277.1	268.6	258.7	262.1
77.5°	223.6	216.8	213.5	208.5	203.6
80°	167.0	165.2	161.8	156.9	153.5
82.5°	113.5	113.5	111.9	105.2	105.2
85°	68.3	66.7	65.1	60.0	58.4
87.5°	30.1	26.8	23.4	18.4	16.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929981

CATALOG NUMBER: DFN2DS-4P4F0-050DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.69	13.30	12.06	13.62	13.93	11.25	12.86	11.62	13.18	13.49
	3H	13.44	14.90	13.82	15.23	15.59	12.95	14.41	13.33	14.73	15.10
	4H	14.09	15.46	14.49	15.81	16.18	13.60	14.97	13.99	15.31	15.69
	6H	14.56	15.83	14.97	16.19	16.58	14.06	15.33	14.47	15.69	16.08
	8H	14.70	15.91	15.13	16.30	16.70	14.20	15.41	14.62	15.80	16.20
	12H	14.79	15.95	15.22	16.33	16.76	14.28	15.44	14.71	15.82	16.25
4H	2H	12.25	13.62	12.65	13.97	14.35	11.90	13.27	12.30	13.62	14.00
	3H	14.23	15.38	14.64	15.77	16.17	13.82	14.97	14.23	15.37	15.77
	4H	15.01	16.04	15.44	16.46	16.89	14.58	15.62	15.01	16.03	16.47
	6H	15.60	16.51	16.06	16.95	17.40	15.17	16.08	15.62	16.52	16.97
	8H	15.79	16.64	16.25	17.08	17.55	15.35	16.20	15.82	16.64	17.11
	12H	15.92	16.68	16.40	17.16	17.63	15.47	16.23	15.95	16.71	17.18
8H	4H	15.28	16.13	15.74	16.57	17.03	14.91	15.75	15.37	16.19	16.66
	6H	15.99	16.70	16.49	17.19	17.66	15.61	16.32	16.11	16.80	17.28
	8H	16.25	16.88	16.76	17.39	17.88	15.86	16.49	16.37	17.00	17.49
	12H	16.45	17.01	16.96	17.50	18.06	16.04	16.60	16.55	17.09	17.65
12H	4H	15.31	16.07	15.79	16.54	17.01	14.94	15.70	15.42	16.18	16.65
	6H	16.04	16.67	16.55	17.18	17.66	15.67	16.30	16.18	16.81	17.30
	8H	16.35	16.91	16.86	17.40	17.96	15.98	16.53	16.48	17.02	17.59