

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930470

Luminaire Tested: DFN2DS-PN2F0-040DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930470
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-040DS950-RLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3213.0 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 42.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930470

CATALOG NUMBER: DFN2DS-PN2F0-040DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930470

CATALOG NUMBER: DFN2DS-PN2F0-040DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3384	3384	3384
5°	3397	3341	3360
10°	3371	3287	3259
15°	3332	3189	3097
20°	3278	3050	2897
25°	3223	2892	2703
30°	3147	2730	2454
35°	3073	2553	2235
40°	2998	2370	1983
45°	2910	2166	1754
50°	2820	1958	1529
55°	2728	1735	1314
60°	2621	1500	1090
65°	2500	1261	992
70°	2355	1039	913
75°	2177	946	853
80°	1921	846	777
85°	1511	666	666

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2910 cd/sqm

TEST NUMBER: P930470

CATALOG NUMBER: DFN2DS-PN2F0-040DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.4	4.6
10°-20°	401.9	12.5
20°-30°	564.3	17.6
30°-40°	615.1	19.1
40°-50°	565.4	17.6
50°-60°	444.0	13.8
60°-70°	289.0	9.0
70°-80°	148.8	4.6
80°-90°	38.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1112.7	34.6
0°-40°	1727.8	53.8
0°-60°	2737.2	85.2
0°-90°	3213.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3213.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1562	1562	1562	1562	1562	
5°	1562	1555	1537	1550	1545	148
15°	1486	1470	1422	1396	1381	419
25°	1349	1304	1210	1152	1131	620
35°	1162	1090	966	877	845	727
45°	950	855	707	606	573	734
55°	722	612	460	375	348	646
65°	488	373	246	198	194	484
75°	260	161	113	103	102	275
85°	61	31	27	27	27	73
90°	0	0	0	0	0	

TEST NUMBER: P930470

CATALOG NUMBER: DFN2DS-PN2F0-040DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1562.3	1562.3	1562.3	1562.3	1562.3
2.5°	1569.4	1562.3	1546.7	1561.0	1558.0
5°	1562.3	1555.2	1536.8	1549.5	1545.4
7.5°	1549.5	1541.1	1521.4	1526.8	1519.8
10°	1532.6	1522.7	1494.4	1490.1	1481.8
12.5°	1511.4	1498.7	1460.4	1452.0	1436.4
15°	1485.9	1470.3	1422.3	1395.5	1381.4
17.5°	1456.2	1433.6	1374.1	1343.1	1320.4
20°	1422.3	1394.0	1323.3	1288.0	1256.8
22.5°	1385.6	1353.1	1270.9	1222.9	1201.9
25°	1348.8	1303.5	1210.2	1152.3	1131.0
27.5°	1305.0	1256.8	1153.7	1087.2	1054.6
30°	1258.4	1204.5	1091.4	1019.4	981.2
32.5°	1213.1	1148.0	1032.1	947.3	911.8
35°	1162.3	1090.1	965.7	876.6	845.4
37.5°	1112.7	1034.9	903.4	805.8	770.6
40°	1060.4	975.6	838.4	738.0	701.3
42.5°	1006.6	916.2	773.4	668.7	633.4
45°	950.1	855.3	707.0	606.5	572.6
47.5°	896.4	796.1	643.4	542.9	511.8
50°	837.0	736.6	581.1	483.5	453.9
52.5°	779.0	672.9	521.7	428.4	401.5
55°	722.5	612.2	459.5	374.7	347.9
57.5°	664.5	551.4	404.4	325.2	302.6
60°	605.1	492.0	346.3	274.3	251.7
62.5°	547.2	434.1	296.8	229.1	217.8
65°	487.8	373.2	246.0	198.0	193.6
67.5°	431.3	316.7	198.0	173.9	169.6
70°	371.9	261.6	164.0	149.9	144.1
72.5°	315.3	210.6	137.1	125.9	123.0
75°	260.1	161.1	113.1	103.2	101.9
77.5°	205.1	114.4	89.1	83.4	80.5
80°	154.0	82.0	67.8	62.3	62.3
82.5°	107.4	55.2	46.7	43.8	43.8
85°	60.8	31.1	26.8	26.8	26.8
87.5°	22.7	11.2	11.2	9.9	9.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930470

CATALOG NUMBER: DFN2DS-PN2F0-040DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.47	16.99	15.83	17.30	17.62	11.43	12.95	11.80	13.27	13.58
	3H	17.24	18.60	17.61	18.93	19.29	12.70	14.06	13.07	14.39	14.75
	4H	17.90	19.18	18.30	19.53	19.91	13.20	14.48	13.60	14.83	15.21
	6H	18.39	19.57	18.80	19.94	20.33	13.58	14.76	13.99	15.13	15.52
	8H	18.56	19.68	18.98	20.07	20.47	13.70	14.83	14.13	15.22	15.62
	12H	18.66	19.74	19.09	20.12	20.55	13.78	14.86	14.21	15.24	15.67
4H	2H	15.57	16.85	15.97	17.20	17.58	12.13	13.41	12.53	13.76	14.13
	3H	17.51	18.57	17.92	18.97	19.37	13.57	14.63	13.98	15.03	15.43
	4H	18.26	19.21	18.69	19.63	20.07	14.17	15.13	14.60	15.54	15.98
	6H	18.85	19.68	19.31	20.12	20.58	14.66	15.49	15.11	15.93	16.39
	8H	19.06	19.84	19.53	20.28	20.75	14.82	15.60	15.28	16.04	16.51
	12H	19.22	19.91	19.70	20.39	20.86	14.94	15.63	15.42	16.11	16.58
8H	4H	18.28	19.06	18.74	19.50	19.97	14.52	15.30	14.99	15.74	16.21
	6H	18.92	19.56	19.41	20.05	20.53	15.11	15.75	15.61	16.24	16.72
	8H	19.17	19.74	19.68	20.25	20.74	15.33	15.91	15.84	16.42	16.90
	12H	19.37	19.88	19.88	20.37	20.94	15.51	16.02	16.02	16.51	17.08
12H	4H	18.27	18.96	18.75	19.44	19.91	14.57	15.26	15.05	15.74	16.21
	6H	18.90	19.48	19.41	19.99	20.47	15.17	15.75	15.69	16.26	16.75
	8H	19.18	19.69	19.69	20.19	20.75	15.45	15.96	15.96	16.45	17.01

END OF REPORT