

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930487

Luminaire Tested: DFN2DS-PN2F0-050DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930487
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-050DS950-FLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4677.7 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 54
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930487

CATALOG NUMBER: DFN2DS-PN2F0-050DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930487

CATALOG NUMBER: DFN2DS-PN2F0-050DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3982	3982	3982
5°	3997	3940	3963
10°	3974	3900	3919
15°	3924	3849	3845
20°	3855	3773	3769
25°	3785	3680	3680
30°	3696	3595	3564
35°	3613	3492	3440
40°	3509	3389	3324
45°	3406	3287	3206
50°	3294	3181	3068
55°	3178	3057	2944
60°	3048	2910	2803
65°	2909	2763	2637
70°	2732	2586	2464
75°	2485	2381	2323
80°	2206	2138	2028
85°	1799	1715	1538

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3406 cd/sqm

TEST NUMBER: P930487

CATALOG NUMBER: DFN2DS-PN2F0-050DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.0	3.7
10°-20°	486.9	10.4
20°-30°	715.5	15.3
30°-40°	831.0	17.8
40°-50°	830.0	17.7
50°-60°	723.7	15.5
60°-70°	535.0	11.4
70°-80°	302.7	6.5
80°-90°	79.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1375.4	29.4
0°-40°	2206.5	47.2
0°-60°	3760.2	80.4
0°-90°	4677.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4677.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1838	1838	1838	1838	1838	
5°	1838	1832	1812	1826	1823	175
15°	1750	1740	1717	1724	1715	493
25°	1584	1570	1540	1543	1540	729
35°	1367	1349	1321	1310	1301	853
45°	1112	1100	1073	1054	1047	858
55°	842	831	810	788	780	752
65°	568	557	539	523	514	561
75°	297	294	284	274	278	317
85°	72	71	69	64	62	85
90°	0	0	0	0	0	

TEST NUMBER: P930487

CATALOG NUMBER: DFN2DS-PN2F0-050DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1838.5	1838.5	1838.5	1838.5	1838.5
2.5°	1849.2	1840.4	1820.9	1838.5	1835.2
5°	1838.5	1831.6	1812.0	1826.1	1822.8
7.5°	1826.1	1815.6	1796.2	1810.4	1806.8
10°	1806.8	1794.5	1773.3	1787.3	1782.1
12.5°	1780.2	1769.7	1748.5	1757.3	1753.7
15°	1750.1	1739.7	1716.6	1723.8	1714.9
17.5°	1713.0	1702.5	1679.5	1688.2	1679.5
20°	1672.4	1661.9	1637.1	1642.3	1635.4
22.5°	1631.8	1615.9	1592.8	1592.8	1589.2
25°	1584.0	1569.9	1539.9	1543.3	1539.9
27.5°	1530.9	1518.5	1495.7	1490.4	1481.6
30°	1478.0	1463.8	1437.3	1432.1	1425.0
32.5°	1421.4	1410.9	1382.5	1371.9	1364.8
35°	1366.6	1349.0	1320.6	1310.0	1301.2
37.5°	1304.7	1288.8	1260.4	1248.1	1239.3
40°	1241.2	1226.9	1198.5	1182.8	1175.7
42.5°	1179.3	1165.0	1136.8	1119.0	1108.5
45°	1112.1	1099.7	1073.0	1053.8	1046.6
47.5°	1046.6	1034.2	1006.0	986.4	975.9
50°	977.6	968.8	944.1	919.3	910.4
52.5°	910.4	898.0	875.2	855.7	843.3
55°	841.6	830.9	809.7	788.5	779.7
57.5°	772.5	763.7	740.7	719.5	712.3
60°	703.6	696.7	671.9	652.3	647.1
62.5°	636.5	624.1	606.4	588.7	581.6
65°	567.6	556.9	539.2	523.3	514.5
67.5°	496.9	487.9	472.1	459.7	452.6
70°	431.4	424.3	408.3	396.0	389.1
72.5°	364.3	357.1	348.3	335.9	330.7
75°	296.9	293.5	284.5	274.0	277.6
77.5°	236.9	229.7	226.2	220.9	215.7
80°	176.9	175.0	171.4	166.2	162.6
82.5°	120.2	120.2	118.5	111.4	111.4
85°	72.4	70.7	69.0	63.6	61.9
87.5°	31.8	28.4	24.8	19.5	17.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930487

CATALOG NUMBER: DFN2DS-PN2F0-050DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.08	17.69	16.45	18.01	18.32	15.64	17.25	16.00	17.56	17.88
	3H	17.83	19.29	18.21	19.61	19.97	17.34	18.80	17.72	19.12	19.48
	4H	18.48	19.85	18.88	20.20	20.57	17.98	19.35	18.38	19.70	20.08
	6H	18.95	20.22	19.36	20.58	20.97	18.45	19.72	18.86	20.08	20.47
	8H	19.09	20.30	19.52	20.69	21.09	18.59	19.80	19.01	20.19	20.59
	12H	19.18	20.34	19.61	20.72	21.15	18.67	19.83	19.10	20.21	20.64
4H	2H	16.64	18.01	17.04	18.36	18.74	16.29	17.66	16.69	18.01	18.38
	3H	18.62	19.77	19.03	20.16	20.56	18.21	19.36	18.62	19.76	20.16
	4H	19.40	20.43	19.83	20.84	21.28	18.97	20.01	19.40	20.42	20.86
	6H	19.99	20.90	20.45	21.34	21.79	19.56	20.46	20.01	20.90	21.36
	8H	20.18	21.03	20.64	21.47	21.94	19.74	20.59	20.20	21.03	21.50
	12H	20.31	21.07	20.79	21.55	22.02	19.86	20.62	20.34	21.10	21.57
8H	4H	19.67	20.52	20.13	20.96	21.42	19.29	20.14	19.76	20.58	21.05
	6H	20.38	21.09	20.88	21.57	22.05	20.00	20.70	20.50	21.19	21.67
	8H	20.64	21.27	21.15	21.78	22.27	20.25	20.88	20.76	21.39	21.87
	12H	20.84	21.40	21.35	21.89	22.45	20.43	20.99	20.94	21.48	22.04
12H	4H	19.69	20.45	20.17	20.93	21.40	19.33	20.09	19.81	20.57	21.04
	6H	20.43	21.06	20.94	21.57	22.05	20.06	20.69	20.57	21.20	21.68
	8H	20.74	21.30	21.25	21.79	22.35	20.36	20.92	20.87	21.41	21.97