

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930488

Luminaire Tested: DFN2DS-PN2F0-050DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-050DS950-RLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4016.3 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 54
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930488

CATALOG NUMBER: DFN2DS-PN2F0-050DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930488

CATALOG NUMBER: DFN2DS-PN2F0-050DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4230	4230	4230
5°	4246	4177	4200
10°	4213	4108	4073
15°	4165	3987	3872
20°	4098	3812	3621
25°	4029	3615	3378
30°	3934	3412	3067
35°	3841	3192	2794
40°	3748	2963	2478
45°	3638	2707	2192
50°	3526	2448	1912
55°	3410	2169	1642
60°	3277	1875	1363
65°	3125	1576	1241
70°	2943	1298	1141
75°	2721	1183	1065
80°	2402	1058	970
85°	1889	832	832

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3638 cd/sqm

TEST NUMBER: P930488

CATALOG NUMBER: DFN2DS-PN2F0-050DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	4.6
10°-20°	502.4	12.5
20°-30°	705.4	17.6
30°-40°	768.9	19.1
40°-50°	706.7	17.6
50°-60°	555.0	13.8
60°-70°	361.3	9.0
70°-80°	186.0	4.6
80°-90°	47.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1390.9	34.6
0°-40°	2159.8	53.8
0°-60°	3421.5	85.2
0°-90°	4016.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4016.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1953	1953	1953	1953	1953	
5°	1953	1944	1921	1937	1932	185
15°	1857	1838	1778	1744	1727	523
25°	1686	1629	1513	1440	1414	775
35°	1453	1363	1207	1096	1057	909
45°	1188	1069	884	758	716	917
55°	903	765	574	468	435	807
65°	610	466	308	248	242	604
75°	325	201	141	129	127	344
85°	76	39	34	34	34	91
90°	0	0	0	0	0	

TEST NUMBER: P930488

CATALOG NUMBER: DFN2DS-PN2F0-050DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1952.8	1952.8	1952.8	1952.8	1952.8
2.5°	1961.6	1952.8	1933.4	1951.1	1947.6
5°	1952.8	1944.1	1921.0	1936.9	1931.7
7.5°	1936.9	1926.4	1901.6	1908.6	1899.7
10°	1915.7	1903.3	1868.1	1862.7	1852.1
12.5°	1889.2	1873.4	1825.6	1815.1	1795.5
15°	1857.4	1837.9	1777.9	1744.4	1726.7
17.5°	1820.3	1792.0	1717.7	1678.9	1650.5
20°	1777.9	1742.5	1654.1	1610.1	1571.1
22.5°	1732.0	1691.3	1588.7	1528.7	1502.3
25°	1686.0	1629.4	1512.8	1440.4	1413.7
27.5°	1631.3	1571.1	1442.1	1359.0	1318.4
30°	1573.0	1505.7	1364.3	1274.2	1226.4
32.5°	1516.3	1435.0	1290.2	1184.1	1139.9
35°	1452.7	1362.6	1207.1	1095.7	1056.8
37.5°	1390.9	1293.6	1129.4	1007.3	963.2
40°	1325.5	1219.5	1047.9	922.5	876.6
42.5°	1258.4	1145.2	966.7	835.9	791.8
45°	1187.7	1069.2	883.7	758.1	715.6
47.5°	1120.5	995.1	804.2	678.6	639.8
50°	1046.3	920.8	726.4	604.3	567.4
52.5°	973.7	841.1	652.1	535.5	502.0
55°	903.0	765.2	574.3	468.3	434.8
57.5°	830.7	689.3	505.5	406.5	378.2
60°	756.4	615.0	432.9	342.9	314.6
62.5°	684.0	542.6	371.1	286.3	272.3
65°	609.7	466.5	307.5	247.5	242.1
67.5°	539.0	395.9	247.5	217.4	212.1
70°	464.8	327.0	205.0	187.3	180.2
72.5°	394.2	263.3	171.4	157.3	153.8
75°	325.2	201.4	141.4	129.0	127.3
77.5°	256.3	143.1	111.4	104.2	100.6
80°	192.6	102.5	84.8	77.8	77.8
82.5°	134.3	69.0	58.3	54.7	54.7
85°	76.0	38.8	33.5	33.5	33.5
87.5°	28.4	14.1	14.1	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930488

CATALOG NUMBER: DFN2DS-PN2F0-050DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.25	17.77	16.61	18.08	18.40	12.21	13.73	12.57	14.04	14.36
	3H	18.01	19.38	18.39	19.70	20.07	13.47	14.84	13.85	15.16	15.53
	4H	18.68	19.96	19.08	20.31	20.68	13.97	15.25	14.37	15.60	15.98
	6H	19.17	20.35	19.58	20.72	21.11	14.35	15.54	14.77	15.90	16.29
	8H	19.33	20.46	19.76	20.85	21.25	14.48	15.60	14.90	15.99	16.39
	12H	19.43	20.51	19.87	20.89	21.32	14.56	15.64	14.99	16.02	16.45
4H	2H	16.35	17.63	16.75	17.98	18.36	12.90	14.18	13.30	14.53	14.91
	3H	18.28	19.35	18.69	19.75	20.15	14.34	15.41	14.76	15.81	16.21
	4H	19.03	19.99	19.46	20.40	20.84	14.94	15.90	15.38	16.32	16.75
	6H	19.62	20.46	20.08	20.90	21.36	15.43	16.26	15.89	16.71	17.17
	8H	19.84	20.62	20.30	21.06	21.53	15.59	16.37	16.06	16.81	17.28
	12H	19.99	20.69	20.47	21.16	21.64	15.71	16.40	16.19	16.88	17.35
8H	4H	19.06	19.83	19.52	20.28	20.75	15.30	16.08	15.76	16.52	16.99
	6H	19.69	20.34	20.19	20.83	21.30	15.88	16.53	16.38	17.02	17.49
	8H	19.94	20.52	20.46	21.03	21.52	16.10	16.68	16.62	17.19	17.68
	12H	20.15	20.66	20.66	21.15	21.72	16.28	16.79	16.79	17.29	17.85
12H	4H	19.04	19.74	19.52	20.21	20.68	15.34	16.04	15.82	16.51	16.99
	6H	19.67	20.25	20.19	20.76	21.25	15.95	16.52	16.46	17.03	17.52
	8H	19.96	20.47	20.47	20.96	21.53	16.22	16.73	16.73	17.22	17.79