

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930505

Luminaire Tested: DFN2DS-PN2F0-060DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930505
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-060DS950-FLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5613.3 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 67.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930505

CATALOG NUMBER: DFN2DS-PN2F0-060DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930505

CATALOG NUMBER: DFN2DS-PN2F0-060DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4778	4778	4778
5°	4797	4727	4756
10°	4768	4680	4703
15°	4709	4619	4614
20°	4625	4528	4523
25°	4542	4416	4416
30°	4436	4314	4276
35°	4336	4190	4128
40°	4211	4067	3989
45°	4088	3944	3847
50°	3953	3817	3681
55°	3813	3669	3533
60°	3657	3493	3364
65°	3491	3316	3164
70°	3278	3103	2956
75°	2982	2857	2787
80°	2647	2566	2433
85°	2157	2058	1846

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4088 cd/sqm

TEST NUMBER: P930505

CATALOG NUMBER: DFN2DS-PN2F0-060DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.7	3.7
10°-20°	584.3	10.4
20°-30°	858.6	15.3
30°-40°	997.2	17.8
40°-50°	996.0	17.7
50°-60°	868.5	15.5
60°-70°	642.0	11.4
70°-80°	363.2	6.5
80°-90°	95.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1650.5	29.4
0°-40°	2647.7	47.2
0°-60°	4512.2	80.4
0°-90°	5613.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5613.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2206	2206	2206	2206	2206	
5°	2206	2198	2174	2191	2187	209
15°	2100	2088	2060	2068	2058	592
25°	1901	1884	1848	1852	1848	875
35°	1640	1619	1585	1572	1561	1024
45°	1334	1320	1288	1264	1256	1030
55°	1010	997	972	946	936	903
65°	681	668	647	628	617	673
75°	356	352	341	329	333	380
85°	87	85	83	76	74	102
90°	0	0	0	0	0	

TEST NUMBER: P930505

CATALOG NUMBER: DFN2DS-PN2F0-060DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2206.2	2206.2	2206.2	2206.2	2206.2
2.5°	2219.0	2208.5	2185.0	2206.2	2202.1
5°	2206.2	2197.9	2174.4	2191.4	2187.3
7.5°	2191.4	2178.8	2155.4	2172.5	2168.2
10°	2168.2	2153.4	2127.9	2144.8	2138.4
12.5°	2136.3	2123.6	2098.2	2108.8	2104.5
15°	2100.2	2087.6	2059.9	2068.5	2057.9
17.5°	2055.7	2043.1	2015.4	2025.9	2015.4
20°	2006.8	1994.2	1964.5	1970.8	1962.5
22.5°	1958.2	1939.0	1911.4	1911.4	1907.1
25°	1900.8	1884.0	1847.9	1851.9	1847.9
27.5°	1837.1	1822.2	1794.7	1788.5	1777.9
30°	1773.7	1756.5	1724.8	1718.5	1709.9
32.5°	1705.6	1693.1	1659.0	1646.2	1637.7
35°	1640.0	1618.8	1584.8	1571.9	1561.3
37.5°	1565.7	1546.5	1512.6	1497.6	1487.1
40°	1489.3	1472.2	1438.3	1419.4	1410.8
42.5°	1415.0	1397.9	1364.2	1342.8	1330.2
45°	1334.5	1319.6	1287.7	1264.5	1255.9
47.5°	1255.9	1241.1	1207.1	1183.7	1171.0
50°	1173.1	1162.5	1132.9	1103.1	1092.5
52.5°	1092.5	1077.7	1050.2	1026.8	1012.0
55°	1009.9	997.1	971.6	946.2	935.6
57.5°	927.1	916.6	888.9	863.4	854.8
60°	844.3	835.9	806.3	782.8	776.5
62.5°	763.7	748.8	727.6	706.5	698.0
65°	681.1	668.3	647.1	628.0	617.4
67.5°	596.2	585.4	566.5	551.7	543.1
70°	517.7	509.2	490.0	475.1	466.8
72.5°	437.1	428.6	418.0	403.1	396.8
75°	356.3	352.3	341.4	328.9	333.1
77.5°	284.3	275.8	271.4	265.2	258.8
80°	212.2	210.0	205.7	199.4	195.1
82.5°	144.3	144.3	142.2	133.7	133.7
85°	86.8	84.9	82.8	76.3	74.3
87.5°	38.3	34.0	29.7	23.4	21.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930505

CATALOG NUMBER: DFN2DS-PN2F0-060DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.72	18.33	17.08	18.64	18.96	16.27	17.88	16.64	18.20	18.51
	3H	18.47	19.92	18.84	20.25	20.61	17.98	19.43	18.35	19.76	20.12
	4H	19.11	20.48	19.51	20.83	21.21	18.62	19.99	19.02	20.34	20.71
	6H	19.58	20.85	19.99	21.22	21.61	19.08	20.35	19.49	20.71	21.10
	8H	19.73	20.94	20.15	21.33	21.72	19.22	20.43	19.65	20.82	21.22
	12H	19.82	20.98	20.25	21.36	21.79	19.30	20.46	19.73	20.85	21.27
4H	2H	17.28	18.65	17.68	18.99	19.37	16.92	18.29	17.32	18.64	19.02
	3H	19.25	20.40	19.66	20.80	21.20	18.85	19.99	19.26	20.39	20.79
	4H	20.03	21.07	20.46	21.48	21.91	19.61	20.64	20.04	21.05	21.49
	6H	20.63	21.53	21.08	21.97	22.43	20.19	21.10	20.65	21.54	21.99
	8H	20.82	21.66	21.28	22.10	22.57	20.38	21.22	20.84	21.67	22.13
	12H	20.95	21.71	21.43	22.18	22.65	20.49	21.25	20.97	21.73	22.20
8H	4H	20.30	21.15	20.76	21.59	22.06	19.93	20.77	20.39	21.22	21.68
	6H	21.02	21.72	21.51	22.21	22.68	20.63	21.34	21.13	21.83	22.30
	8H	21.28	21.91	21.79	22.41	22.90	20.88	21.51	21.39	22.02	22.51
	12H	21.48	22.03	21.98	22.52	23.09	21.06	21.62	21.57	22.11	22.67
12H	4H	20.33	21.09	20.81	21.56	22.03	19.96	20.72	20.44	21.20	21.67
	6H	21.06	21.69	21.57	22.20	22.69	20.69	21.33	21.20	21.83	22.32
	8H	21.38	21.93	21.88	22.42	22.99	21.00	21.56	21.50	22.05	22.61

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7